

ThinkCentre M75s Gen 2

Looking for a versatile device to support existing or new desk workers in your company? This compact, space-saving desktop can be configured to meet a wide variety of user expectations - from basic admin use to extensive productivity tasks. It comes with thoughtful features like Smart Power-On to which enables the PC to be started via a keyboard shortcut instead of reaching for the power button.



For employees working with data or graphics, configure the device with 128GB DDR4 memory to boost multitasking performance, AMD Radeon 520 graphics, up to 2x fast SSD storage drives, and the latest AMD Ryzen™ 9 Pro processor.

There are 9x USB ports including 5 located on the front of the device. If data security is a concern, Smart USB protection can block data transfer but still enable keyboards, mice and printers to be used.

Optimized to reduce power consumption with EPEAT Gold and Energy Star 8.0 certifications.

Mainstream computing for a variety of business uses

ThinkCentre M7 Series desktops offer enterprise security features, a wide range of configurations and expansion options, and reliability trusted by leading businesses across the globe.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..

Accessories

ThinkVision T27i-10

27" Full HD monitor with wide viewing angle and 1000:1 contrast ratio
1x HDMI, 1x DisplayPort, 1x VGA, 4x USB3.0, 1x USB3.0 Type-B upstream, audio out
Lift, Tilt, Pivot, Swivel stand for viewing comfort



ThinkVision T24i-10

23.8" Full HD monitor with 72% NTSC colour gamut & anti-glare coating
1x HDMI, 1x DisplayPort, 1x VGA, 4x USB3.0, 1x USB3.0 Type-B upstream, audio out
Lift, Tilt, Pivot, Swivel stand for viewing comfort



ThinkCentre M75s Gen 2

Key Specifications

Processor

Up to AMD Ryzen 9 Pro processor

Operating System

Powered by Windows 11 Pro

Graphics

AMD Radeon Vega 11, 8 or 3, optional AMD Radeon 520 2GB

Memory

Up to 128GB DDR4-3200

Storage

Internal storage: up to 1x 3.5" 2TB SATA HDD + 1x 2.5" 1TB SATA HDD or 2x 2.5" 256GB SATA SSD

M.2 SSD: up to 1x 1TB M.2 PCIe NVMe

Optical

Optional DVD-ROM or DVD burner

Additional Internal Bays

Optional 2.5" Bay

Expansion Slots

PCIe x16, low-profile

PCIe x1, low-profile

Power Supply

One of the following

180W 85% | 260W 85% | 310W 92%

Dimensions

Width: 93mm (3.6") Depth: 298mm (11.7") Height: 340mm (13.4")

Weight

Starting at 5.3kg (11.7lb)

Green Certifications

EPEAT Gold, Energy Star 8.0.

Connectivity

Front I/O

2x USB 3.2 Gen 2, 2x USB 3.2 Gen 1, 1x USB 3.2 Type-C Gen 1, 1x microphone (3.5mm), 1x headphone / microphone combo jack (3.5mm), optional 3-in-1 card reader

Rear I/O

4x USB 2.0, 1x serial (9-pin), 1x ethernet (RJ-45), 2x DisplayPort, 1x HDMI, 1x line-out (3.5mm); Optional: 2x USB 3.2 Gen 1 via PCIe x1, 2x USB 3.2 Type-C Gen 2 via PCIe x4, 1x 2nd serial (9-pin), 1x parallel (25-pin)

Optional Rear Ports

One of the following

1x Parallel | 1x Parallel + 1x Serial | 1x Parallel + 1x Serial + 2x USB 2.0 | 1x Parallel + 1x Serial + 2x USB 3.2 Gen 1 | 1x Parallel + 2x USB 2.0 | 1x Parallel + 2x USB 3.2 Gen 1 | 1x Serial | 1x Serial + 2x USB 2.0 + 2x USB 3.2 Gen 1 | 1x Serial + 2x USB 3.2 Gen 1 | 1x Serial + 2x USB-C 3.2 Gen 2 | 2x USB 2.0 | 2x USB 2.0 + 2x USB 3.2 Gen 1 | 2x USB 2.0 + 2x USB-C 3.2 Gen 2 + 2x USB 3.2 Gen 1 | 2x USB 3.2 Gen 1 | 2x USB-C 3.2 Gen 2 | 4x Serial | 5x Serial

WLAN + Bluetooth

One of the following

Intel 9260, 11ac 2x2 + BT5.0 | Intel Wi-Fi 6 AX200, 11ax 2x2 + BT5.1 | MediaTek Wi-Fi 6 MT7921, 11ax 2x2 + BT5.1 | Realtek RTL8822CE, 11ac 2x2 + BT5.0 | Realtek Wi-Fi 6 RTL8852AE, 11ax 2x2 + BT5.1

Ethernet

One of the following

Integrated 100/1000M | Integrated 100/1000M + BN8E88 | Integrated 100/1000M + RTL8111FP

Security & Privacy

Chassis Intrusion Switch

E-Lock

Kensington lock slot

Padlock slot

Smart USB protection

Hardware TPM

Manageability

DASH 1.2

Non-DASH

Optional Mechanical Peripherals

ThinkCentre Dust Filter