



stellar

Product Specifications

Stellar Plus Black Nitrile Examination Gloves



Measurements

Material	Cuff thickness	Palm Thickness	Finger thickness	Length	Donning	Colour	Texture
Nitrile	0.10 +/- 0.01	0.13 +/- 0.01	0.16 +/- 0.01	240 mm	Powder Free	Black	Fully Textured

Item #	Size	Glove Weight (g)	Palm Width	Case Weight (lbs)
002-E10205-S	Small	6.0 +/- 0.1	85 +/- 5	13.2
002-E10205-M	Medium	6.5 +/- 0.1	95 +/- 5	14.3
002-E10205-L	Large	6.9 +/- 0.1	105 +/- 5	15.2
002-E10205-XL	Extra Large	7.2 +/- 0.1	115 +/- 5	15.9
002-E10205-2XL	2 Extra Large	7.5 +/- 0.1	120 +/- 5	16.5

	Before Aging	After Aging
Tensile Strength (Mpa)	Min 22	Min 22
Elongation (%)	Min 500	Min 400
Force at Break	Min 500	Min 400

	Length (mm)	Width (mm)	Height (mm)
Case Dimensions	358	245	245
Box Dimensions	235	120	70

Storage: To be stored in a dry environment, avoid direct sunlight

Shelf Life: 5 year from date of manufacturing

Packaging: 100 Gloves / Box x 10 Boxes / Case= 1,000 Gloves / Case

Country of Origin: Thailand

Acceptances: Comply with CFIA and FDA guidelines

Health Canada licenced Class II medical device



LATEX FREE



NON-STERILE



POWDER FREE

Stellar Safety Supply

www.stellarsafetysupply.com

1.844.459.0015