



FN80

High performance 80mm fan

- High efficiency exhaust application fan
- Hydraulic bearing for extended life and low operational noise
- Suitable for HTPC and SFF cases

Product Specifications

Model No.

SST-FN80B

Color

Black

Connectors

3 pin connector

Starting Voltage

6.5V

Rated Power

1.8W

Airflow

27.81 CFM

Noise Level

22.9 dBA

Weight

70g

Material

PBT

Bearing

Hydraulic bearing

Rated Voltage

12V

Rated Current

0.15A

Speed


2000 RPM

Static Pressure

1.86mmH₂O


Dimension

80mm (W) x 25mm (H) x 80mm (D)
3.15" (W) x 0.98" (H) x 3.15" (D)



Ideal for HTPC & SFF applications

At a mere 80mm in size, FN80 is designed to work flawlessly as an exhaust application for HTPC and SFF ecosystems.



Higher airflow and reduced noise with 7-blade design

Equipped with Hydro Dynamic Bearing (HDB) providing great reliability with low noise operation and great life expectancy.

