


OVERVIEW



1. Power button	8. HDMI 2.1 TMDS
2. Card reader *	9. VGA
3. Microphone (3.5mm)	10. Ethernet (RJ-45)
4. Headphone / microphone combo jack (3.5mm)	11. 2x USB 2.0
5. USB-C 3.2 Gen 1 (support data transfer and 5V@3A charging)	12. USB 3.2 Gen 1 (with smart power on)
6. 2x USB 3.2 Gen 1	13. USB 3.2 Gen 1
7. Line-out (3.5mm)	14. Power connector

Notes:

- Items with * are only available on selected models

PERFORMANCE

Processor

Processor Family

13th Generation Intel® Core™ i5 / i7 Processor

Processor**^[1]

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
Core i5-13400	10 (6 P-core + 4 E-core)	16	P-core 2.5GHz / E-core 1.8GHz	P-core 4.6GHz / E-core 3.3GHz	20MB	DDR4-3200	Intel UHD Graphics 730
Core i7-13700	16 (8 P-core + 8 E-core)	24	P-core 2.1GHz / E-core 1.5GHz	Max Turbo up to 5.2GHz / P-core 5.1GHz / E-core 4.1GHz	30MB	DDR4-3200	Intel UHD Graphics 770

Notes:

^[1] Intel Max Turbo frequency will vary depending on application workload and the hardware and software configurations, see <http://www.intel.com/technology/turboboost/> for more information.

Operating System

Operating System**

- Windows® 11 Home
- Windows 11 Home Single Language
- Windows 11 Pro
- No operating system

Graphics

Graphics**

Graphics	Type	Memory	Connector	Max Resolution	Key Features
Intel UHD graphics 730	Integrated	Shared	1x VGA, 1x HDMI® 2.1 TMDS	1920x1200@60Hz(VGA), 3840x2160@60Hz(HDMI)	DirectX® 12
Intel UHD graphics 770	Integrated	Shared	1x VGA, 1x HDMI 2.1 TMDS	1920x1200@60Hz(VGA), 3840x2160@60Hz(HDMI)	DirectX 12

Monitor Support

Monitor Support

Supports up to 2 independent displays via onboard ports (VGA + HDMI)

Chipset

Chipset

Intel B660 chipset

Memory

Max Memory^[1]

Up to 32GB DDR4-3200

Memory Slots

Two DDR4 UDIMM slots, dual-channel capable

Memory Type

DDR4-3200

Memory Protection

Non-ECC

Notes:

^[1] The max memory is based on the test results with current Lenovo® memory offerings.

Storage

Storage Support^[1]

Up to two drives, 1x 3.5" HDD + 1x M.2 SSD

- 3.5" HDD up to 2TB
- M.2 SSD up to 1TB

Storage Type**

Disk Type	Interface	RPM
3.5" SATA HDD	SATA 6Gb/s	7.2K
M.2 2280 SSD	PCIe® NVMe®, PCIe 4.0 x4	-

RAID

No support

Notes:

[1] The max capacity of each disk type is based on the test results with current Lenovo storage offerings.

Removable Storage

Optical

None

Card Reader

- 7-in-1 card reader (SD, SDHC, SDXC, MMC, MS, MS-Pro, MMC plus)
- No card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC623-CG codec

Speakers

No speakers

Power Supply

Power Supply**

Power	Type	Efficiency	Key Features
180W	Fixed	85%	Autosensing
260W	Fixed	85%	100-240V, 50-60Hz

DESIGN

Input Device

Keyboard

- Lenovo Calliope Keyboard (USB connector), black
- No keyboard

Mouse

- Lenovo Calliope Mouse (USB connector), black
- No mouse

Mechanical

Form Factor

SFF (7.4L)

Dimensions (WxDxH)^[1]

100 x 303.5 x 274.8 mm (3.9 x 11.94 x 10.8 inches)

Packaging Dimensions (WxDxH)

195 x 500 x 390 mm (7.7 x 19.7 x 15.4 inches)

Weight^[2]

Models	Weight
Around	4.4 kg (9.8 lbs)

Packaging Weight

Around 6.25 kg (13.8 lbs)

Case Color

Cloud grey

Bays

1x 3.5" disk bay

Expansion Slots

Two M.2 slots (one for WLAN, one for SSD)

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

Onboard Ethernet

Gigabit Ethernet, 1x RJ-45

WLAN + Bluetooth®

Wi-Fi® 6, 802.11ax 2x2 Wi-Fi + Bluetooth 5.1, M.2 card

Ports^[1]

Front Ports

- 1x USB-C® 3.2 Gen 1 (support data transfer and 5V@3A charging)
- 2x USB 3.2 Gen 1
- 1x headphone / microphone combo jack (3.5mm)
- 1x microphone (3.5mm)

Rear Ports

- 2x USB 2.0
- 2x USB 3.2 Gen 1
- 1x HDMI 2.1 TMDS
- 1x VGA
- 1x Ethernet (RJ-45)
- 1x audio-out (3.5mm)

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

SECURITY & PRIVACY

Security

Security Chip

Firmware TPM 2.0 integrated in chipset

BIOS Security

- Administrator password
- Power-on password
- Hard disk password

MANAGEABILITY

System Management

System Management

None

SERVICE

Warranty^[1]

Base Warranty**

- 1-year mail-in service
- 1-year courier or carry-in service
- 1-year limited onsite service
- 2-year courier or carry-in service
- 3-year courier or carry-in service

Notes:

[1] The warranty upgrades may be bundled with some models, please check the "Included upgrade" column in the specific model's configurations. For more service extensions, please go to <https://smartfind.lenovo.com/>. To learn more details of warranty policy, please access <https://pcsupport.lenovo.com/warranty>.

ENVIRONMENTAL

Operating Environment

Temperature

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage: -40°C (-40°F) to 60°C (140°F)

Humidity

- Operating: 20% to 80%
- Storage: 10% to 90%

Altitude

- Operating: 0 m (0 ft) to 3048 m (10,000 ft)
- Storage: 0 m (0 ft) to 12192 m (40,000 ft)

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- ErP Lot 3
- RoHS compliant

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

- Feature with ** means that only one offering listed under the feature is configured on selected models.

responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.


- The specifications on this page may not be available in all regions, and may be changed or updated without notice.




intel



intel



intel



intel



intel