

SAFETY DATA SHEET

Confirms to OSHA Hazard Communication Standard (CFR 29 1910.1200) HazCom 2012



Product: Stainless Steel Cleaner and Polish- 02, 02A, 02WMA, 49, 49A, 102, 494, 955D

Revision Date: 16-Mar-2021

SECTION 1 – IDENTIFICATION

Product Identifier

Product Name: Stainless Steel Cleaner and Polish

Product Code: 02, 02A, 02WMA, 49, 49A, 102, 494, 955D

Recommended Use of the Chemical and Restrictions for Use

Recommended Use: Cleaner

Restrictions for Use: Use only as directed.

Details of the Supplier

Manufacturer: Weiman Products
755 Tri-State Parkway
Gurnee, IL 60031
847-263-3500

Emergency Phone Number

24-Hour Number: 1-800-535-5053

International: 1-352-323-3500

SECTION 2 – HAZARDS IDENTIFICATION

Classification

Hazard Class	Category
Flammable aerosol	2
Gases under pressure- Liquefied gas	N/A

Label Elements

Hazard Symbols(s):



Signal Word(s): Warning

Hazard Statement(s): Flammable aerosol. Contains gas under pressure; may explode if heated.

Precautionary Statement(s): Keep away from heat/sparks/open flames/hot surfaces.-No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use. Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. Store in well-ventilated place.

Other Hazards

1% of the mixture consists of ingredients of unknown acute toxicity.

SECTION 3 – COMPOSITION / INFORMATION ON INGREDIENTS

Chemical Name	CAS Number	Wt %
Petroleum gases, liquefied	68476-85-7	10-30
Petroleum distillates, hydrotreated light	64742-47-8	7-13
White mineral oil, petroleum	8042-47-5	7-13

The exact percentage (concentration) of composition has been withheld as a trade secret in accordance with paragraph (i) of §1910.1200.

SECTION 4 – FIRST AID MEASURES

First Aid Measures

Inhalation: If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical advice/attention if you feel unwell.

Eye Contact: In case of contact, immediately flush eyes with plenty of water. Remove contact lenses, if worn. If irritation persists, get medical attention.

SAFETY DATA SHEET

Confirms to OSHA Hazard Communication Standard (CFR 29 1910.1200) HazCom 2012



Product: Stainless Steel Cleaner and Polish- 02, 02A, 02WMA, 49, 49A, 102, 494, 955D

Revision Date: 16-Mar-2021

Ingestion: If swallowed, do NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical advice/attention if you feel unwell.

Skin: If irritation occurs, flush skin with plenty of water. Get medical attention if irritation persists.

Most Important Symptoms and Effects (Acute and Delayed)

Inhalation: May cause respiratory tract irritation.

Eye Contact: May cause eye irritation. Symptoms may include discomfort or pain, excess blinking and tear production, with possible redness and swelling.

Ingestion: May be harmful if swallowed. May cause stomach distress, nausea or vomiting.

Skin: May cause skin irritation. Symptoms may include redness, drying, defatting and cracking of the skin.

Indication of any Immediate Medical Attention and Special Treatment Needed

Note to Physician: Treat symptomatically.

SECTION 5 – FIRE FIGHTING MEASURES

Extinguishing Media

Suitable: Treat for surrounding material.

Unsuitable: None known.

Specific Hazards Arising from Chemical

Flammable aerosol. Products of combustion include, and are not limited to: oxides of carbon. Heat may build pressure, rupturing closed containers, spreading fire and increasing risk of burns and injuries.

Protective Equipment and Precautions for Firefighters

Cool closed containers exposed to fire with water spray. Keep upwind of fire. Wear full fire-fighting turn-out gear (full Bunker gear) and respiratory protection (SCBA).

SECTION 6 – ACCIDENTAL RELEASE MEASURES

Personal Precautions, Protective Equipment, and Emergency Procedures

Personal Precautions: Use personal protection recommended in Section 8. Isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental Precautions: See Section 12 for ecological information.

Methods and Material for Containment and Cleaning Up

Eliminated sources of ignition. Contain and/or absorb spill with inert material (e.g. sand, vermiculite), then place in a suitable container. Do not flush to sewer or allow to enter waterways. Use appropriate Personal Protective Equipment (PPE). Scoop up material and place in a disposal container. Provide ventilation.

SECTION 7 – HANDLING AND STORAGE

Precautions for Safe Handling

Handling: Keep away from sources of ignition- No smoking. Avoid contact with skin and eyes. Avoid breathing dust/fume/gas/mist/vapors/spray. Do not swallow. When using do not eat, drink or smoke. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use.

General Hygiene Advice: Launder contaminated clothing before use. Wash hands before eating, drinking, or smoking.

Conditions for Safe Storage, Including any Incompatibilities

Storage Conditions: Proper grounding procedures to avoid static electricity should be followed. Keep out of the reach of children. Do not expose to temperatures exceeding 50°C/122°F. Store away from direct sunlight or other heat sources. Store in a well-ventilated place.

Incompatible Materials: Strong oxidizing agents.

SECTION 8 – EXPOSURE CONTROLS/PERSONAL PROTECTION

Control Parameters

Exposure Guidelines:

Document No.: 130529-5
Release Date: 1/10/2014

SAFETY DATA SHEET

Confirms to OSHA Hazard Communication Standard (CFR 29 1910.1200) HazCom 2012



Product: Stainless Steel Cleaner and Polish- 02, 02A, 02WMA, 49, 49A, 102, 494, 955D

Revision Date: 16-Mar-2021

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Petroleum gases, liquefied (68476-85-7)	1000 ppm	180 mg/m ³	Not available
Petroleum distillates, hydrotreated light (64742-47-8)	Not available	Not available	Not available
White mineral oil, petroleum (8042-47-5)	Not available	Not available	Not available

Appropriate Engineering Controls

Use ventilation adequate to keep exposures (airborne levels of dust, fume, vapor, etc.) below recommended exposure limits.

Individual Protection Measures

Respiratory Protection: In case of insufficient ventilation, wear suitable respiratory equipment. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

Skin and Body Protection: Wear suitable protective clothing.

Eye/Face Protection: Safety glasses or goggles are recommended when using product.

General Work/Hygienic Practices: Handle in accordance with good industrial hygiene and safety practice.

SECTION 9 – PHYSICAL AND CHEMICAL PROPERTIES

Appearance: White emulsion

Odor: Floral

Odor threshold: Not determined

pH: Not determined

Melting point/freezing point: Not determined

Initial boiling point and boiling range: Not determined

Flash point: >93.3°C (>200°F) TCC (concentrated product)

Evaporation rate: Not determined

Flammability (solid, gas): Flammable aerosol

Upper/lower flammability or explosive limits: Not determined

Vapor pressure: Not determined

Vapor density: Not determined

Relative density: 0.94

Solubility(ies): Not determined

Partition coefficient (n-octanol/water): Not determined

Auto-ignition temperature: Not determined

Decomposition temperature: Not determined

Viscosity: 2900-5600 cP at 25°C (77°F)

SECTION 10 – STABILITY AND REACTIVITY

Reactivity: Not reactive under normal conditions.

Chemical stability: Stable under recommended storage conditions. Flammable aerosol. Contents under pressure. Container may explode if heated. Do not puncture. Do not burn.

Possibility of hazardous reactions: None under normal use.

Conditions to avoid: Heat. Incompatible materials. Sources of ignition.

Incompatible materials: Strong oxidizing agents.

Hazardous decomposition products: May include and are not limited to: oxides of carbon.

SECTION 11 - TOXICOLOGICAL INFORMATION

Information on Toxicological Effects

SAFETY DATA SHEET

Confirms to OSHA Hazard Communication Standard (CFR 29 1910.1200) HazCom 2012



Product: Stainless Steel Cleaner and Polish- 02, 02A, 02WMA, 49, 49A, 102, 494, 955D

Revision Date: 16-Mar-2021

Likely Routes of Exposure: Inhalation, skin contact, eye contact, ingestion

Information Related to Physical, Chemical, and Toxicological Effects

See section 4 of this SDS.

Delayed and Immediate Effects as well as Chronic Effects from Short and Long-term Exposure

Carcinogenicity: NTP: No IARC: No OSHA: No

Numerical Measures of Toxicity

Product	
ATE (oral)	>2000 mg/kg, rat
ATE (dermal)	>2000 mg/kg, rabbit
ATE (inhalation)	>5 mg/l/4h, rat

Component Information:

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Petroleum gases, liquefied (68476-85-7)	Not available	Not available	658 mg/l/4h (rat)
Petroleum distillates, hydrotreated light (64742-47-8)	>5000 mg/kg (rat)	>2000 mg/kg (rabbit)	>5.2 mg/l/4h (rat)
White mineral oil, petroleum (8042-47-5)	>5000 mg/kg (rat)	>2000 mg/kg (rabbit)	>5 mg/l/4h (rat)

SECTION 12 - ECOLOGICAL INFORMATION

Ecotoxicity: Not established

Persistence and degradability: Not established

Bioaccumulative potential: Not established

Mobility in soil: Not established

Other adverse effects: No additional information available.

SECTION 13 – DISPOSAL CONSIDERATIONS

See section 8 of this SDS for exposure controls and personal protection.

Dispose of the product and container in accordance with all applicable local, state, and federal regulations.

SECTION 14 – TRANSPORT INFORMATION

Note: Classification changes based on quantity, packaging, and method of shipment. See current shipping paper for most up to date shipping information.

UN1950, Aerosols, 2.1

DOT (Ground): Limited quantity

IATA (Air): Regulated

IMDG (Vessel): Limited quantity

SECTION 15 – REGULATORY INFORMATION

All ingredients in this product are listed or are excluded from listing on the US Toxic Substances Act (TSCA) Chemical Substance Inventory.

This product is labeled in accordance with regulations administered by the Consumer Product Safety Commission (CPSC). The use pattern and exposure in the workplace are generally not consistent with those experienced by consumers. The requirements of the Occupational Safety and Health Administration (OSHA) applicable to this Safety Data Sheet differ from the requirements of the CPSC and as a result, this SDS may contain additional health hazard information not pertinent to consumer use and not found on the product label.

SECTION 16 – OTHER INFORMATION

Issue Date: 11-Mar-2015

Revision Date: 16-Mar-2021

SAFETY DATA SHEET

Confirms to OSHA Hazard Communication Standard (CFR 29 1910.1200) HazCom 2012



Product: Stainless Steel Cleaner and Polish- 02, 02A, 02WMA, 49, 49A, 102, 494, 955D

Revision Date: 16-Mar-2021

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information, and belief at the date of its publication. The information given is designed only as guidance for safe handling, use, processing, storage, transportation, disposal, and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designed and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet