


ProductSheet  
**HP P22va G4 FHD Monitor (453D2AA)**



**An everyday, affordable business monitor that's easy on you.**

Tackle your daily task list with the budget-friendly HP P22va G4 Monitor that adjusts to your comfort needs and delivers Full HD picture quality.



**Crisp image clarity for all your content.**

Get lifelike color and sharp details for everything you do on a 21.5" diagonal Full HD screen with 178° x 178° viewing angles.

**Modern connectivity.**

Conveniently and quickly connect to your devices and additional monitors through the HDMI and VGA ports, no dongles required.

**Make conscientious buying choices.**

Choose a monitor that's TCO and ENERGY STAR® certified to help meet your environmental buying requirements.

**Featuring**

**Personalize your comfort settings.**

See your screen in a whole new light with HP Low Blue Light for more comfortable viewing, then tilt the screen up to 5° forward or 20° back for your best viewing position.

**Personalize and help protect your monitor.**

Customize your monitor and help deter its theft with easy, intuitive HP Display Center software that lets you tailor your settings, partition screens, and more through the host PC. <sup>[1]</sup>

**We have your back.**

Rest assured that your IT investment is supported with our three-year standard limited warranty. <sup>[2]</sup>

## Specifications

<b>Display size (diagonal)</b>	21.5"
<b>Panel technology</b>	VA
<b>Display size (diagonal)</b>	54.6 cm (21.5")
<b>Aspect ratio</b>	16:9 <sup>[1]</sup>
<b>Native resolution</b>	FHD (1920 x 1080) <sup>[1]</sup>
<b>Resolutions supported</b>	1024 x 768; 1280 x 1024; 1280 x 720; 1280 x 800; 1440 x 900; 1600 x 900; 1680 x 1050; 1920 x 1080; 640 x 480; 720 x 400; 800 x 600
<b>Pixel pitch</b>	0.0831 mm x 0.241 mm
<b>Brightness</b>	250 nits <sup>[1]</sup>
<b>Contrast ratio</b>	3000:1 <sup>[1]</sup>
<b>Response time (typical)</b>	7ms GtG (with overdrive) <sup>[1]</sup>
<b>Minimum dimensions (W x D x H)</b>	50.43 x 4.4 x 30.02 cm (Without stand.)
<b>Minimum dimensions (W x D x H)</b>	19.85 x 1.73 x 11.82 in (Without stand.)
<b>Dimensions With Stand (W x D x H)</b>	50.43 x 18.1 x 36.71 cm
<b>Weight</b>	2.84 kg (With stand.)
<b>Weight</b>	6.27 lb (With stand.)
<b>Display features</b>	Anti-glare; Low blue light mode
<b>Onscreen controls</b>	Exit; Information; Management; Menu; Power control; Input control; Brightness+; Image; Color
<b>Display colors</b>	Up to 16.7 million colors supported (through FRC technology)
<b>Display scan frequency (horizontal)</b>	30-80 KHz
<b>Display scan frequency (vertical)</b>	50-60 Hz
<b>Camera</b>	No integrated camera
<b>Power</b>	100 - 240 VAC 50/60 Hz
<b>Power consumption</b>	20 W (maximum), 18.5 W (typical), 0.5 W (standby)
<b>Operating temperature range</b>	5 to 35°C
<b>Operating humidity range</b>	20 to 80% non-condensing
<b>Certifications and compliances</b>	Australian-New Zealand MEPS; BIS; BSMI; CB; CCC; CE; CECP; CEL; cTUVus; EAC; ENERGY STAR®; E-standby; EUP Lot-5; EUP Lot-6; FCC; ICES; ISO 9241-307; KC/KCC; NOM; VCCI; Vietnam MEPS; WEEE; Low blue light; EUP Lot-26; California Energy Commission (CEC); South Africa Energy; WW application; UAE; Ukraine certificates; NRCS of South Africa
<b>Ecolabels</b>	EPEAT® Silver
<b>Physical security</b>	Security lock-ready <sup>[2]</sup>
<b>Management Software</b>	HP Display Assistant
<b>UPC number</b>	195908960966
<b>What's in the box</b>	Monitor; HDMI cable; Documentation; AC power cord <sup>[4,5]</sup>

## Top Recommended Displays, Accessories and Services

---

### Personal Systems Commercial Care Pack Services

HP 4y Next Business Day Response Advanced Exchange Small DisplayHardware Support	U0J10E
HP 5y Next Business Day Response Advanced Exchange Small DisplayHardware Support	U0J11E

## Messaging Footnotes

[1] Requires Windows 10 on host PC.

[2] HP Care Packs sold separately. Service levels and response times for HP Care Packs may vary depending on your geographic location. Service starts on date of hardware purchase. Restrictions and limitations apply. For details, visit [www.hp.com/go/cpc](http://www.hp.com/go/cpc). HP Services are governed by the applicable HP terms and conditions of service provided or indicated to Customer at the time of purchase. Customer may have additional statutory rights according to applicable local laws, and such rights are not in any way affected by the HP terms and conditions of service or the HP Limited Warranty provided with your HP Product.

## Technical Specifications Footnotes

[1] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[2] Lock sold separately.

[4] Monitors produced until December 2020 are delivered with VGA cable. Monitors produced from December 2020 are delivered with HDMI cable.

[5] China continues shipping with VGA cable, no HDMI cable is included.

Learn more at  
[hp.com](http://hp.com)

---

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

ENERGY STAR® is a registered trademark of the U.S. Environmental Protection Agency.

