

ThinkPad T14 Gen 4 (Intel)

Designed for hybrid users in need of everyday computing power and functionality, this ThinkPad has everything you seek for comfortable days at work. It is power packed with 13th Gen Intel Core i7 processor, integrated Intel Iris Xe graphics and up to 2TB SSD storage to sail you through the busiest days at work. The multiple standard and optional ports, including Thunderbolt 4 enable data transfers, power delivery and connectivity to surrounding devices, monitors and peripherals.



Its 14" 2.8K display presents visuals that are rich in colors and are too detailed to be true. Plus, the multi-touch, anti-glare screen surface is Eyesafe certified and lets users to work comfortably for longer hours without straining their eyes.

It also onboards a full range of smart security features such as discrete TPM 2.0 chip, Kensington Nano security slot, touch style fingerprint reader, optional camera privacy shutter and optional RFID reader.

Minimal preloaded applications mean maximum battery life and responsiveness for users, and faster deployment for IT admins.

Lenovo devices that are a class apart

The ultimate productivity notebook, ThinkPad T Series will keep users productive all day with long battery life, docking and enhanced connectivity options, security and manageability features.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

No-hassle repair process at a Lenovo service center
 Lenovo pays for all shipping between the customer and service facility
 Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo Essential FHD Webcam

This camera is powered by a Full HD 1080P 2.1 megapixel CMOS camera
 Plug and play setup, no drivers needed
 Full stereo dual-mics that are perfect for conferencing or long-distance video calls



PN: 4XC1B34802

Lenovo 700 Ultraportable Bluetooth Speaker

Just 11mm (0.43") thin and weighing 145g (0.32lb), this ultra-thin Bluetooth speaker delivers 360-degree sound with 2x 2Watt power output
 Supports Siri and Google Assistant voice commands for your iOS and Android devices, as well as a dedicated button for taking calls
 Fast-charges in 2 hours and lasts for up to 12hours of audio playback or voice calls



PN: 4XD0T32974

ThinkPad T14 Gen 4 (Intel)

Key Specifications

<p>Processor 13th Gen Intel U or P Series Core i5 / i7</p>
<p>Operating System Windows 11 Pro, Windows 11 Home, Windows 11 Home Single Language, Windows 11 DG Windows 10 Pro 64, Linux, Ubuntu Linux</p>
<p>Display 14", WUXGA (1920x1200), IPS, Anti-glare display, 16:10 Aspect Ratio - 300nits Brightness, 45% NTSC Color Gamut - 300nits Brightness, 45% NTSC Color Gamut, touch - 400nits Brightness, 100% sRGB Color Gamut, low power, Eyesafe, ICC Template color calibration - 500nits Brightness, 100% sRGB Color Gamut, touch, ThinkPad Privacy Guard</p> <p>14", 2.2K (2240x1400), IPS, Anti-glare display, 16:10 Aspect Ratio - 300nits Brightness, 100% sRGB Color Gamut, Eyesafe certified</p> <p>14", 2.8K (2880x1800), OLED AGARAS display, 16:10 Aspect Ratio - 400nits Brightness, 100% DCI-P3, DisplayHDR True Black 500, Dolby Vision, Eyesafe certified</p>
<p>Touchscreen Optional Touchscreen</p>
<p>Graphics Intel Iris Xe Graphics (integrated), NVIDIA GeForce MX550</p>
<p>Memory Up to 32GB LPDDR5x-6400, soldered Up to 40GB DDR4-3200, 1x Soldered + 1x SO-DIMM Up to 32GB DDR5-5200, 1x Soldered + 1x SO-DIMM</p>
<p>Storage Up to 1x 2TB M.2 2280 PCIe NVMe SSD</p>
<p>Audio High Definition (HD) Audio 2W x2, Dolby Audio Stereo speakers 360° far-field, Dolby Voice Dual-array microphone</p>
<p>Battery[†] 39.3Wh or 52.5Wh battery, up to 9.5 hr battery life, Rapid Charge support</p>
<p>Power Adapter <i>One of the following</i> 45W USB-C (2-pin) 45W USB-C (3-pin) 65W USB-C (2-pin) 65W USB-C (3-pin) 65W USB-C Slim (2-pin) 65W USB-C Slim (3-pin)</p>
<p>Camera <i>One of the following</i> 5.0MP + IR Discrete with Privacy Shutter FHD 1080p + IR Hybrid with Privacy Shutter HD 720p with Privacy Shutter</p>
<p>Keyboard 6-row, spill-resistant, optional backlight, TrackPoint and glass-like Mylar surface touchpad, 61 x 115 mm (2.40 x 4.53 inches)</p>
<p>Dimensions 317.7 x 226.9 x 17.9 mm (12.51 x 8.93 x 0.70 inches)</p>
<p>Weight Starting at 1.32 kg (2.92 lbs)</p>

Green Certifications

EPEAT Gold, ENERGY STAR 8.0, ErP Lot 6/26, TCO Certified 9.0, RoHS compliant

Other Certifications

MIL-STD-810H military tested, (Optional) Eyesafe Certified 2.0

Connectivity

I/O Ports

1x USB 3.2 Gen 1, 1x USB 3.2 Gen 1, 2x Thunderbolt 4, 1x HDMI, 1x Ethernet, 1x Headphone / microphone combo jack, 1x Smart card reader, 1x Nano-SIM card slot

WLAN + Bluetooth

One of the following

Intel Wi-Fi 6E AX211, 11ax 2x2 + BT5.1

Qualcomm Wi-Fi 6E NFA725A, 11ax 2x2 + BT5.1

WWAN

Optional

NFC

Optional

Docking

Docking support via Thunderbolt / USB-C

Security & Privacy

Fingerprint Reader
Smart Card Reader
IR Camera with Windows Hello
ThinkPad PrivacyAlert
ThinkPad PrivacyGuard screen
Discrete TPM 2.0, TCG certified
Kensington Nano Security Slot
Optional Smart card reader
Optional Touch style MOC fingerprint reader
Optional Camera privacy shutter
Optional IR camera for Windows Hello
Optional Privacy Guard with Privacy Alert
Glance by Mirametrix
Ultrasonic Human Presence Detection (IR Camera models)
Optional RFID reader

Manageability

Intel vPro Enterprise
Intel vPro Essentials
Non-vPro