

Storage SuperServer SSG-631E-E1CR16H

3U front-loading storage server with 16 hot-swap 3.5" SAS/SATA bays (SAS hardware RAID) and PCIe 5.0



More details here

Key Applications



Enterprise Server, iSCSI SAN, HPC, Data Center, Database Processing & Storage,
Corporate Database, Appliance Optimized Storage Building Blocks,

Key Features

- Dual Socket E (LGA-4677) 5th/4th Gen Intel® Xeon® Scalable processors;
- Up to 4TB 3DS ECC RDIMM, DDR5-5600MT/s(1DPC) in 16 DIMM slots;
- 2x 10 GbE onboard via Broadcom BCM57416
1x GbE Dedicated LAN for server remote management: IPMI 2.0 / KVM over LAN / Media over LAN;
- 16x 3.5"/2.5" Hot-swap SAS3/SATA3 drives, 2x Rear 2.5" SATA Slots, 2x NVMe M.2 (form factor: 2280 and 22110);
- 5x 8cm hot-swap counter-rotate redundant PWM cooling fans;
- 1200W Redundant Power Supplies Titanium Level (96%);
- HW RAID support via Broadcom® 3908;



Form Factor	3U Rackmount Enclosure: (17.2" x 5.2" x 25.5") Package: (27" x 13" x 35")
Processor	Dual Socket E (LGA-4677) 5th Gen Intel® Xeon® / 4th Gen Intel® Xeon® Scalable processors
System Memory	Slot Count: 16 DIMM slots Max Memory (1DPC): Up to 4TB 5600MT/s ECC DDR5 RDIMM
Drive Bays Configuration	Default: Total 18 bay(s) • 16 front hot-swap 3.5" SAS/SATA drive bay(s) • 2 rear hot-swap 2.5" SATA drive bay(s) M.2: 2 M.2 PCIe 4.0 x2 NVMe slot(s) (M-key 2280/22110) Peripheral Bays: 1 slim DVD bay(s) (optional)
Expansion Slots	Default • 4 PCIe 5.0 x16 (in x16) FHHL slot(s) • 2 PCIe 5.0 x8 (in x8) FH/10.5"L slot(s)
On-Board Devices	Chipset: Intel® C741 Network Connectivity: 2 RJ45 10GbE with Broadcom® BCM57416 IPMI: Support for Intelligent Platform Management Interface v.2.0 IPMI 2.0 with virtual media over LAN and KVM-over-LAN support
Input / Output	LAN: 1 RJ45 1 GbE Dedicated IPMI LAN port(s) 2 RJ45 10 GbE LAN port(s) (Broadcom® BCM57416) (IPMI shared on LAN port 1) USB: 4 USB 3.0 port(s) (rear) Video: 1 VGA port(s) (Rear) Serial: 1 COM port(s) (Rear) TPM: 1 TPM header



System Cooling	Fans: 5 Heavy Duty 8cm Fan(s)
Power Supply	1200W Redundant Titanium Level power supplies
System BIOS	BIOS Type: AMI 32MB SPI Flash EEPROM
Management	Redfish API; Supermicro Server Manager (SSM); Supermicro Power Manager (SPM); Supermicro Update Manager (SUM); SuperDoctor® 5; Super Diagnostics Offline ; KVM with dedicated LAN ; IPMI 2.0
PC Health Monitoring	CPU: Monitors for CPU Cores, Chipset Voltages, Memory 7+1 Phase-switching voltage regulator FAN: Fans with tachometer monitoring Status monitor for speed control Pulse Width Modulated (PWM) fan connectors Temperature: Monitoring for CPU and chassis environment Thermal Control for fan connectors
Dimensions and Weight	Weight: Gross Weight: 79 lbs (48 kg) Available Color: Silver
Operating Environment	RoHS Compliant Operating Temperature: 10°C ~ 35°C (50°F ~ 95°F) Non-operating Temperature: -40°C to 60°C (-40°F to 140°F) Operating Relative Humidity: 8% to 90% (Non-Condensing) Non-operating Relative Humidity: 5% to 95% (Non-Condensing)
Motherboard	Super X13DEI-T
Chassis	CSE-836BTS-R1K23BP2