



L35

2U Liquid Cooler

PRODUCT SPECIFICATIONS

Specification Version: 03/18/2024

(Specifications are subject to change without notice)

Model Number: L35

- Recommend for CPU as following
 - AMD® Socket AM2/AM3/AM4/AM5/FM1/FM2;
 - Intel® Socket FCLGA 1150, 1151, 1155, 1156, 1366;
 - Intel® Socket LGA 1700;
 - Intel® Socket FCLGA 2011(sq), 2066(sq);
- Liquid cooler for 2U server & up

Overall Specification


- Cold Plate Module with Copper base
- Space-saving lightweight Radiator
- Triple 8 cm Cooling Fans with 4-Pin PWM Function
- Stand-alone Water Pump with Powerful Flow Rate 2.9 Litter Per Minute
- 300 mm Black Pair EPDM Tube Assembled
- Mounting Accessories are included
- Shin-Etsu 7762 or Equivalent Thermal Compound Pre-Printed on Base
- Support CPU Overclocking Power Mode up to 305 Watts Heat Dissipation at 30°C ambient temperature

Cooling Fan Specification

Model Number	DB128038BX-PWMG
Dimension	80 x 80 x 38 mm
Bearing	Liquid State
Rated Voltage	12V
Rated Speed	At Duty Cycle 0~20%: 2400± 200 RPM At Duty Cycle 50%: 4800± 10% RPM At Duty Cycle 100%: 8000±10% RPM
Input Power	At Duty Cycle 0~20%: 1.20 W At Duty Cycle 50%: 5.52 W At Duty Cycle 100%: 24.72 W
Maximum Airflow	At Duty Cycle 0~20%: 35.52CFM At Duty Cycle 50%: 67.24 CFM At Duty Cycle 100%: 115.61 CFM
Rated Static Pressure	At Duty Cycle 0~20%: 1.39 mm-H2O At Duty Cycle 50%: 5.97 mm-H2O At Duty Cycle 100%: 34.06 mm-H2O
Acoustical Noise	At Duty Cycle 0~20%: 25.63 dBA

L35 | Socket LGA 115X/1366/1700/2011(Sq) | AM2/AM3/AM4/AM5/FM1/FM2

	At Duty Cycle 50%: 47.85 dBA At Duty Cycle 100%: 64.40 dBA
Lead Wire Pin Out	Pin#1- Black(-) Pin#2- Yellow(+) Pin#3- Green(Tachometer/ Signal Output) Pin#4- Blue (PWM)



Pin#1- Ground (-)


Pin#2- Power (+)

Pin#3- Signal (Tachometer Output)

Pin#4- PWM Control


Performance Chart: Liquid Cooler L35 Thermal Resistance Thermal Resistance vs. Fan Speed @ PWM Duty Cycle

LGA 1700:



L35 | Socket LGA 115X/1366/1700/2011(Sq) | AM2/AM3/AM4/AM5/FM1/FM2

AM5:




Publication History:

02/13/2023: Initial Release

03/18/2024: V1.0 Pump Location Change

(Specifications are subject to change without notice)



REV#	DESCRIPTION	CHECKER	DATE
0.0	INITIAL RELEASE	JUN	2/10/23
1.0	PUMP LOCATION CHANGE	JUN	3/18/24

	NAME	DATE
DRAWN BY	JUN	3/18/2024
CHECKED BY	JUN	3/18/2024
ENG.APPROVED		
MFG.APPROVED		

CONFIDENTIAL DOCUMENT
THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO DYNATRON CORPORATION AND DYNAEON INDUSTRIAL CO., LTD. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DRAWING IS EXPRESSLY PROHIBITED EXCEPT AS DYNATRON CORPORATION AND DYNAEON INDUSTRIAL CO., LTD. MAY OTHERWISE AGREE TO IN WRITING.



DYNATRON CORPORATION

TITLE:

LIQUID COOLER L35
OVERALL DIMENSION DRAWING

VIEW		DWG. No:	REV.
UNITS	MM	DYN-BD-L35	1.0



CONFIDENTIAL DOCUMENT

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO DYNATRON CORPORATION AND DYNAEON INDUSTRIAL CO., LTD. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DRAWING IS EXPRESSLY PROHIBITED EXCEPT AS DYNATRON CORPORATION AND DYNAEON INDUSTRIAL CO., LTD. MAY OTHERWISE AGREE TO IN WRITING.

REV#	DESCRIPTION	CHECKER	DATE
0.0	INITIAL RELEASE	JUN	02/10/24
1.0	PUMP LOCATION CHANGE	JUN	03/18/24

B

B



11	RADIATOR	ALUMINUM ALLOY	1
10	FAN, DF128038BX-PWM	PLASTIC	3
9	SCREW, FANS	STEEL	12
8	PUMP, PUMP-60	PLASTIC	1
7	HOSE, 300MM	EPDM	2
6	SCREW, RETENTION (INCLUD AM4/5, INTEL LGA1700/115X, LGA2011)	STEEL	12
5	AMD RETENTION BRACKET	STEEL	1
4	INTEL RETENTION BRACKET	STEEL	1
3	COLD PLATE	PLASTIC LID, CU BASE	1
2	THERMAL GREASE	SHIN-ETSU X23-8079-2	N/A
1	INTEL BACKPLATE	STEEL	1
ITEM #	DESCRIPTION	MATERIAL	QTY.

	DATE	NAME	 DYNATRON CORPORATION	
DRAWN	3/18/2024	JUN	TITLE: 2U LIQUID COOLER L35 BOM & exploded Assembly Drawing	
CHECKED	3/18/2024	JUN		
ENG.APPR.				
MFG.APPR.				
COMMENTS:			DWG. NO. DNY-EP-L35	REV 1.0

NOTES:
THE FIGURE IS FOR REFERENCE ONLY, AND NOT FOR SCALE