

GHDSW8K4

4-Port 8K UltraHD HDMI® Switch



- Connect up to four 8K sources to one HDMI enabled HDTV or projector
- Supports maximum resolution of 7680 x 4320 @60Hz (4:2:0 color sampling); 7680 x 4320 @30Hz (4:4:4 color sampling)
- Configures video resolution automatically according to the maximum output of each monitor with the capability to output 4K resolution to one monitor while output 1080p to another monitor (EDID function)
- High bandwidth of up to 48 Gbps with no latency
- HDMI 2.1 and HDCP 2.2 Compliant
- Supports HDR+ and full 3D pass-through

8K Ultra High Definition (UHD) Video Support

IOGEAR's 4-Port HDMI Switch supports UHD 8K, the latest digital format for high definition displays. This switch is capable of HD resolutions up to 7680x4320 @60Hz (4:2:0), 7680x4320 @30Hz (4:4:4) or 4K @120Hz.

Supports HDR+ and High Quality Audio Formats

Display your HDR content on any 8K capable HDMI display using IOGEAR's 4-Port 8K HDMI switch. Enjoy not only a wide range of colors, and detail. But enjoy high quality audio formats such as DSD (Direct Stream Digital) and HBR audio (High Bit Rate) such as Dolby True HD and DTS-HD.

Easily switch between four different HDMI sources

Switch between different devices from the comfort of your couch using the included IR remote. With the built in IR extension port, connect an IR extension cable (not included) to place the 4-port switch out of sight to keep your entertainment center neat and tidy.

- Connect up to four 8K sources to one HDMI enabled HDTV or projector
- Supports maximum resolution of 7680 x 4320 @60Hz (4:2:0 color sampling); 7680 x 4320 @30Hz (4:4:4 color sampling)
- Configures video resolution automatically according to the maximum output of each monitor with the capability to output 4K resolution to one monitor while output 1080p to another monitor (EDID function)
- High bandwidth of up to 48 Gbps with no latency
- HDMI 2.1 and HDCP 2.2 Compliant
- Supports HDR+ and full 3D pass-through
- Compatible with Standard audio, DSD (Direct Stream Digital) and HBR audio (High Bit Rate) such as Dolby True HD and DTS-HD
- Switch between devices via front-panel pushbutton, or IR remote.
- Front-panel LEDs for port and power status
- Low power consumption
- Plug-n-Play



Requirements

Display:

- 1x 8K capable HDMI Port
- 1x 48Gbps HDMI cable 2 meters or shorter

Media Source:

- 1x 8K Capable HDMI Port
- 1x 48Gbps HDMI cable 2 meters or shorter

Switch:

- 1x USB-C Cable to Power Source (5V/1A)
- 1x IR Extension Cable (optional)

Package Contents

1x GHDSW8K4 4-Port 8K UltraHD HDMI Switch

1x USB Power Cable

1x IR Remote Control Unit

1x Quick Start Guide

1x Warranty Card

Specifications

Function	GHDSW8K4	Dimensions	GHDSW8K4
Video connections		Unit Dimensions	
Input	4x HDMI 2.1	Height	.75" (1.9cm)
Output	1x HDMI 2.1	Length	2.625" (6.6cm)
Connectors		Inner Pack	
Video Input	4x Female HDMI Type A 19 Pin	Height	6.7" (17cm)
Video Output	1x Female HDMI Type A 19 Pin	Width	6.5" (16.5cm)
USB-C	1x USB-C for Power	Depth	6.7" (17cm)
LEDs		Inner Pack Qty.	
Input	4	6	
Output	1	Unit Package Dimensions	
Video Resolution		Height	
Up to 7680x4320@60Hz		6.3" (16cm)	
Color Depth		Width	
8-bit / 10-bit / 12-bit		5.1" (13cm)	
Data Rate		Depth	
48Gbps		1" (2.5cm)	
Environment		Master Carton	
Operation Temperature	-10 ~ +55°C	Height	13.75" (35cm)
Storage Temperature	-20 ~ +70°C	Width	6.9" (17.5cm)
Power		Depth	7.5" (19cm)
Amps	1 Amp	Master Carton Qty.	12
Voltage	DC5V	Weight	
Housing		Master Carton Wt.	
Case	Metal	8.8lbs (4Kg)	
		Inner Pack Wt.	
		4lbs (1.8Kg)	
		Unit Pack Wt.	
		.65lb (.29Kg)	
		Unit Wt.	
		.45lbs (.2Kg)	