



SLOT IN PCS

VPCF5-W55-G1

Key Features

- Windows 11 Pro
- Ideal Integrated Solution for ViewBoard® Interactive Displays & Presentation Displays
- Powerful Intel® 11th Core Processors embedded TPM2.0
- Improved System Stability, Security, & Thermal Control



Product Description

Seize the power to get more done when you sync your ViewBoard® interactive displays and Presentation Displays with the ViewSonic VPCF5-W55-G1 slot-in PC. Integrated with exceptional performance from Intel® processors, 16GB DDR4 memory, and 512GB of SSD storage, the experience enhances computing performance to breeze through complex classes and collaborations. Plug into pure productivity with dual-band WiFi, Bluetooth 5.2, and a range of ports, including 4K HDMI, 5K DP, USB 3.1, and Gigabit LAN RJ45 for faster workflows.

Visit Us

www.viewsonic.com

SOFTWARE

Operating System: Windows 11 pro

CORE

CPU: Intel® Tiger Lake Mobile Processor
Intel Gen11th core i5
CPU or later Gen. CPU

Graphics: Integrated Intel® Iris Xe Graphics (96EU)
Total Available Graphics Memory:
32GB
Max Resolution up to 7680x4320@60Hz (DP)

MEMORY

Type: DDR4

Capacity: 16GB

STORAGE

Dimension: M.2 SSD

Capacity: 512GB

Interface: PCIE

INPUT

MIC(Microphone): MIC-In&Line-Out two in one connector

OPS Standard: x1(USB type A 3.1X2,
USB type C 3.1 X1 (DATA ONLY), USB 2.0 x1)

OUTPUT

HDMI: x1 (Max 3840x2160@30Hz)

Audio: MIC-In&Line-Out two in one connector

LAN

RJ45: x1 (10M/100M/1000M)

WIRELESS / BLUETOOTH

Wireless / Bluetooth: Intel® AX101NGW
WIFI 6 802.11 ax + BT5.2

USB

Type A: USB 3.1 x 2 / USB 2.0 x 1

Type C: USB 3.1 Gen2 *1 (Data Only)

BUNDLE SOFTWARE

Bundle Software: myViewBoard Whiteboard,
Adobe Reader,
FinchGuard(Watchdog)/Winflash

POWER

Voltage: DC 12-19V/8A Max

Consumption: Max 90 W

OPERATING CONDITIONS

Temperature (° C): 0°C ~ 40°C(working)

Humidity: 10% ~ 90% @ 40°C
Non-condensing(working)

DIMENSIONS (W X H X D)

REGULATIONS

REGULATIONS:

CE EMC / LVD / CE
RED / RoHS /REACH /
WEEE / CB2018

PACKAGE CONTENTS

PACKAGE CONTENTS:

1. Quick Start Guide(With Compliance Statement)
2. Screws x 2
3. Antenna x 2

Physical (inch / mm): 7.87 x 4.68 x 1.18 in /
200 x 119 x 30 mm

Packaging (inch / mm): 10.23xx 7.87 x 3.15 in /
260 x 200 x 80 mm

WEIGHT

Net (lb / kg): 1.54 lb / 0.7 kg

Gross (lb / kg): 2.65 lb / 1.2 kg