


QNAP

TS-855X

Powered by Intel Atom® C5125 8-core
2.8GHz processor, support up to 128GB
memory, hybrid storage architecture suitable
for small and medium-sized enterprises
backup and monitoring applications



Powered by server-grade Intel 8-core CPU strong performance and expandability

8

Core

Intel 8-core CPU

Server-grade Intel Atom® C5125 2.8GHz 8-core processor provides powerful NAS performance



1 x 10GBASE-T & 2 x 2.5GbE


Integrated 10GBASE-T & dual 2.5 GbE network ports, provide smooth data transmission experience



M.2 SSD

Dual M.2 PCIe SSD slots

Two PCIe Gen3 x4 M.2 2280 slots for optimal configuration of NVMe SSD and 3.5" SATA HDD



2 x PCIe Gen3 x4 slots

Provide a variety of expansions including 10G/25GbE network card, M.2, HBA and other expansion cards

128 GB



Maximum 128 GB memory

Pre-installed 8 GB non-ECC memory with 4 x DDR4 UDIMM slots, optionally support highly reliable ECC memory modules



Hybrid architecture

6 x 3.5"/2.5" SATA HDD + 2 x 2.5" SATA SSD provide a hybrid NAS with high cost performance ratio

Choose between QTS and ZFS based QuTS hero

TS-855X is shipped with the QTS operating system, which has powerful data transmission performance and more efficient memory usage, and enjoys the Qtier automatic tiered storage function. You can also change to the QuTS hero operating system according to your needs

| | QuTS hero | QTS |
|-----------------------------------------------------------------|--------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Filesystem | ZFS | Ext4 |
| SSD cache | Read Cache | Read/Write Cache Read Cache Write Cache |
| Inline Compression | Yes (LZ4 compression, ideal for RAW files and document files) | No |
| Inline Deduplication | Yes (At least 16 GB RAM required) | No |
| HBS with QuDedup for Remote Backup | Yes | Yes |
| Power Failure Protection (Software) | ZIL Copy-on-Write | No |
| Permission Management | Rich ACL (14 types) | POSIX ACLs (3 types) + certain special permissions |
| Capacity Expansion | Upgrade RAID capacity Change higher capacity disk drives Attach expansion enclosures/JBODs | Add a disk drive to a RAID group Upgrade RAID capacity Change higher capacity disk drives Attach expansion enclosures/JBODs |
| Data Security | Better (Self-Healing & Copy-on-Write) | Standard |
| Recommendation SSD Configuration for Video Editing Applications | Use SSD Pools Note: Set the block size 128K when creating Folders/LUNs | Editing (from original/RAW files): Use SSD Pools Post production: Enable Read/Write cache Note: Set the block size to 32K or 64K when creating Volumes, and choose "All I/O" for cache mode. |

Support Intel QAT and SR-IOV to increase efficiency

SR-IOV

SR-IOV Network I/O Virtualization


Install a PCIe network card that supports SR-IOV technology, and directly allocate the bandwidth resources of the physical network card to the virtual machine.

QAT

Intel® QAT hardware acceleration

Supports the Intel® QuickAssist hardware acceleration engine (Intel® QAT), which accelerates data compression/decompression, and can greatly improve the performance of encryption and decryption transmission operations





Hardware


TS-855X | 8-bay Hybrid HDD/SSD NAS

TS-855X front view

2 x 2.5" SATA
6Gb/s SSD tray

HDD port LEDs

Lockable tray with 2
keys provided




LCD panel
and buttons

6 x 3.5"/ 2.5" SATA
6Gb/s HDD/SSD tray

Power button

1 x USB 3.2 Gen 1
& OTC button

TS-855X rear view



Internal design

4 x DDR4
UDIMM slots

2 x M.2 2280 PCIe
Gen3 x4 slots

1 x PCIe Gen3 x4 slot


1 x PCIe Gen3 x4 slot



Support ECC Memory (Error Correcting Code)

**Reliable memory and
avoiding data corruption**


ECC



TS-855X supports ECC memory, automatically detecting and timely correcting single-bit errors

System supports up to 128GB (4 x 32GB) memory

- The NAS is pre-installed with a 8GB non-ECC UDIMM memory by default.
- ECC memory and non-ECC memory modules cannot be installed together




Features 10GBASE-T & 2.5GbE connectivity

1 x 10GBASE-T + 2 x 2.5GbE ports


Sufficient 10GBASE-T & Dual 2.5 GbE network ports, provide smooth data transmission experience

1 x 10GBASE-T

2 x 2.5GbE



Compared to the previous model

| | TS-855X  | TS-h886 | TS-673A |
|-----------|---------------------------------------------------------------------------------------------|---------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------|
| SKU | TS-855X-8G | TS-h886-D1602-8G | TS-673A-8G |
| CPU | Intel ® Atom® C5125 8-core processor, 2.8GHz | Intel® Xeon® D-1602 2-core/4-thread processor, up to 3.2 GHz | AMD Ryzen™ Embedded V1500B 4-core/8-thread 2.2 GHz processor |
| Drive bay | 6 x 3.5-inch SATA 6Gb/s + 2 x 2.5-inch SATA 6Gb/s | | 6 x 3.5-inch SATA 6Gb/s |
| O.S. | QTS (Pre-installed) / QuTS hero | QuTS hero (Pre-installed) / QTS | QTS (Pre-installed) / QuTS hero |
| Memory | 8 GB UDIMM DDR4 (1 x 8 GB) Max 128GB (Support ECC) | 8 GB UDIMM DDR4 ECC (2 x 4 GB) Max 128 GB (Support ECC) | 8 GB SODIMM DDR4 (1 x 8GB) Max 64GB (Support ECC) |
| LAN | 1 x 10GBASE-T 2 x 2.5 Gigabit Ethernet Port (2.5G/1G/100M) | 4 x 2.5 Gigabit Ethernet Port (2.5G/1G/100M) | 2 x 2.5GbE (2.5G/1G/100M) |
| PCIe Slot | 2 x PCIe Gen3 x4 | 2 x PCIe Gen3 x8 | 2 x PCIe Gen3 x4 |
| M.2 | 2 x M.2 2280 PCIe Gen 3 x4 | 2 x M.2 22110/2280 NVMe PCIe Gen3 x4 | 2 x M.2 2280 PCIe Gen3 x1 |
| I/O | <ul style="list-style-type: none"> 1 x USB 2.0 3 x USB 3.2 Gen 1 | <ul style="list-style-type: none"> 3 x USB 3.2 Gen 1 | <ul style="list-style-type: none"> 3 x USB 3.2 Gen 2 Type-A 1 x USB 3.2 Gen 1 Type-C |

Live Demo

Hardware introduction and RAM expansion





QTS 5.1.0

Boosted performance,
flexible management, and
higher security

SMB Multichannel for doubled speed

A SMB 3 client automatically establishes multiple connections to the SMB server for a single SMB session. The connection also provides bandwidth aggregation and network fault tolerance.

Requirement: Both NAS and Client device support SMB 3.0 protocol. NAS: QTS 5.1.0 (or later), QuTS hero h5.1.0 (or later). Clients: Windows Server 2012 (or later), macOS Big Sur 11.3.1 (or later)

Without Multichannel




With Multichannel




Built in 10GBASE-T and dual 2.5 GbE ports bring essential performance out of the box

2 x 2.5GbE Windows File Transfer



1 x 10GbE SMB Sequential Throughput (1MB)



Test environment:

NAS: TS-855X

OS : QTS 5.0.1


Volume type: RAID 5; 8 x Samsung 860 EVO 1TB

Client PC: Windows Server 2016, Intel i7-6700 3.4GHz, 64GB RAM,


IOmeter : RAM*4, 30-sec ramp up time, 3-min seq. run time, 1 worker, 32-outstanding

Dual PCIe Gen3 slots for 25GbE network expansion


1 x 25GbE SMB Sequential Throughput (1MB)



2x 25GbE SMB Sequential Throughput (1MB)



Test environment :
NAS: TS-855X
OS : QTS 5.0.1
Volume type: RAID 5; 8 x Samsung 860 EVO 1TB
Client PC: Windows Server 2016, Intel i7-6700 3.4GHz, 64GB RAM,
IOMeter : RAM*4, 30-sec ramp up time, 3-min seq. run time, 1 worker, 32-outstanding



QXG-25G2SF-CX6
2 x 25GbE SFP28 NIC

Certified for enterprises & virtualization, 8-core NAS for data storage & surveillance

Intel® 8-Core server-grade CPU

High performance processor suitable for virtual machines and multitasking



Virtualization station



Container station

6 x SATA HDD + 2 x SATA SSD hybrid storage

Suitable for multi-device file backup and as a surveillance host



QVR Elite



Qsync



HBS3



HDD+SSD




Certified for virtualization

Microsoft Hyper-V / Citrix ready /
VMware ready / Veeam ready


File Station is the ultimate and user-friendly web & iOS/Android-based file explorer

File Station is a file management tool in QTS that enables QNAP NAS users to intuitively access shared folder content through web browsers.



Local
NAS

Remote
NAS
Cloud
Storage



Easily make NAS your team collaboration portal with File Station



Edit with Office Online




View in Google Docs



Open with Google Chrome
Extension

| | | | |
|--------------------------|------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|
| Requirement | CloudLink needs to be enabled | CloudLink needs to be enabled | Use Chrome with extension "Office Editing for Docs, Sheets & Slides" to open |
| Supported formats | .docx, .pptx, .xlsx | .doc, .ppt, .xls .docx, .pptx, .xlsx | .doc, .ppt, .xls .docx, .pptx, .xlsx |
| Capabilities | <ul style="list-style-type: none">•File collaboration•Auto save to NAS in real time | <ul style="list-style-type: none">•Document preview•Convert to Google docs for editing & saving in your Google Drive | <ul style="list-style-type: none">•Document preview•Convert to Google docs for editing & saving in your Google Drive |





Save to NAS in real time




Multi-user online editing

Qsync 5.0 – Cross-device file sync for individuals and teams

Qsync enables efficient file synchronization between a QNAP NAS and linked devices such as computers, laptops, and mobile devices. With Qsync, you can easily access data across all your devices and share it among your team members.



If you own many devices, any file changed on one device will be automatically synchronized with the others.



For team works, any file changed will be automatically distributed to your teams' devices, accelerating and streamlining your workflows.

DA Drive Analyzer disk failure prediction



Each NAS can perform one disk prediction for free, and you can also pay to subscribe to enhance protection for all disks.

DA Drive Analyzer

Overview

Drive Prediction

Email Alerts

Additional Information

Prediction History

Overview

DA Drive Analyzer

Drive enclosures: 2, Drives: 21 (HDD: 19; SSD: 0; NVMe drives: 2)

Faulty

5

Defective drive detected.
Replace the drive.

Critical

4

90% risk of failure
Replace the drive as soon as possible.

Warning

9

70% risk of failure
Start planning for a drive replacement.

Normal

1

Drive(s) are functioning normally.

Data Analysis in Progress

0

There are no new drives in the cloud AI data analysis stage.

Important: Review Drive Status

Drives: 18 (Faulty: 5, Critical: 4, Warning: 9)

| Drive (Drive Enclosure) | Severity Level | Drive Manufacturer | Drive Capacity | |
|-------------------------|----------------|--------------------|----------------|--|
| Disk 1 (NAS Host) | Warning | ST320LM001 | 298.09 GB | |
| Disk 2 (NAS Host) | Warning | WDC | 298.09 GB | |
| Disk 4 (NAS Host) | Faulty | ST320LM001 | 298.09 GB | |
| Disk 7 (NAS Host) | Warning | TOSHIBA | 298.09 GB | |
| Disk 8 (NAS Host) | Critical | WDC | 298.09 GB | |
| Disk 9 (NAS Host) | Faulty | TOSHIBA | 298.09 GB | |

License

License plan:
BETA

Valid until:
2022-02-18

Disk health analysis and failure prediction

DA Drive Analyzer integrated ULINK AI predict technology can warn you before disk failure, help you protect valuable data

All-in-one solution for hosting virtual machines and containerized apps




Virtualization Station

Virtualization Station allows you to create virtual machines (VM) on Turbo NAS, supporting Windows®、Linux® operating systems.



Container Station

Experience LXD and Docker® lightweight virtualization technologies, download apps from the Docker Hub Registry®, import/export containers, and create abundant microservices.




Data security




QuFirewall

You can allow/deny IP addresses and regions to prevent unauthorized access and brute force attacks for safeguarding data and service security.



Malware Remover

Protect your NAS data against malware attacks



Snapshots Help You Fight with Ransomware Threats

TS-855X supports Snapshot, like taking a photo - within seconds the complete status of your NAS system and data is recorded.

QTS supports up to **1,024** snapshots, QuTS hero supports up to **65,536** snapshots

Mitigate the growing threat of ransomware

Step 1


Regularly update, and use Malware Remover

Step 2

Routinely back up to your NAS, and create multi-version snapshots

Step 3

Back up snapshots to another QNAP NAS



Your NAS is also a surveillance server



QVR Pro

- 6,000+ Compatible cameras
- 8 embedded monitoring channels
- Expand to 36 channels by purchasing QVR Pro licenses
- View USB camera images through QUSBCam2




QVR Elite

The flexible subscription QVR Elite can be expanded to a maximum of 54 channels by purchasing licenses



QVR Pro Client



- iOS & Android mobile devices
- Support cross-platform : Windows, Mac, Ubuntu
- Use HDMI output and USB keyboard and mouse to control the NAS through installing Graphic card

Compatible with a huge amount of camera models

over **190 brands**

 **GeoVision**

 **VIVOTEK**
BUILT WITH RELIABILITY

Panasonic

AXIS
COMMUNICATION

MOBOTIX

Canon

HIKVISION

ahua
TECHNOLOGY

Honeywell

Brickcom

over **6000 Models**



ONVIF Profile Supported



**RTSP Stream
Input / Output**

**RTMP Stream
Input**

Supports up to 24 more HDDs with two JBOD units, add nearly 500TB (24 x 22TB) of storage space

USB



TR-002



TR-004



TL-D800C



TR-004U



TL-R1200C-RP

Maximum of JBOD / RAID expansion enclosures

| | |
|--------------|---|
| TR-002 | 2 |
| TR-004 | 2 |
| TR-004U | 2 |
| TL-D800C | 1 |
| TL-R1200C-RP | 1 |
| TL-D400S | 2 |
| TL-D800S | 2 |
| TL-D1600S | 2 |
| TL-R400S | 2 |
| TL-R1200S-RP | 2 |

SATA



TL-D400S



TL-D800S



TL-D1600S



TL-R400S



TL-R1200S-RP

Note: These expansion units can only be used as an individual storage pool or volume on the NAS. Their storage pool or volume cannot be combined into the connected NAS. NAS applications cannot be installed on the them.

QNAP 16/32Gb Fibre Channel cards for a reliable, scalable and budget-friendly FC SAN storage solution

10GbE NIC



QXG-10G2TB

2 x RJ45



QXG-10G1T

1 x RJ45

25GbE NIC



QXG-25G2SF-CX6
(Support 25GbE SFP28,
10GbE SFP+)

2 x SFP28 25Gb/s

5GbE NIC




QXG-5G1T-111C

QXG-5G2T-111C

QXG-5G4T-111C

1/2/4 x RJ45



QXP-16G2FC : Dual ports 16Gbps

QXP-32G2FC : Dual ports 32Gbps

(FC HBA with 16/32Gb FC transceivers)

For more, please check :
<https://www.qnap.com/go/compatibility/>

3-year standard warranty covering hardware repair and support services

TS-855X is backed by a 3-year warranty at no additional cost.

You can also purchase a warranty extension that extends your warranty coverage up to 5 years total (2-year extended warranty P/N: EXTW-BROWN-2Y).

SKU : TS-855X

Intel Atom® C5125 8-core CPU 2.8 GHz, , 8 GB DDR4 (1 x 8 GB)



Support
5/10/25GbE
NICs



Support
multiple
JBOD



C5125 2.8 GHz
8-core
CPU

10
Direct
connection
2.5GbE

Hybrid storage : SATA HDD + SSD



2.5"
SSD
x2



3.5"
HDD
x6

Supports both

QTS

QuTS hero
edition

intel®
Quick Assist
Technology



USB 3.2
Gen1
(5Gbps) &
One-Touch-
Copy

TS-855X



1 x 10GBASE-T +
2 x 2.5GbE

Availability at least until

2027

128GB ECC
Memory



QVR Elite
Surveillance
solution

2

PCIe Gen3 x4
slots



2 x M.2 2280

PCIe Gen3 x4

SR-IOV



Up to 5 years
warranty

QNAP

TS-855X

Powered by Intel Atom® C5125 8-core 2.8GHz processor, support up to 128GB memory, hybrid storage architecture suitable for small and medium-sized enterprises backup and monitoring applications

