




AR09-1700

Superior 2U server thermal solution for Intel LGA1700

- 3 x Ø6mm heat-pipes and aluminum fins for excellent heat conducting efficiency
- Heat-pipe direct contact (HDC) technology
- Includes spring screw mounting bracket and backplate
- 60mm dual ball bearing PWM fan
- Compatible with Intel LGA1700 socket

Product Specifications

Model No.

SST-AR09-1700

Material

Copper heat pipes with aluminum fins

Application

Intel LGA1700

Fan

Dimension	60mm (W) x 25mm (H) x 60mm (D)
Speed	1200 ~ 5000 RPM
Noise level	18.02~42.5 dBA
Rated Voltage	12V
Rated Current	0.35A
Max airflow	27.9 CFM
Max air pressure	4.83mmH ₂ O
Connector	4 Pin PWM
Bearing	Dual ball bearing
MTTF	70,000 hours

Dimension

88mm (W) x 66mm (H) x 88mm (D)
3.46" (W) x 2.6" (H) x 3.46" (D)

Net weight

323g

