

# Product datasheet

Specifications



## Battery Breaker Box, 630A, one circuit breaker for Easy UPS 3M/3L

E3M BBB100K200H

### Overview

Presentation	Wall mounted battery breaker box for use with third party battery solutions.
Lead Time	Usually Ships within 6 Weeks

### Main

Battery Type	VRLA
Provided Equipment	Installation guide

### Batteries & Runtime

Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Device Mounting	Enclosed battery cabinet
Battery Power In VAh	0 VAh

### Physical

Height	80 cm
Width	50 cm
Depth	28 cm
Net Weight	38 kg
Mounting Mode	Not rack-mountable

### Environmental

Ambient Air Temperature For Operation	0...40 °C
Operating Altitude	0...4921 ft
Relative Humidity	0...95 % non-condensing

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	120 cm
Package 1 Width	53 cm
Package 1 Length	82.5 cm
Package 1 Weight	65 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

✔ Toxic Heavy Metal Free

---

✔ Mercury Free

---

✔ Rohs Exemption Information [Yes](#)

---

**Reach Regulation** [REACH Declaration](#)

---

**Eu Rohs Directive** Compliant with Exemptions

---

**China Rohs Regulation** [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information

---