

Product datasheet

Specifications



Power Module, 20 kW at 400/480V, 10 kW at 208V, for Galaxy V Ranges

GVPM20KD

Overview

Presentation A 20kW (400V or 480V) / 10kW (208V) power module compatible with the Galaxy VS 3-phase UPS. When the power module is installed, the UPS automatically detects the change. Available as a power module replacement, or for increased capacity for the Scalable Galaxy VS models.

Lead time Usually Ships within 2 Weeks

Main

Other Input Voltage 208 V
400 V
480 V

Other Output Voltage 208 V
400 V
480 V

Rated power in W 20000 W

Rated power in VA 20000 VA

Physical

Height 130 mm

Width 432 mm

Depth 645 mm

Net weight 25 kg

Output

Maximum configurable power in W 20000 W

Environmental

Ambient air temperature for operation 0...50 °C

Relative humidity 0...95 % non-condensing

Operating altitude 0...3000 m

Ambient air temperature for storage -25...55 °C

Storage Relative Humidity 10...80 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	330 mm
Package 1 Width	780 mm
Package 1 Length	580 mm
Package 1 Weight	48 kg

Offer Sustainability

EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Recommended replacement(s)