



Poly Rove Single/Dual Cell DECT 1920-1930 MHz B2 Base Station and 30 Phone Handset Kit (84H81AA)



Overview

Reliable coverage, all around

Keep the conversation going whenever, wherever in the office with the Poly Rove 30 wireless DECT™ IP phone solution. It stays cleaner for longer with Microban® antimicrobial product protection and has the flexibility to scale as you grow.

Ruggedized protection

Keep your onsite employees productive with handsets that include ruggedized and Microban® antimicrobial protection built to withstand all that life throws at it. Drops, dust, water – these pro-grade handsets will go the distance [1,2,3].

You grow, we scale

You don't have to worry about outgrowing your communication solution or feel held back by its options. Poly Rove 30 wireless DECT™ IP phone solution has flexibility to scale with handsets, bases, and repeaters as your organization grows.

Features

Durable IP65-rated handsets

Maintain confidence that your devices will last and that your investment is protected: The ruggedized handsets are drop proof and IP65 dust-tight and water resistant.^[3]

Privacy is ensured

Conversations are safe and secure with DECT™ wireless security. And it doesn't stop there - maintain DECT™ encryption even when you add a base or repeater to your solution.

Grab a Poly headset and go

Communicate hands-free with a Poly wired headset using the dedicated 3.5 mm connection. Perfect for users who feel more comfortable wearing a headset.^[4]

Microban® protection

Rest assured that your devices, enhanced with Microban® antimicrobial product protection, stay cleaner, fresher and more durable for longer. Protection that lasts the life of the product, actively reducing the growth of bacteria.^[1,2]

Long-lasting battery power

Enable employees on the move to communicate more effectively, respond faster to requests and alerts, and be more productive with up to 18 hours of talk time and up to 300 hours of standby time.

Single/Dual Cell Base Stations

Mid-level DECT™ base station for small to medium deployments needing between 5,000 sq ft (single cell) – up to 15,000 sq ft (dual cell) of coverage. Compatible with all Poly Rove handsets, and up to 3 Rove R8 Repeaters.

[1] Microban antimicrobial product protection is a built-in active ingredient that enables products to resist the growth of microbes such as bacteria, mold, and mildew. Microban protection helps products stay cleaner, fresher, and last longer than products with untreated surfaces.

[2] Microban antimicrobial product protection available for the Poly Rove 30 handset models.

[3] Poly Rove 30 ruggedized handsets are drop proof (up to 6.6 ft/2 m) and IP65 dust-tight and water resistant.

[4] Poly wired headset sold separately.

Additional specifications

Audio	DTMF tone generation (RFC 2833 and in-band)
Audio codecs	G.165, 168 echo cancellation
Battery life	Up to 18 hours (talk time); Up to 300 hours (standby time)
Battery type	Rechargeable Li-ion
Cartons per layer	4
Cartons per pallet	32
Certifications and compliances	UL 62368-1
Certified collaboration software	Zoom
Color	Black
Country of origin	Made in China
DECT frequency	1880 to 1900 MHz
Display features	Adjustable font size selection (regular, medium, large)
Display size (diagonal)	6.1 cm (2.4")
Display size (diagonal)	2.4"
ECCN	5A991
Energy star certified	ENERGY STAR® certified
HTS code	8517140080
Headset and handset compatibility	Compliant with ADA Section 508 Subpart B 1194.23 (all)
Headset ports	1 3.5 mm headset jack
Management Software	Polycom Device Management Service for Service Providers (PDMS-SP) Cloud Management
Manufacturer Warranty	Poly standard one-year limited warranty
Minimum dimensions (W x D x H)	56.9 x 146.3 x 36.8 mm
Minimum dimensions (W x D x H)	2.2 x 5.8 x 1.5 in
Minimum order quantity	10
Native resolution	240 x 320
Network protocols, supported	Manual or dynamic host configuration protocol (DHCP) network setup; IPv4
Onscreen controls	Three multi-colored mute indicators; Three sets of capacitive touch volume and mute buttons
Operating humidity range	5 to 95%
Operating temperature range	-10 to 55°C
Operating temperature range	14 to 131°F
Package dimensions (W x D x H)	7.48 x 8.26 x 2.16 in

Package dimensions (W x D x H)	239 x 141 x 44 mm
Package weight	300 g
Package weight	0.66 lb
Pallet (layers)	8
Pallet dimensions	40 x 48 x 58.66 in
Pallet dimensions (W x D x H)	101.6 x 121.9 x 149 cm
Pallet weight	787.05 lb
Pallet weight	357 kg
Panel technology	Color TFT LCD
Power	External universal AC adapter: 5V 1A DC
Products per pallet	320
Products per pallet layer	40
Security management	DECT™ security certified
Special features	Unicode UTF-8 character support; Push-to-talk
Storage temperature range	-40 to 70°C
Storage temperature range	-40 to 158°F
Telephony and call handling features	Up to 10 simultaneous calls (single cell)
UNSPSC code	43191511
UPC number	(ABA) 197497527773; (ABB) 197497527780; (ABG) 197497527803; (ABU) 197497527834
VoIP features	Up to Twenty (20) service subscription profile assignments (SP 1 – 20)
Weight	0.37 lb
Weight	168 g
What's in the box	Safety information sheet; Handset; Quick start guide; AC power adapter; Charging cradle; Spare battery; Base station; Ethernet cable; Belt clip
Wireless range	Up to 50 m indoor
Wireless range (imperial)	Up to 165 ft indoor

Services

Poly Services

★ : Recommended

Poly Support Services

3 Year Poly+ Rove 30 and B2 S/D Cell DECT Base Station Kit	P86850312 ★
1 Year Partner Poly+ Rove 30 B2 Single and Dual Cell DECT Base Station Kit	P86850160
1 Year Poly Elite Rove 30 and B2 S/D Cell DECT Base Station Kit	E86850112
1 Year Poly+ Rove 30 and B2 S/D Cell DECT Base Station Kit	P86850112
3 Year Partner Poly+ Rove 30 B2 Single and Dual Cell DECT Base Station Kit	P86850362
7 Year HWR Rove 30+B2 Single/Dual Cell DECT Base Station Kit NBD with Poly DaaS Svc	D7YLLT034

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Apr 22, 2024 7:16 AM UTC+0000