

Overview


HPE FlexFabric 20Gb 2-port 630M Adapter

Recommended SKU - This adapter is a recommended option that has been selected by HPE experts to provide the right technology for a range of workloads and market segments offering the best combination of performance, value and availability.

The HPE FlexFabric 630M is a 2-port 20GbE Mezzanine adapter, featuring the first generation of 20Gb Ethernet offering in a single chip solution on a mezzanine form factor that further reduces power requirements for 2 ports of 20Gb Ethernet. It is designed for use with HPE BladeSystem c-Class blade server platforms' type A and Type B mezzanine slots.

It provides full duplex high performance Ethernet connectivity with support for HPE Virtual Connect Flex-20 blade interconnect technology, allowing each 20GbE port to be divided into four physical NICs and optimize bandwidth management for virtualized servers. The HPE FlexFabric 630M adapter, in conjunction with HPE Virtual Connect FlexFabric technology, helps to extend the benefits of virtualization beyond the server and into the rest of the infrastructure.

The HPE 630M supports enterprise class features such as VLAN tagging, adaptive interrupt coalescing, MSI-X, NIC teaming (bonding), Tunnel Offload (NVGRE, VxLAN),# Receive Side Scaling (RSS), jumbo frames and PXE boot. It also supports virtualization features such as SR-IOV, Network Partitioning (NPAR), VMware NetQueue and Microsoft VMQ.



HPE FlexFabric 20Gb 2-port 630M Adapter

Platform Information

Models

HPE FlexFabric 20Gb 2-port 630M Adapter

700076-B21

NOTE: This adapter requires a minimum of 2GB of server memory.

NOTE: This adapter supports linking at 10Gb/s when not connected to a Flex-20 device.

Kit Contents

- HPE FlexFabric 20Gb 2P 630M Adapter
- Quick install card
- Product warranty statement

Compatibility - Supported Servers

- HPE ProLiant BL460c Gen9 Server
- HPE ProLiant BL460c Gen10 Server
- HPE ProLiant WS460c Gen9 Server
- HPE ProLiant BL660c Gen9 Server

NOTE: This is a list of supported servers. Some may be discontinued.

Compatibility - Supported Interconnect Modules

- HPE Virtual Connect FlexFabric-20/40 F8 Module for c-Class BladeSystem
- HPE Virtual Connect FlexFabric-20/40 F8 Module for c-Class BladeSystem with TAA
- HPE Virtual Connect FlexFabric 10Gb/24-port Module for c-Class BladeSystem
- HPE Virtual Connect FlexFabric 10/24 Enterprise Edition BLc7000 Option
- HPE Virtual Connect Flex-10/10D Module for c-Class BladeSystem
- HPE Virtual Connect Flex-10/10D Module Enterprise Edition for BLc7000 Option
- HPE Virtual Connect Flex-10 10Gb Ethernet Module for c-Class BladeSystem
- HPE Virtual Connect Flex-10 Ethernet Module Enterprise Edition for BLc7000 Option
- HPE 6127XLG Ethernet Blade Switch
- HPE 6127XLG Ethernet Blade Switch with TAA
- HPE 6125XLG Ethernet Blade Switch
- HPE 6125XLG Ethernet Blade Switch with TAA
- HPE 6125G/XG Ethernet Blade Switch
- HPE 6125G/XG Ethernet Blade Switch with TAA
- HPE 6125G Ethernet Blade Switch
- HPE 6125G Ethernet Blade Switch with TAA

NOTE: Supported features with VC modules and Ethernet switches.

Feature	VC FF20/40 F8	VC FF 10/24	VC Flex-10/10D	VC Flex-10	HPE 6125	HPE 6127
20G		-	-	-	-	
10G						
FCoE				-		

This adapter also supports 1Gb or 10Gb connections with the following modules:

- HPE 10GbE Ethernet Pass-Thru Module for c-Class BladeSystem

- HPE 1Gb Ethernet Pass-Thru Module for c-Class BladeSystem

- HPE Cisco B22HP Fabric Extender with 16 FET for BladeSystem c-Class

Standard Features

At a Glance Features

- Full hardware offload of iSCSI and FCoE storage protocol processing for highest performance converged Ethernet data and storage networks
- Dual-port Flex-20 10GbE Type A adapter for HPE BladeSystem c-Class Gen8 and Gen9 blade servers
- Hardware acceleration and offloads for stateless TCP/IP, TCP Offload Engine (TOE)
- Industry-leading throughput and latency performance
- Improved small packet performance
- Support for Tunnel Offload (NVGRE, VXLAN)
- Integrated PHY and MAC
- Support for Preboot eXecution Environment (PXE)
- Optimized for virtual server environments with support for HPE Flex-20 Technology, Network Partitioning (NPAR) and Single-Root I/O Virtualization (SR-IOV)
- The HPE 630M adapter is compatible with Type A and B mezzanine slots for greater deployment versatility
- The HPE 630M is a Type A mezzanine adapter (works in Type A and Type B mezzanine slots)
- User configurable bandwidth settings when combined with the 20Gb Flex-20 Virtual Connect module or NPAR. From 100Mb/s to 20Gb/s on up to four "Physical Function" NICs per port, in increments of 100Mb/s for NIC. The combined bandwidth of NICs cannot exceed port bandwidth i.e. 10Gb
- DPDK and Virtual Connect cannot be used at the same time.
- Storage personality must be disabled on NIC intended for DPDK workload. DPDK and Storage modes cannot be used concurrently on current generation CNA NICs. HPE Recommends using 2 separate NICs for Storage (Control Plane), and DPDK (Data Plane) workloads for the optimal high availability configuration.

Virtual Connect FlexFabric 20 Gb Ethernet Module for the c-Class BladeSystem

Evolve 20 Gb at your own speed! When paired with the HPE Virtual Connect FlexFabric 20 Gb Ethernet Modules, take advantage of four Flex Nics, which are PCI Physical Function devices that are OS/ Hypervisor independent. In addition take advantage of new storage I/O functionality making it a full-Converged Network Adapter (CNA).

Server ROM recognizes them as individual NICs

Speeds can be set per NIC from 100 Mb/s to 20 Gb/s in 100 Mb/s increments

Three fold increase in number of network connections per port and up to four physical function NICs per port. Ideal for virtualized server environments, especially for dedicated bandwidth applications like virtual machine migration from one physical server to another physical server.

Throughput-Theoretical Bandwidth

This adapter delivers 40 Gb/s bi-directional Ethernet transfer rate per port (80 Gb/s per adapter), providing the network performance needed to improve response times and alleviate bottlenecks.

802.1p QoS Tagging

IEEE quality of service (QoS) 802.1p tagging allows the adapter to mark or tag frames with a priority level across a QoS-aware network for improved traffic flow.

802.1Q VLANs

IEEE 802.1Q virtual local area network (VLAN) protocol allows each physical port of this adapter to be separated into multiple virtual NICs for added network segmentation and enhanced security and performance.

Standard Features

VLANs increase security by isolating traffic between users. Limiting the broadcast traffic to within the same VLAN domain also improves performance.

DPDK	This adapter supports DPDK with benefit for packet processing acceleration and use in NFV deployments.
HPE Sea Of Sensors 3D	Support for the HPE Sea of Sensors which is a collection of 32 sensors that automatically track thermal activity - heat - across the server. When temperatures get too high, sensors can initiate fans and make other adjustments to reduce energy usage. A significant improvement lies in the ability to apply fan speed increases only to the portion of the system that is rising in temperature, rather than all six fans in unison, which reduces the amount of energy used for cooling.
iSCSI/FCoE	This adapter supports accelerated iSCSI or iSCSI boot and FCoE.
Jumbo Frames	This adapter supports Jumbo Frames (also known as extended frames), permitting up to a 9,000 byte (KB) transmission unit (MTU) when running Ethernet I/O traffic. This is over five times the size of a standard 1500-byte Ethernet frame. With Jumbo Frames, networks can achieve higher throughput performance and greater CPU utilization. These attributes are particularly useful for database transfer and tape backup operations.
Management Support	This adapter ships with agents that can be managed from HPE Systems Insight Manager or other management application that support SNMP.
Message Signaled Interrupt (Extended) (MSI-X)	Message Signaled Interrupt (Extended) provides performance benefits for multi-core servers by load balancing interrupts between CPUs/cores.
Network Adapter Teaming	This adapter support for NIC teaming helps IT administrators increase network fault tolerance and increased network bandwidth, the team of adapters can work together as a single virtual adapter, providing support for several different types of teaming enabling IT administrators to optimize availability, improve performance and help reduce costs.
Network Partitioning (NPAR)	This adapter supports Network Partitioning (NPAR) allowing administrators to configure a 10 Gb port as four separate partitions or physical functions. Each PCI function is associated with a different virtual NIC. To the OS and the network, each physical function appears as a separate NIC port.
Optimized for Virtualization	I/O Virtualization support for VMware NetQueue and Microsoft VMQ helps meet the performance demands of consolidated virtual workloads.
Preboot eXecution Environment (PXE)	Support for PXE enables automatic deployment of computing resources remotely from anywhere. It allows a new or existing server to boot over the network and download software, including the operating system, from a

Standard Features

management/ deployment server at another location on the network. Additionally, PXE enables decentralized software distribution and remote troubleshooting and repairs.

Single-Root I/O Virtualization

Single-Root I/O Virtualization (SR-IOV) provides a mechanism to bypass the host system hypervisor in virtual environments providing near metal performance and server efficiency. SR-IOV provides mechanism to create multiple Virtual Functions (VFs) to share single PCIe resources. The device is capable of SR-IOV, and requires Server BIOS support, controller firmware, and OS support.

TCP/UDP/IP

For overall improved system response, this adapter supports standard TCP/IP offloading techniques including: TCP/IP, UDP checksum offload (TCO) moves the TCP and IP checksum offloading from the CPU to the network adapter. Large send offload (LSO) or TCP segmentation offload (TSO) allows the TCP segmentation to be handled by the adapter rather than the CPU.

TOE

TCP/IP Offload Engine (TOE) shifts the processing of data in the TCP protocol stack from the server CPU to the adapter's processor, freeing server CPU cycles for other operations.

Tunnel Offload

Minimize the impact of overlay networking on host performance with tunnel offload support for VXLAN and NVGRE. By offloading packet processing to adapters, customers can use overlay networking to increase VM migration flexibility and virtualized overlay networks with minimal impact to performance. HPE Tunnel Offloading increases I/O throughput, reduces CPU utilization, and lowers power consumption. Tunnel Offload supports VMware's VXLAN and Microsoft's NVGRE solutions.

Warranty

Maximum: The remaining warranty of the HPE product in which it is installed (to a maximum three-year, limited warranty).

Minimum: One year limited warranty.

NOTE: Additional information regarding worldwide limited warranty and technical support is available at: <http://h17007.www1.hpe.com/us/en/enterprise/servers/warranty/index.aspx#.V4e3tPkrJhE>

Service and Support

Service and Support **NOTE: This adapter is covered under HPE Support Services/ Service Contract applied to the HPE ProLiant Server or enclosure. No separate HPE Support Services# need to be purchased.**

Most HPE branded options sourced from HPE that are compatible with your product will be covered under your main product support at the same level of coverage, allowing you to upgrade freely. Additional support is required on select workload accelerators, switches, racks and UPS options 12KVA and over. Coverage of the UPS battery is not included under HPE support services; standard warranty terms and conditions apply.

Warranty and Support Services

Warranty and Support Services will extend to include HPE options configured with your server or storage device. The price of support service is not impacted by configuration details. HPE sourced options that are compatible with your product will be covered under your server support at the same level of coverage allowing you to upgrade freely. Installation for HPE options is available as needed. To keep support costs low for everyone, some high value options will require additional support. Additional support is only required on select high value workload accelerators, fibre switches, InfiniBand and UPS options 12KVA and over. Coverage of the UPS battery is not included under TS support services; standard warranty terms and conditions apply.

Protect your business beyond warranty with HPE Support Services

HPE Technology Services delivers confidence, reduces risk and helps customers realize agility and stability. Connect to HPE to help prevent problems and solve issues faster. HPE Support Services enable you to choose the right service level, length of coverage and response time as you purchase your new server, giving you full entitlement to the support you need for your IT and business.
Protect your product, beyond warranty.

Parts and Materials

Hewlett Packard Enterprise will provide HPE-supported replacement parts and materials necessary to maintain the covered hardware product in operating condition, including parts and materials for available and recommended engineering improvements. Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services. The defective media retention service feature option applies only to Disk or eligible SSD/Flash Drives replaced by Hewlett Packard Enterprise due to malfunction.

For more information

Visit the Hewlett Packard Enterprise Service and Support [website](#).

Technical Specifications

General Specifications	Network Processor	Cavium 57840S with integrated MAC/PHY
	Data Rate	Two ports, each at 40Gb/s bi-directional; 80Gb/s aggregate bi-directional theoretical bandwidth.
	Bus type	PCI Express 3.0 (Gen 3) x8
	Form Factor	Type A mezzanine adapter (works in Type A and Type B mezzanine slots)
	IEEE Compliance	802.3, 802.3ab, 802.3u, 802.3x, 802.3ad, 802.3p, 802.1q, 802.3ae, 802.3ap, 1588

Power and Environmental Specifications	Power	<12W maximum
	Temperature - Operating	0° to 55°C (32° to 131°F)
	Humidity - Operating	10% to 90% non-condensing
	Agency Approvals	USA: FCC Part 15 Class A Canada: ICES-003, Issue 4 Japan: VCCI V3 (2010.04) Class A International: EN55022:2006 + A1:2007 Class A International: EN55024:1998+A1:2011+A2; EN61000-3-2:2006, EN61000-3-3:2008 Taiwan: BSMI, CNS13438 (2006) Class A Australia/New Zealand (AS/NZS): EN55022:2006+A12007 class A Korea: KN22 Class A, KN24
	RoHS Compliance	6 of 6

Operating System and Virtualization Support

- Microsoft Windows Server 2008 SP2, R2 w/SP1 (x86 and x64)
- Microsoft Windows Server 2012 and 2012 R2
- Red Hat Enterprise Linux (RHEL) 5.9, 5.10, 6.4, 6.5, 6.7, 7.0 (x86, x64)
- Red Hat Enterprise Linux (RHEL) 7.1, 7.2 (x64)
- SUSE Linux Enterprise Server (SLES) 11, SP2, SP3 (x86 & x64)
- SUSE Linux Enterprise Server (SLES) 11 SP4 (x64)
- SUSE Linux Enterprise Server (SLES) 12, SP1 (x64)
- Solaris 10 U10
- Solaris 11 x64
- VMware ESXi 5.0 U3, 5.1 U2
- VMware vSphere 5.5, 6.0

NOTE: For more operating system support and certification information, please visit: http://h17007.www1.hp.com/us/en/enterprise/servers/supportmatrix/redhat_linux.aspx#.V4e8tPkrJD8

- NOTE:**
- Minimum Linux versions for FCoE support include RHEL 6.4 and SLES 11 SP3
 - For RHEL 7.x, RHEL 7.2 is the minimum version for FCoE Boot from SAN support
 - vSphere 5.5 is the minimum version of VMware for 20 Gb support and SRIOV support
 - vSphere 6.0 is the minimum version of VMware for UEFI FCoE Boot from SAN support
 - Boot from SAN via the iSCSI offload path is not supported for VMware
 - Networking only support for Solaris and Citrix XenServer
 - FCoE is not supported on XenServer

Technical Specifications

- **UEFI is not supported for Xenserver**

Environment-friendly Products and Approach - End-of-life Management and Recycling

Hewlett Packard Enterprise offers end-of-life **product return, trade-in, and recycling programs** in many geographic areas, for our products. Products returned to Hewlett Packard Enterprise will be recycled, recovered or disposed of in a responsible manner.

The EU WEEE Directive (2012/19/EU) requires manufacturers to provide treatment information for each product type for use by treatment facilities. This information (product disassembly instructions) is posted on the **Hewlett Packard Enterprise web site**. These instructions may be used by recyclers and other WEEE treatment facilities as well as Hewlett Packard Enterprise OEM customers who integrate and re-sell Hewlett Packard Enterprise equipment.

Summary of Changes

Date	Version History	Action	Description of Change
05-Mar-2018	Version 14	Changed	General Specifications section was updated
05-Feb-2018	Version 13	Changed	Overview section was updated
04-Dec-2017	Version 12	Changed	Standard Features-At a Glance Features was updated.
11-Jul-2017	Version 11	Changed	Compatibility section was updated.
27-Mar-2017	Version 10	Changed	Standard Features and General Specifications were updated.
07-Oct-2016	Version 9	Added	Added DPDK support.
22-Jul-2016	Version 8	Changed	QuickSpecs sections were updated.
29-Apr-2016	Version 7	Added	SKUs added in Related Options: 787635-B21, 787635-B22.
		Changed	Rebranding applied to document.
19-Jun-2015	Version 6	Changed	Overview, Compatibility, Standard Features, and Technical Specifications sections were updated.
28-Nov-2014	Version 5	Added	SKUs Added on HPE 10/20Gb interconnects: 737230-B21, 737226-B21, 658247-B21, 737220-B21.
		Changed	Compatibility, Related Options and Technical Specifications sections were updated.
17-Oct-2014	Version 4	Added	SKUs added on Related Options: 691367-B21, 691367-B22, 571956-B21, 605865-B21, 638526-B21, 662048-B21, 711307-B21, 658250-B21, 516733-B21, 538113-B21, 406740-B21, 657787-B21.
		Changed	Overview, Compatibility, Product features, Standard features, Technical Specifications sections were updated.
11-Jul-2014	Version 3	Changed	Kit contents, Product features, and Network processor were revised.
13-Jun-2014	Version 2	Changed	Image change only.
10-Jun-2014	Version 1	New	Initial version.



Sign up for updates



© Copyright 2018 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

c04312720 - 14972 - Worldwide - V14 -05-March-2018