

# Cisco Nexus 9332D-H2R Switch

---

# Contents

Product overview	3
Features and benefits	4
Licensing	6
Product sustainability	6
Product specifications	6
Supported optics modules	9
Ordering information	9
Warranty information	9
Cisco and Partner Services	9
Regulatory standards compliance	10
Cisco Capital	11
Document history	12

---

The Cisco Nexus® 9332D-H2R Switch is a deep-buffer, 32-port 400G fixed switch.

## Product overview

Artificial Intelligence and Machine Learning (AI/ML) applications are being used increasingly in today's data centers, and the Cisco Nexus 9000 Series Switches have the hardware and software capabilities to provide the right latency, congestion-management mechanisms, and telemetry to meet the requirements of those applications. The Cisco Nexus 9000 Series switches address the need for high-performance, power-efficient, compact switching in the networking infrastructure, designed to support 400G fabrics for next-generation leaf and spine designs.

Large-cloud and data-center networking teams require a flexible, reliable solution that efficiently manages, troubleshoots, and analyzes their IT infrastructure. In addition, they need security, automation, visibility, analytics, and assurance. Managed by the operations and automation platform Cisco Nexus Dashboard with services such as Cisco Nexus Dashboard Insights for visibility and Nexus Dashboard Fabric Controller for automation, Cisco Nexus 9000 Series switches are ideal platforms to build a high-performance AI/ML network fabric.

The Cisco Nexus 9332D-H2R Switch introduces the first switch with deep-buffer capability to the Nexus 9000 fixed-switch portfolio. The switch is built with backward-compatible 400G optical interface Quad Small Form-Factor Pluggable-Double Density (QSFP-DD) ports to migrate existing data center fabrics from 40-Gbps and 100-Gbps speeds to 400 Gbps; it also offers various lower port speeds and densities, including 10, 25, 40, 50, 100, and 200 Gbps, using breakouts. The Cisco Nexus 9332D-H2R Switch is based on Cisco® Cloud Scale technology equipped to support next-generation cloud architecture.

The Cisco Nexus 9332D-H2R is a 1-Rack-Unit (1RU) 32-port 400 Gigabit Ethernet switch that supports 25.6 Tbps of bandwidth. The switch provides 80MB of on-die packet buffer and 8GB of high bandwidth memory (or HBM) with MACsec capability on all 32 ports.

The Cisco Nexus 9332D-H2R supports the Precision Time Protocol (PTP) with Class C timing accuracy for telecom as well as media profiles. Through PTP and Synchronous Ethernet, it delivers frequency and time distribution with high accuracy.



**Figure 1.**  
Cisco Nexus 9332D-H2R Switch, frontside



**Figure 2.**  
Cisco Nexus 9332D-H2R Switch, rearside

## Features and benefits

**Table 1.** Features and benefits

Features	Description and benefits
<b>Architectural flexibility</b>	<ul style="list-style-type: none"> <li>• Cisco Nexus 9000 Series switches support Cisco Application Centric Infrastructure (ACI), Cisco NXOS VXLAN EVPN, Cisco IP Fabric for Media (IPFM), Cisco Nexus Data Broker, and IP routed or Ethernet switched layer 2 fabrics using a comprehensive set of unicast and multicast IPv6/IPv4 and Ethernet protocols.</li> <li>• Purpose-built Cisco NX-OS Software operating system with comprehensive, proven innovations. The operating system is modular, with a dedicated process for each routing protocol: a design that isolates faults while increasing availability.</li> <li>• Industry-leading Cisco Software-Defined Networking (SDN) solution with Cisco ACI support. Cisco ACI is a holistic, intent-driven architecture with centralized automation and policy-based application profiles.</li> <li>• Support for standards based VXLAN EVPN fabrics, inclusive of hierarchical multisite support (Refer to VXLAN network with MP-BGP EVPN control plane for more information)</li> <li>• Three-tier BGP architectures, enabling horizontal, nonblocking IPv6 network fabrics at web scale</li> <li>• Comprehensive protocol support for Layer 3 (v4 and v6) unicast and multicast routing protocol suites, including BGP, Open Shortest Path First (OSPF), Enhanced Interior Gateway Routing Protocol (EIGRP), Routing Information Protocol Version 2 (RIPv2), Protocol Independent Multicast Sparse Mode (PIM-SM), Source-Specific Multicast (SSM), and Multicast Source Discovery Protocol (MSDP)</li> <li>• Segment Routing (SR and SRv6) allows the network to forward Multiprotocol Label Switching (MPLS) packets and engineer traffic without Resource Reservation Protocol (RSVP) Traffic Engineering (TE). It provides a control-plane alternative for increased network scalability and virtualization. Cisco IP Fabric for Media helps you migrate from an SDI router to an IP-based infrastructure. In an IP-based infrastructure, a single cable has the capacity to carry multiple bidirectional traffic flows and can support different flow sizes without requiring changes to the physical infrastructure.</li> <li>• Nexus Dashboard Data Broker provides customers complete observability into their network and solution(s) that can help and facilitate them to identify and mitigate security threats, realize and remediate performance bottlenecks, adhere to data compliance and have insight into capacity planning operations.</li> </ul>
<b>Extensive programmability</b>	<ul style="list-style-type: none"> <li>• Day-0 automation through Power On Auto Provisioning (POAP), drastically reducing provision time</li> <li>• Industry-leading integrations for leading DevOps configuration management applications, such as Ansible. Extensive native YANG and industry-standard OpenConfig model support through RESTCONF/NETCONF/gNMI</li> <li>• REST API interacting with Data Management Engine (DME)</li> <li>• Model-Driven telemetry enhances network observability</li> <li>• 3rd party application hosting using Cisco Application Framework (CAF)</li> </ul>
<b>High scalability, flexibility, and security</b>	<ul style="list-style-type: none"> <li>• Flexible forwarding tables support up to two million shared entries</li> <li>• Flexible shared ingress and egress of max 56000 ACL entries</li> <li>• 8GB of off-die High Bandwidth Memory (HBM), DRAM based deep buffer</li> <li>• IEEE 802.1ae MAC Security (MACsec) capability on all ports, allows traffic encryption at the physical layer and provides secure server, border leaf, and leaf-to-spine connectivity.</li> </ul>

Features	Description and benefits
<b>AI/ML Networking</b>	<p>Cisco Nexus 9000 Series switches support innovative congestion management and flow control algorithms along with the right latency and telemetry to meet the design requirements of AI/ML fabrics.</p> <ul style="list-style-type: none"> <li>• Priority Flow Control (PFC) is a key capability supported on Cisco Nexus 9000 Series switches that prevents Ethernet frame drops by signaling, controlling, and managing Ethernet flows along the path by sending pause frames to appropriate senders.</li> <li>• The platform also supports Explicit Congestion Notification (ECN), which provides end-to-end notification per IP flow by marking packets that experienced congestion, without dropping traffic. The platform can track ECN statistics, including the number of marked packets that have experienced congestion.</li> <li>• The platform offers lossless transport for Remote Direct Memory Access (RDMA) over converged Ethernet (RoCE) with support of Data Center Bridging (DCB) protocols: <ul style="list-style-type: none"> <li>◦ Enhanced Transmission Selection (ETS) reserves bandwidth per priority class in network contention situations.</li> <li>◦ Data Center Bridging Exchange Protocol (DCBX) can discover and exchange priority and bandwidth information with endpoints.</li> </ul> </li> <li>• Weighted Random Early Detection (WRED) is a congestion avoidance technique that allows Cisco Nexus 9000 Series switches to detect and react to congestion in the network by marking flows that could cause congestion.</li> <li>• The platform offers Cisco's innovative intelligent buffer management, which offers the capability to distinguish mice and elephant flows and apply different queue management schemes to them based on their network forwarding requirements in the event of link congestion.</li> <li>• Approximate Fair Dropping (AFD) with Elephant Trap (ETRAP). AFD distinguishes long-lived elephant flows from short-lived mice flows, by using ETRAP. ETRAP measures the byte counts of incoming flows and compares this against the user defined ETRAP threshold. After a flow crosses the threshold, it becomes an elephant flow.</li> <li>• Dynamic Packet Prioritization (DPP) provides the capability of separating mice flows and elephant flows into two different queues so that buffer space can be allocated to them independently.</li> </ul>
<b>Hardware and software high availability</b>	<ul style="list-style-type: none"> <li>• Virtual Port-Channel (vPC) technology provides Layer 2 multipathing through the elimination of Spanning Tree Protocol (STP).</li> <li>• Can do fabric link in the VXLAN environment, eliminating the need for peer-to-peer VPC. The 128-way Equal-Cost MultiPath (ECMP) routing enables the use of Layer 3 fat-tree designs. This feature helps organizations prevent network bottlenecks, increase resiliency, and add capacity with little network disruption.</li> <li>• Software Maintenance Upgrade (SMU) contains fixes for a specific defect. They provide a quick resolution of critical issues.</li> <li>• In-service software upgrade (ISSU) allows to upgrade the device software while the switch continues to forward traffic. ISSU reduces or eliminates the downtime typically caused by software upgrades</li> <li>• The switches use hot-swappable Power-Supply Units (PSUs) and fans with N+1 redundancy.</li> </ul>
<b>Cisco Nexus Dashboard</b>	<p>Cisco Nexus Dashboard is a platform that transforms data center and cloud network operations through simplicity, automation, and analytics. Cisco Nexus Dashboard Fabric Controller (NDFC), Cisco Nexus Dashboard Insights (NDI) and Cisco Nexus Dashboard Orchestrator (NDO) are integrated as services in Cisco Nexus Dashboard.</p> <p>Cisco Nexus Dashboard is included with all Cisco Nexus 9000 switch tiered licenses, DCN Essentials, Advantage and Premier. The services hosted on Cisco Nexus Dashboard require their own licenses. For the full breakdown of features included in each tier, please refer to the <a href="#">Cisco DCN Software Subscriptions</a> page.</p>

## Licensing

The default system software has a comprehensive Layer-2 security and management feature set. To enable additional functions, including Layer-3 IP unicast and IP multicast routing and Cisco Nexus Data Broker, you must install additional licenses. The Cisco Nexus 9332D-H2R switch uses the XF2 class Cisco Data Center Network (Cisco DCN) Premier, Advantage, and Essentials subscription licenses. The [licensing guide](#) illustrates the software packaging and licensing available to enable advanced features. For the latest software release information and recommendations, refer to the release notes.

## Product sustainability

Information about Cisco’s Environmental, Social, and Governance (ESG) initiatives and performance is provided in Cisco’s CSR and sustainability [reporting](#).

**Table 2.** Cisco environmental sustainability information

Sustainability topic		Reference
<b>General</b>	Information on product-material-content laws and regulations	<a href="#">Materials</a>
	Information on electronic waste laws and regulations, including our products, batteries and packaging	<a href="#">WEEE Compliance</a>
	Information on product takeback and reuse program	<a href="#">Cisco Takeback and Reuse Program</a>
	Sustainability Inquiries	Contact: <a href="mailto:csr_inquiries@cisco.com">csr_inquiries@cisco.com</a>
	Countries and Regions Supported	Table 8: Regulatory Compliance
<b>Power</b>	Power	Table 4: Power-supply specifications
<b>Material</b>	Product packaging weight and materials	Contact: <a href="mailto:environment@cisco.com">environment@cisco.com</a>
	Weight	Table 6. Weight

## Product specifications

**Table 3.** Cisco Nexus 9332D-H2R Switch specifications

Item	Cisco Nexus 9332D-H2R Switch
<b>Technical</b>	<ul style="list-style-type: none"> <li>• 32-port 400G QSFP-DD ports</li> <li>• On-die buffer: 80MB</li> <li>• High-bandwidth memory: 8GB</li> <li>• System memory: 32GB, expandable to 64GB</li> <li>• SSD: 128GB</li> <li>• USB: 1 port</li> <li>• RS-232 serial console ports: 1</li> <li>• Management ports: 2</li> <li>• CPU: 6 cores</li> </ul>

Item	Cisco Nexus 9332D-H2R Switch
<b>Power and cooling</b>	<ul style="list-style-type: none"> <li>• Power: 2000W AC, DC, HV</li> <li>• Hot-swappable, 6 fans, 5+1 redundancy</li> <li>• Typical power: 1015 W</li> <li>• Maximum power: 1900 W</li> </ul>
<b>Physical and Environmental</b>	<ul style="list-style-type: none"> <li>• Dimensions (H x W x D): 1.72 x 17.3 x 29.34 in. (4.36 x 43.94 x 74.52 cm)</li> <li>• Acoustics: <ul style="list-style-type: none"> <li>◦ at 60% fan speed: 76.3dB</li> <li>◦ at 70% fan speed: 80.4dB</li> <li>◦ at 100% fan speed: 87.6dB</li> </ul> </li> <li>• Operating temperature: 32 to 104F (0 to 40C)</li> <li>• Nonoperating (storage temperature): -40 to 131F (-40 to 55C)</li> <li>• Humidity: 5 to 95% (non-condensing)</li> <li>• Altitude: 0 to 10,000 ft (0 to 3048m)</li> <li>• Mean Time Between Failure (MTBF): 154,950 hours</li> </ul>

**Table 4.** Cisco Nexus 9332D-H2R Switch power-supply specifications

Model	Cisco Nexus 9300 AC power supply	Cisco Nexus 9300 DC power supply	Cisco Nexus 9300 HV power supply
<b>Output power</b>	2000 W	2000 W	2000 W
<b>Input voltage</b>	90-140V AC 180-264V AC	-40 to -72V DC	90-140V AC 180-305V AC 192-400V DC
<b>Input frequency</b>	50/60 Hz	-	50/60 Hz
<b>Connector</b>	IEC60320 C14	Amphenol C10-638976-000	Anderson Power product: Saf-D-Grid
<b>Efficiency</b>	80PLUS Platinum efficiency rating		80PLUS Platinum efficiency rating

**Table 5.** Performance and scalability specifications

Item	Cisco Nexus 9332D-H2R Switch
<b>Number of slices</b>	4 slices
<b>Maximum number of IPv4 Longest Prefix Match (LPM) routes*</b>	~2 Million
<b>Maximum number of IPv4 host entries*</b>	~2 Million

Item	Cisco Nexus 9332D-H2R Switch
Maximum number of IPv6 Longest Prefix Match (LPM) routes*	~1 Million ~2 Million
Maximum number of IPv6 host entries*	
Maximum number of MAC address entries*	~1 Million
Maximum number of multicast routes	256,000
Number of Internet Group Management Protocol (IGMP) snooping groups	Maximum: 32,000
Maximum number of Access Control List (ACL) entries	14,000 shared ingress and egress/slice Max: 56,000 shared ingress and egress
Maximum number of VLANs	4096**
Number of Virtual Routing and Forwarding (VRF) instances	Maximum: 16,000
Maximum number of ECMP paths	128
Maximum number of port channels*	512
Maximum number of links in a port channel*	32
Number of SPAN sessions	32 (4 Active)
Maximum number of VLANs in Rapid per-VLAN Spanning Tree (RPVST) instances	4K
Maximum number of Hot-Standby Router Protocol (HSRP) groups	1000
Maximum number of Multiple Spanning Tree (MST) instances	64
Flow-table size	128K/slice
Number of Network Address Translation (NAT) entries	2000
Number of Output Queues per physical port	8

\* Refers to the hardware capacity, please visit the Cisco Nexus 9000 Series Verified Scalability Guide and Cisco Application Policy Infrastructure Scalability Guide for the latest supported scalability numbers validated for specific software.

\*\*127 VLANs out of 4096 are reserved

**Table 6.** Weight

Part Number	Weight
N9K-C9332D-H2Rwithout power supplies or fans	31.6 lbs (14.3 kg)
N9K-C9332D-H2Rwith power supplies and fans	38.4 lbs (17.4 kg)
NXA-SFAN-35CFM-PI	0.26 lbs (0.1 kg)



## Supported optics modules

For details on the optical modules available and the minimum software release required for each supported optical module, visit [here](#).

## Ordering information

**Table 7.** Ordering information

Part number	Product description
<b>N9K-C9332D-H2R</b>	Cisco Nexus 9300 Series w 32p 400G w HBM
<b>N9K-C9332D-H2R=</b>	Cisco Nexus 9300 Series w 32p 400G w HBM w/o power supply, fans
<b>NXA-PAC-2KW-PI</b>	Cisco Nexus 9000 2KW AC power supply, port-side intake
<b>NXA-PHV-2KW-PI</b>	Cisco Nexus 2KW PHV power supply, port-side intake
<b>NXA-PDC-2KW-PI</b>	Cisco Nexus 9K 2KW DC PS, port-side intake
<b>NXA-SFAN-35CFM-PI</b>	Cisco Nexus fan, 35CFM, port-side intake airflow /w EEPROM
<b>NXA-PAC-2KW-PI=</b>	Cisco Nexus 9000 2KW AC power supply, port-side intake, spare
<b>NXA-PHV-2KW-PI=</b>	Cisco Nexus 2KW PHV power supply, port-side intake, spare
<b>NXA-PDC-2KW-PI=</b>	Cisco Nexus 9K 2KW DC PS, port-side intake, spare
<b>NXA-SFAN-35CFM-PI=</b>	Cisco Nexus fan, 35CFM, port-side intake airflow /w EEPROM, spare

## Warranty information

The Cisco Nexus 9332D-H2R switch has a 1-year limited hardware warranty. The warranty includes hardware replacement with a 10-day turnaround from receipt of a Return Materials Authorization (RMA).

## Cisco and Partner Services

Cisco offers a wide range of services to help accelerate your success in deploying and optimizing the Cisco Nexus 9300 switch in your data center. The innovative Cisco Services offerings are delivered through a unique combination of people, processes, tools, and partners and are focused on helping you increase operation efficiency and improve your data center network. Cisco Advanced Services uses an architecture-led approach to help you align your data center infrastructure with your business goals and achieve long-term value. Cisco SMARTnet™ Service helps you resolve mission-critical problems with direct access at any time to Cisco network experts and award-winning resources.

## Regulatory standards compliance

**Table 8.** Regulatory standards compliance: safety and EMC

Specification	Description
<b>Regulatory compliance</b>	Products complies with CE Markings according to directives 2014/30/EU and 2014/35/EU
<b>Safety</b>	<ul style="list-style-type: none"> <li>• ANSI/UL 60950-1 2nd Edition and 62368-1 3rd Edition</li> <li>• CAN/CSA-C22.2 No. 60950-1 2nd edition and 62368-1 3rd edition</li> <li>• EN 62368-1 2nd Edition</li> <li>• IEC 62368-1 Third Edition</li> <li>• AS/NZS 62368-1 Third Edition</li> <li>• GB4943</li> </ul>
<b>EMC: Emissions*</b>	<ul style="list-style-type: none"> <li>• 47 CFR Part 15 Class A</li> <li>• CISPR32 Class A</li> <li>• CNS 15936</li> <li>• EN 55032 Class A</li> <li>• EN 61000-3-3</li> <li>• EN IEC 61000-3-11</li> <li>• EN IEC 61000-3-2</li> <li>• EN61000-3-12</li> <li>• ICES-003:Iss:7 Class A</li> <li>• KS C 9610-3-11</li> <li>• KS C 9610-3-12</li> <li>• KS C 9610-3-2</li> <li>• KS C 9610-3-3</li> <li>• KS C 9832</li> <li>• VCCI-CISPR 32 Class A</li> </ul>
<b>EMC: Immunity</b>	<ul style="list-style-type: none"> <li>• CISPR24</li> <li>• CISPR35</li> <li>• EN55035</li> <li>• EN/IEC61000-6-1</li> <li>• EN 300 386</li> <li>• EN61000-6-1</li> <li>• EN61000-6-2</li> <li>• IEC61000-6-1</li> <li>• IEC61000-6-2</li> <li>• KS C 9835</li> </ul>
<b>RoHS</b>	<ul style="list-style-type: none"> <li>• The product is RoHS-6 compliant with exceptions for leaded-Ball Grid-Array (BGA) balls and lead press-fit connectors.</li> </ul>

---

## Cisco Capital

### **Flexible payment solutions to help you achieve your objectives**

Cisco Capital makes it easier to get the right technology to achieve your objectives, enable business transformation and help you stay competitive. We can help you reduce the total cost of ownership, conserve capital, and accelerate growth. In more than 100 countries, our flexible payment solutions can help you acquire hardware, software, services and complementary third-party equipment in easy, predictable payments. [Learn more.](#)

---

## Document history

New or revised topic	Described In	Date

**Americas Headquarters**  
Cisco Systems, Inc.  
San Jose, CA

**Asia Pacific Headquarters**  
Cisco Systems (USA) Pte. Ltd.  
Singapore

**Europe Headquarters**  
Cisco Systems International BV Amsterdam,  
The Netherlands

Cisco has more than 200 offices worldwide. Addresses, phone numbers, and fax numbers are listed on the Cisco Website at <https://www.cisco.com/go/offices>.

Cisco and the Cisco logo are trademarks or registered trademarks of Cisco and/or its affiliates in the U.S. and other countries. To view a list of Cisco trademarks, go to this URL: <https://www.cisco.com/go/trademarks>. Third-party trademarks mentioned are the property of their respective owners. The use of the word partner does not imply a partnership relationship between Cisco and any other company. (1110R)

Printed in USA

C78-3807765-01 02/24