



19" Double Section Wallmount Cabinet

12U, 550 mm (21.7 in.) Depth, Assembled, Black

Part No.: **716277**

EAN-13: 0766623716277 | UPC: 766623716277

Network wall mount rack with double section for convenient access to the rear cabling of your cabinet

Intellinet Network Solutions double-section wall-mount cabinets offer you a flexible solution for your network installations. The tempered-glass door, easily removable side panels and cold-rolled galvanized steel are just some of its top quality workmanship and materials. This cabinet ship completely assembled for a quick and easy installation.

Space-saving

The rack's wall-mountable option is perfect for saving valuable floor space while organizing network and server equipment from telecom, surveillance and audio/video applications where space is at a premium and a full-size floor-standing rack or cabinet cannot be used. The 425 mm (16.73 in.) usable depth allows for the mounting of shelves, switches, patch panels and more. 20 rack screws and cage nuts are included to securely mount your equipment.

Easy access

A double-section allows for convenient access to the back of the cabinet. This means that you can easily adjust, maintain, or replace the cables and equipment without having to dismount the cabinet from the wall.

High-quality steel

The strong and durable housing, constructed of high-quality SPCC cold-rolled steel with antistatic powder coating, carries a load capacity up to 30 kg (66 lbs.).

Features:

- Wall-mountable 19 in. network rack with lockable double section for convenient access to rear cabling
- Maximum load capacity of 30 kg (66 lbs.)
- Usable depth: 425 mm (16.73 in.)
- Tempered-glass door can be opened more than 180°
- Pre-punched cable entry openings on top and rear
- Rear door for easy access to back of cabinet
- Cold-rolled, galvanized SPCC steel with up to 1.2 mm thickness
- Reversible front door
- Removable and lockable side panels for easy access to cabling and components
- IP20-rated protection
- Ships fully assembled for quick installation
- Three-year warranty

Specifications:

General

- 19"
- Height: 12U
- Color: Black RAL9004
- Complies with: ANSI/EIA RS-310-D; IEC60297-2; DIN41494, Part 1; DIN41494, Part 7

Physical

- Dimensions (H x W x D): 635 x 600 x 550 mm (25 x 23.62 x 21.65 in.)
- Usable depth: 425 mm (16.73 in.)
- Maximum static load: 30 kg (66 lbs.)
- Net weight: 25 kg (55.12 lbs.)
- Gross weight: 26 kg (57.32 lbs.)

Package Contents

- Double section wall mount
- Installation hardware including tool, 20x M6 Sets and 6x Keys



