



This USB-C to HDMI Audio/Video Adapter Converter is an ideal solution for connecting a device with a USB-C port to an HDTV, projector, or other display with an HDMI port. This adapter supports up to a 4k (3840 x 2160) at 60Hz resolution, allowing it to deliver a high-quality video image to the connected display. The compact design of this adapter makes it a perfect pair for BYOD (Bring Your Own Device) applications in education or corporate environments. This adapter is an ideal accessory for Apple® and other leading laptops and tablets.

**Features and Benefits**

- Supports resolutions up to 4K (3840 x 2160) at 60Hz
- Compatible with USB-C, Thunderbolt™ 3 and Thunderbolt™ 4 ports
- A reversible, symmetrical USB-C connector
- Compact, lightweight design
- Plug and Play—no driver required
- Compatible with the Apple® MacBook®, MacBook Air®, and MacBook Pro®

**Features & Benefits**

- Supports resolutions up to 4K (3840 x 2160) at 60Hz
- A reversible, symmetrical USB-C connector
- Plug and Play—no driver required
- Compatible with USB-C, Thunderbolt™ 3 and Thunderbolt™ 4 ports
- Compact, lightweight design
- Compatible with the Apple® MacBook®, MacBook Air®, and MacBook Pro®

**Specifications**

**General Info**

Product Line	C2G	UPC Number	757120269366
Country Of Origin	China	Application Sector	Residential, Commercial
Warranty Type	Lifetime	Type	Adapter

**Dimensions**

Product Width US	1.5 in	Product Height US	0.6 in
Product Length US	1.65 in	Cable Length	4.2 in

---

## Listing Agencies / 3rd Party Agencies

---

CE Certified	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

---

## Technical Information

---

Jacket Material	PVC (Polyvinyl Chloride)	Video Resolution	4K 60Hz
-----------------	--------------------------	------------------	---------

---

Bend Radius	40 mm	Thickness	4 mm
-------------	-------	-----------	------

---

Cable Type	Adapter	Jacket Rating	VW-1
------------	---------	---------------	------

---

Adapter Rear	HDMI Female	Adapter Front	USB-C Male
--------------	-------------	---------------	------------

---

Operating Temperature	0 C, 50 C	Voltage	0 to 30 V, 30, 0
-----------------------	-----------	---------	------------------

---