

Poly VVX 250 4-Line IP Phone and PoE-enabled GSA/TAA (89B64AA)



For today's office

Quality sound is standard on the Poly VVX 250 IP desk phone. You'll appreciate all the smart features on non-stop call days, but equally love the color display. It's a win-win for today's office environments.



Conversations stay on track

Hear every nuance on the Poly VVX 250 IP desk phone with quality audio featuring Poly HD Voice. And reduce distracting background noise at the source with Poly Acoustic Fence technology.

Integrated protection [1]

Your phones stay cleaner for longer with integrated Microban® antimicrobial product protection [1] actively reducing the growth of bacteria 24/7.

Featuring

Lines

Stay productive with 4-line keys supporting up to 34-line key appearances with pagination for autodialed and contacts.

LCD color display

A 2.8-inch backlight color display offers an engaging experience with all the information you need at a glance.

Keys

4-way navigation cluster with a center select key and a 12-key dial pad with controls for mute, speaker, and headset volume.

Add a Poly headset

Multiple Poly headset options are available to suit your style — in addition to the traditional handset. [2]

Ethernet ports

2 high-speed 10/100/1000 Ethernet ports with an integrated switch allow LAN connection for your phone with a pass-through connection to your PC. PoE reduces cable clutter on your desktop, eliminating the need for a separate power adapter.

Specifications

No Technical Specifications

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] Microban antimicrobial product protection is a built-in active ingredient that enables products to resist the growth of microbes such as bacteria, mold, and mildew. Microban protection helps products stay cleaner, fresher, and last longer than products with untreated surfaces.

[2] Poly headsets sold separately. Poly Electronic Hook Switch (EHS) sold separately.

Technical Specifications Footnotes

No Technical Specifications Footnotes

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

