

HP 937 Yellow Original Ink Cartridge (4S6W4NA)



Overview

Reliable, quality printing for business

Count on professional-quality documents. Original HP Ink Cartridges provide impressive reliability for dependable performance and durable results.[1] Print with inks that produce business documents with vibrant colors and sharp black text.[2]

Consistent business printing you can count on

Represent your business with proprietary Original HP Inks designed for consistent, professional results.

Upgraded chip[8] for enhanced print security

ISO/IEC 20243 OTTP-S certified for supply chain security for trust and tamper resistance.[10]

Free and easy recycling to help reduce waste[3]

To date, customers have recycled over a billion Original HP Cartridges through HP Planet Partners.[4]

Free and easy recycling to help close the loop[3]

Most Original HP Cartridges have been engineered to contain recycled content and meet HP's quality standards.

Features



Quality and reliability you can trust

Designed to be recycled^[1]



Meets eco-label emission criteria^[2]^[2]



Engineered for security^[3]

[1] Based on HP internal testing and Wilhelm Imaging Research Dark Storage Statement. See <http://www.hp.com/go/printpermanence> .

[2] Applicable to Original HP 936/937/938 and Original HP 936e/937e/938e Ink Cartridges.

[3] Program availability varies. For more information, visit <http://www.hp.com/hprecycle> .

[4] See <http://www.hp.com/SIR2022> , page 6

[8] Compared to previous OfficeJet Pro ink cartridge chips.

[10] See ISO/IEC 20243:2018 Open Trusted Technology Provider™ Standard Certification Register certification.opengroup.org/register/ottps-certification

[1] HP Planet Partners program availability varies. For details, see <http://www.hp.com/hprecycle> . On recycled materials in cartridges, see <http://www.hp.com/TonerRecycledContent> .

[2] Blue Angel DE-UZ 219 emissions criteria or earlier versions of criteria applicable when printing system launched. An HP printing system consists of HP printer, paper and Original HP supply.

[3] HP office-class printing systems are select Enterprise and Managed devices with FutureSmart firmware 4.5 and up, Pro devices, LaserJet models 200 and up, with respective Original HP Toner, PageWide and Ink Cartridges. Does not include HP integrated printhead cartridges. Digital supply-chain tracking, hardware, chips and packaging security features vary locally by SKU. See www.hp.com/cartridgesecurity .

Specifications

Color(s) of printing supplies	Yellow
Print Technology	Ink
Supply type	Cartridges
Operating temperature range	15 to 35°C
Storage temperature range	0 to 40°C
Operating humidity range	5 to 80% RH
Non-Operating Humidity Range	5 to 80% RH
Compatibility	HP OfficeJet Pro 9110, HP OfficeJet Pro 9120, HP OfficeJet Pro 9130, HP OfficeJet Pro 9720, HP OfficeJet Pro 9730
Product count per unit	1
Quantity per pallet	4224
Cartons per pallet	176
UPC number	196548610976
Minimum dimensions (W x D x H)	114.8 x 23.9 x 100.1 mm
Minimum dimensions (W x D x H)	4.52 x 0.94 x 3.94 in
Package dimensions (W x D x H)	114.8 x 23.9 x 100.1 mm
Package dimensions (W x D x H)	4.52 x 0.94 x 3.94 in
Pallet dimensions (W x D x H)	1016 x 1219.2 x 1333.5 mm
Pallet dimensions	40 x 48 x 52.5 in
Package weight	~0.05 kg
Package weight	~0.12 lb
Pallet weight	288.2 kg
Pallet weight	634.9 lb
Page Yield	800
What's in the box	1 Cartridge
Manufacturer Warranty	HP's ink cartridges and printheads are warranted to be free from defects in materials and workmanship during the period of the warranty.

Additional specifications

Business Segment	Premium Home
Business filter	cMPS
Cartons per layer	16
Cartridge Colors	Yellow
Color starter yield	420
Color yield	800
Compatibility headline	HP 937 ink cartridges work with:
Component type	Cartridges
Count of layers in pallet	11
Country of origin	Made in Malaysia, Singapore
Operating temperature range	59 to 95°F
Package count	1
Page yield (color)	800 standard pages in accordance with ISO/IEC 19752
Page yield (yellow)	(~800) pages
Page yield footnote	Tested in HP Officejet Pro 9100 series. Approximate average based on ISO/IEC 24711 or HP testing methodology and continuous printing. Actual yield varies considerably based on content of printed pages and other factors. For details see http://www.hp.com/go/learnaboutsupplies .
Print technology	HP Thermal Inkjet
Product subgroup	Standard Capacity Ink Cartridges
Segment (filter)	Premium Home
Selectability	937
Storage temperature range	32 to 113°F
Subgroup	Standard Capacity Cartridges
UNSPSC code	441031052
Warranty	HP's ink cartridges and printheads are warranted to be free from defects in materials and workmanship during the period of the warranty. This warranty pertains to the product when used in its designated HP or authorized OEM printing device. HP will, at HP's option, either refund the purchase price or replace products that prove to be defective. Visit the HP online support web site http://www.hp.com/support for a list of support phone numbers and conditions or return to your point of purchase.
Weight	~0.04 kg
Weight	~0.08 lb

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Mar 04, 2024 4:58 PM UTC+0000