Azure All-Purpose Surface & Glass Cleaner



Applications:

Use on all glass and hard surfaces. Dilute with unheated tap water according to the dilution rates listed below. Recommended for use with a squeegee. If not available, then apply evenly on surface to be cleaned and wipe off with lint free cloth or paper towel.

Benefits:

- · Suitable for all glass surfaces, mirrors, chrome, stainless steel and any hard surfaces
- · Acts as a dust collector when sprayed lightly on a microber cloth
- · Works fast less wiping
- Ammonia-free
- · Streak-free shine

Codes:

 Product Code: 50201

• UPC: 0 56069 50201 6

Specifications:

Colour	Blue
DIN	No
Odour	Mild
рН	10.8 - 11.3
Viscosity	Not determined
Solvent	No
Phosphates	No
WHMIS	No
ECOLOGO	Yes
Food Safe	Yes
Kosher	Yes
Shelf Life	Up to 3 years after manufacturing

Dilution Rates:

Normal Cleaning

1:40



UL ECOLOGO (UL 2759) / **Heavy Duty Cleaning**

1:16

Available Formats:



Packaging:

Bottle: 5.8" x 5.8" x 12.3" (14.7 x 14.7 x 31 cm)

10 lbs (4.5 kg)

Box: 11.6" x 11.6" x 12.9"

40 lbs (18 kg) 4 per case





