



HP DesignJet XT950 36-in Multifunction Printer (2Y9H3F)



Overview

The world's most efficient A3-A1 printing experience to boost productivity[1]

Boost productivity with the world's most efficient A3-A1 experience. [1] Do it all—print multi-size CAD and renders with the integrated input/output tray. Save time with HP Click. And go beyond with this robust and compact plotter.

MOST EFFICIENT[1]—Save time, get through more jobs

Pick up your jobs quickly and simply—stacker holds up to 40 pages flat for easy collection.[2]

GO BEYOND—Meet office and environmental needs

Advance environmental goals—printer is made with at least 35% recycled plastics[4] and recyclable supplies[5].

CONNECTED—Secure and seamless collaboration

Save time with HP Click—print in fewer steps and avoid reprinting with print preview.

[1] The HP DesignJet T950 is faster than its main competitors: 44% faster than competitor A and 43% faster than competitor B in end-to-end performance, including job preparation with printing software, processing, printing, and collection. Testing performed by Sogeti, April 2023. Detailed test report is available upon request.

[2] Based on test results using A1 size, plain paper, and standard configuration. Stacking capacity is subject to paper type, printed file and ambient conditions.

[4] Declared %RCP content is based on the quantity and weight of parts made with RCP resin over the total plastic parts.

[5] Program availability varies. See <https://www.hp.com/go/recycle>

Specifications

Print quality color (best)	Up to 2400 x 1200 optimized dpi
Functions	Print, copy, scan
Connectivity, standard	Gigabit Ethernet (1000Base-T), Wi-Fi 802.11b/g/n
Software included	HP Click for Windows and macOS, HP app for Windows, macOS, Android, and iOS
Technical features	A3 input tray;Stacker;A3 sheet organizer;1- click scan/copy;Auto-power on/off scheduler;Max. resolution 2400 x 2400 dpi;HP Wolf Pro Security;130/300 ml cartridges;HP Flex Tech Inks
Energy star certified	Yes
Scan file format	JPEG, PDF, TIFF
Scan input modes	Scan to email, network, and USB. Scan to cloud, computer, and mobile through HP app.
Scanner type	Sheetfed, CIS (Contact Image Sensor), media jam detection sensor, front feed scanning method
Minimum dimensions (W x D x H)	1407 x 720 x 967 mm
Minimum dimensions (W x D x H)	55.4 x 28.3 x 38.1 in
Weight	71 kg
Weight	156.5 lb
Power consumption	35 W (printing), <11 W (ready), <3.5 W (sleep), <0.1 W (standby). Auto-scheduled printer on/off usage.
Environmental certification	ENERGY STAR, EPEAT, UL ECOLOGO® certified inks, CE marking (including WEEE, RoHS, REACH, ErP). In compliance with applicable WW RoHS materials restriction requirements.
What's in the box	HP DesignJet XT950 MFP, printhead, introductory ink cartridges, printer stand, spindle, guide, warranty flyer, power cord

Additional specifications

Acoustic power emissions (active, printing)	5.8 B(A) (operating), <3.4 B(A) (idle)
Acoustic pressure emissions	42 dB(A) (operating), <16 dB(A) (idle)
Color(s) of printing supplies	Cyan, magenta, yellow, matte black
Copy reduce / enlarge settings	50 to 400%
Datasheet photo 1	AHID/ade012476455a8c902318555b2b3ace40fad8fda
Dynamic security	Dynamic security enabled printer
Eco label	ENERGY STAR® certified; EPEAT registered
Electromagnetic compatibility	Compliant with Class B requirements, including: USA (FCC rules), Canada (ICES), EU (RED Directive), Australia (ACMA), New Zealand (RSM), China (CCC), Japan (VCCI); Korea (KCC)
Finished output handling	Sheet feed, roll feed, front-loading input tray (100 sheet capacity), sheet organizer (50 sheet capacity[5]), stacker (40 sheet capacity[5]), automatic horizontal cutter
HP ePrint capability	Yes
Ink drop	6 pl (C, M, Y); 12.6 pl (mK)
Ink types	Pigment-based (C, M, Y, mK)
Internal Storage	None
Line accuracy	±0.1%[2]
Linear scan speed	Up to 3.81 cm/sec (color, 200 dpi), up to 11.43 cm/sec (grayscale, 200 dpi)
Linear scan speed	Up to 1.5 in/sec (color, 200 dpi), up to 4.5 in/sec (grayscale, 200 dpi)
Maximum media thickness	Up to 0.8 mm
Maximum optical density (black)	15 L* min/1.7 D[3]
Maximum scan length	7 m[4]
Maximum scan length	23 ft[4]
Media sizes standard (metric rolls)	369 to 914 mm
Media sizes standard (sheets, rolls)	14.5 to 36 in
Media sizes supported	Input tray: A, B; Manual feed: A, B, C, D, E
Media sizes supported	Input tray: A4, A3; Manual feed: A4, A3, A2, A1, A0
Media sizes, custom	Front-loading input tray: 210 x 279 to 305 x 457 mm; Manual feed: 210 x 279 to 914 x 1676 mm
Media sizes, custom	Front-loading input tray: 8.3 x 11 to 12 x 18 in; Manual feed: 8.3 x 11 to 36 x 66 in
Media thickness	Up to 0.03 in
Media thickness	Up to 11.8 mil

Media thickness (metric)	Up to 0.3 mm
Media types	Bond and coated paper (bond, coated, heavyweight coated, plain, bright white, blueprint), technical paper (natural tracing), film (clear, matte), photographic paper (ID satin, ID gloss), self-adhesive (adhesive matte/gloss, adhesive polypropylene gloss), Polypropylene (matte)
Media weight, recommended	60 to 280 g/m ² (roll/manual feed); 64 to 220 g/m ² (front-loading input tray)
Media width, maximum	36 in
Media width, maximum	914 mm
Memory	2 GB
Model size	914 mm
Model size	36 in
Network ready	Standard
Non-Operating Humidity Range	0 to 95% RH
Non-printable area (cut-sheet)	5 x 5 x 5 x 5 mm
Non-printable area (cut-sheet)	0.2 x 0.2 x 0.2 x 0.2 in
Non-printable area (roll media)	0.2 x 0.2 x 0.2 x 0.2 in
Non-printable area (roll media)	5 x 5 x 5 x 5 mm
Number of print cartridges	4 (C, M, Y, mK)
Operating altitude	Up to 3000 m
Operating altitude	Up to 9843 ft
Operating humidity range	20 to 80% RH
Operating temperature range	5 to 40°C
Operating temperature range	41 to 104°F
Orderable supplies	HP Original Ink: HP 738 cartridges (Black, Cyan, Magenta, Yellow), and HP 739 printhead
Package dimensions (W x D x H)	62 x 24.8 x 30.7 in
Package dimensions (W x D x H)	1575 x 630 x 780 mm
Package weight	213.8 lb
Package weight	97 kg
Playbook TS icon connectivity	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08201987.png
Playbook TS icon dimensions AiO	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08192862.png
Playbook TS icon display AiO	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08727006.png
Post consumer recycled plastic in hardware by weight of plastic	36%
Power	Input voltage (auto ranging): 100-240 V (±10%), 50/60 Hz (±3 Hz), 1.2 A max
Print Technology	Ink

Print cartridge volume delivered	300 ml, 130 ml
Print head nozzles	1376 per color; 5504 in total
Print heads	1 (C, M, Y, mK)
Print languages	TIFF, JPEG, URF, PDF, HP-GL/2, HP-RTL, CALS G4
Print multi-size files in one click	Yes
Print speed	21 sec/page for D size, 120 D size 24" x 36" prints per hour[1]
Print speed	21 sec/page on A1, 120 A1 prints per hour[1]
Print technology	HP Thermal Inkjet
Printer drivers included	Raster driver for macOS and Windows, HP-GL/2 driver for Windows
Printing path	Wi-Fi Direct, remote printing, Apple AirPrint and HP app for Android and iOS devices, Windows and macOS printer drivers, printing support for Chrome OS, print from USB pen drive
Product logos	AirPrint; CE marking; ENERGY STAR; EPEAT green; IPv6 Ready; Mac; Wi-Fi Certified; Windows 11 Compatible
Recommended media	HP Universal Bond Paper (FSC® certified)[6] (recyclable)[7];HP Coated Paper (FSC® certified)[6] (recyclable)[7];HP Heavyweight Coated Paper (FSC® certified)[6] (recyclable)[7]
Remote print enabled	Yes
Roll external diameter	5.5 in
Roll external diameter	140 mm
Roll maximum input	1
Roll maximum weight	13 kg
Roll maximum weight	28.6 lb
Safety	USA and Canada (CSA certified); EU (RED Directive, EN 62368-1 compliant); Singapore (PSB); China (CCC); Mexico (NYCE); Argentina (IRAM); India (BIS)
Scan resolution, optical	Up to 600 dpi
Scan size, maximum	914 mm x 2.77 m
Scan size, maximum	36 x 109 in
Scan size, minimum	127 x 127 mm
Scan size, minimum	5 x 5 in
Security features	HP Secure Boot, whitelisting, Security event logging, Disable network ports and protocols, SNMPv3, 802.1x compatibility, TLS/SSL, Semi-permanent-queue Erase, NTLM v2, HP Web JetAdmin, HP Security Manager, SIEM Integration
Storage	2.7 GB reprint queue
Storage temperature range	-13 to 131°F
Storage temperature range	-25 to 55°C
Supported Primary Applications	Line drawings; Renderings; Presentations; Maps; Posters
Technology logo 1	AHID/cce10ebbd356d96074154a12dc62032a64b058f3

Technology logo 2	AHID/60d2a69d632efba286c546dd6a2fcfdb5c3c9e1f
Technology logo 3	AHID/cd33e848211911e4369b10008531951b0aa3cde7
Technology logo 4	AHID/c51bf05ff1023abad6fda02c5a970763b91946f4
Technology logo 5	AHID/6615658f92b8dd21f3c5b78f3bea628bd257123b
Technology logo 6	AHID/0e41ea2a916263d4c3403cc03016fcaae7311969
Technology logo 7	AHID/1f8b1ff3a68a6ba2a0939f2536845c50fe9dec4f
Theoretical minimum line width	0.02 mm (via raster driver)
Theoretical minimum line width	0.0008 in (via raster driver)
UNSPSC code	43212107
UPC number	(B19) 196548380756; (B1K) 196548313334
Web address for additional information	https://www.hp.com/go/designjet-t950-mfp

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Nov 15, 2023 7:20 AM UTC+0000