

This USB-C to DisplayPort Adapter Converter is ideal for showing presentations, pictures, or other audio/video content from the USB-C port of a laptop or tablet to the DisplayPort input of a monitor, projector, or HDTV. This adapter supports up to a 4K (3840 x 2160) at 60Hz resolution, allowing it to deliver a high-quality video image to the connected display. The compact design of this adapter makes it perfect for BYOD (Bring Your Own Device) applications in education or corporate environments. This adapter is an ideal accessory for Apple® and other leading laptops and tablets.



Features and Benefits

- Supports resolutions up to 4K (3840 x 2160) at 60Hz
- Compatible with USB-C, Thunderbolt™ 3 and Thunderbolt™ 4 ports
- A reversible, symmetrical USB-C connector
- Compact, lightweight design
- Plug and Play—no driver required
- Compatible with the Apple® MacBook®, MacBook Air®, and MacBook Pro®

Features & Benefits

Supports resolutions up to 4K (3840 x 2160) at 60Hz	Compatible with USB-C, Thunderbolt™ 3 and Thunderbolt™ 4 ports
A reversible, symmetrical USB-C connector	Compact, lightweight design
Plug and Play—no driver required	Compatible with the Apple® MacBook®, MacBook Air®, and MacBook Pro®

Specifications

General Info

Product Line	C2G	UPC Number	757120269335
Country Of Origin	China	Application Sector	Residential, Commercial
Warranty Type	Lifetime	Type	Adapter

Dimensions

Product Width US	1.5 in	Product Height US	0.6 in
Product Length US	1.65 in	Cable Length	4.7 in

Listing Agencies / 3rd Party Agencies

CE Certified	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Video Resolution	4K 60Hz
-----------------	--------------------------	------------------	---------

Bend Radius	40 mm	Thickness	4 mm
-------------	-------	-----------	------

Cable Type	Adapter	Jacket Rating	VW-1
------------	---------	---------------	------

Adapter Rear	DisplayPort Female	Adapter Front	USB-C Male
--------------	--------------------	---------------	------------

Operating Temperature	0 C, 50 C	Voltage	0 to 30 V, 30, 0
-----------------------	-----------	---------	------------------
