

## USB4 40Gbps Cable (M/M) - USB-C, 8K 60 Hz, 240W PD Charging, Black, 1.2 m (4 ft.)

MODEL NUMBER: U521-1P2M-BK



USB4 40Gbps cable connects 2 devices with USB-C or Thunderbolt 3 ports, including 4K/8K displays, laptops, smartphones, docks and PCs.

### Features

#### USB4 Cable Streams Video and Processes Data at 40 Gbps, 8x Faster Than USB 3.0

This USB4 40Gbps cable (M/M) transmits across two bidirectional lanes, supporting speeds up to 40 Gbps, which is eight times faster than USB 3.0/3.1/3.2. Unlike previous USB generations, the USB4 40Gbps cable has the ability to allocate resources. Instead of splitting video and data equally between its two lanes, the U521-1P2M-BK allows the connected display as much bandwidth as it needs, while saving all remaining bandwidth for high-speed data transfers. This makes the cable perfectly suited for 4K or 8K video streaming and editing, as well as transferring large RAW video or CAD files.

#### Supports DisplayPort Alternate Mode for Unidirectional 80 Gbps Video Connections

By connecting a 4K or 8K display to a host device that supports DisplayPort Alt Mode 2.1, this cable can use both high-speed lanes to transmit 4K or even 8K video at 60 Hz in one direction at 80 Gbps maximum speed with 30-bit Deep Color, HDR and 4:4:4 chroma subsampling. Connected to a host that supports DisplayPort Alt Mode 1.4, the U521-1P2M-BK can transmit 8K at 30 Hz.

#### Backward Compatible with Legacy USB and Thunderbolt 3 Devices

Though both connected devices must support USB4 40Gbps for the cable to reach its full potential, the U521-1P2M-BK is backward compatible with USB 3.x, USB 2.0 and Thunderbolt 3 devices. It connects two USB-C devices, including MacBooks, Chromebooks, Windows laptops, Kindles, game consoles, smartphones, external hard drives, docking stations and wall chargers. It is compatible with all USB-C and Thunderbolt 3 devices, enabling use in existing installations while preparing for future upgrades.

#### PD Charging Cable Keeps the Connected Notebook, Laptop or Other Device at Capacity

The U521-1P2M-BK supports Power Delivery (PD) 3.1 charging of the connected PD Charging-compliant device. It carries power output up to 48V 5A (240W), which is sufficient for fast-charging and powering your MacBook or other mobile device, including the latest iPhone and other smartphones with a USB-C connector.

#### USB-IF Certification Ensures Rigorous Testing and Top-of-the-Line Performance

This cable meets the high standards of USB-IF (USB Implementers Forum, Inc.), a non-profit organization consisting of companies that developed the USB specification. Receiving USB-IF certification means the U521-1P2M-BK meets the industry's highest environmental, mechanical and electrical standards. It operates with your USB peripherals, adapters and cables with top efficiency and safety.

### Highlights

- Transfers large video and data files at speeds up to 40 Gbps - 8x faster than USB 3.0
- Converts audio/video signals from sources supporting USB-C DisplayPort Alt Mode
- Supports single 8K display or dual 4K displays at 60 Hz up to 80 Gbps
- PD Charging cable supports 240W power output for charging high-powered devices
- Backward compatible with USB 3.x, USB 2.0 and Thunderbolt 3 devices

### System Requirements

- Devices with USB-C or Thunderbolt 3 ports (USB4 40Gbps compatibility required to achieve USB4 40Gbps performance)
- DP 2.1 Alt Mode required for maximum video output capability (8K/60Hz)
- 240W PD Charging output is supported, but the actual charging performance of a connected device is dictated by the maximum power draw of the device itself

### Package Includes

U521-1P2M-BK USB4 40Gbps Cable (M/M), Black, 1.2 m (4 ft.)

## Specifications

OVERVIEW	
UPC Code	037332281159
Device Compatibility	Amazon Kindle; Chromebook; Computer; Laptop; Monitor/HDTV; Phone; Tablet; Video Game System
Technology	USB4
Country/Region	Global
Cable Type	Active
VIDEO	
Resolutions Supported	The U521-1P2M-BK is compatible with USB3.x/USB4/Thunderbolt hosts that support at least DisplayPort Alt Mode 1.4 and supports the following video output capabilities: <b>DP 2.1 Alt Mode Host</b> Up to 7680 x 4320 (8K) @ 60 Hz <b>DP 1.4 Alt Mode Host</b> Up to 7680 x 4320 (8K) @ 30 Hz
Supported Resolutions	3840x2160 (4K); 7680x4320 (8K)
Max Supported Video Resolution	7680 X 4320 @ 60HZ
Max Supported Color Depth	30-bit Deep Color
HDR Support	Yes
3D Video Supported	Yes
Chroma Sub Sampling	4:2:0; 4:2:2; 4:4:4
EDID Support	Yes
Bandwidth	40 Gbps; 80 Gbps (DP 2.0 cable)
DisplayPort Alt Mode	Yes
DSC Support	Yes
INPUT	
Maximum Input Amps	5.0
Maximum Input Watts	240
POWER	
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	3.1
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight



Powering Business Worldwide

TRIPP LITE  
SERIES

Latching or Gripping Connector	No
Angled Connector	No
<b>CHARGING</b>	
Total Charging Amps	5
Total Charging Watts	240
Standards	PD 3.1
Compatible Devices	Chromebook; Laptop; Smartphone; Tablet; Video Game Console
<b>PHYSICAL</b>	
Color	Black
Material of Construction	TPE
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	TPE
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.95MM
Wire Gauge (AWG)	34/30/23
Cable Length (ft.)	3.94
Cable Length (m)	1.20
Cable Length (in.)	47.2
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.22
Shipping Weight (kg)	0.10
Unit Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
Unit Packaging Type	Polybag
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10% to 85%, Non-Condensing
Storage Humidity Range	5% to 90%, Non-Condensing
Power Provided to Connected Device(s)	240W (48V/5A)
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB4 (up to 40 Gbps)



Powering Business Worldwide

TRIPP LITE  
SERIES

Data Transfer Rate	40 Gbps
Antibacterial	No
IP68 Rated	No
Displayport Specification	1.4; 2.1
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL 94
Product Compliance	CE (Europe); FCC Part 15 Class A (USA); RoHS; UKCA; WEEE
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.