

# Gigabit SFP to SFP Fiber Converter Datasheet

MODEL: MC230L



## Highlights


- Supports a variety of SFP module combination
- LED indicators provide an easy way to monitor network activity
- Supports hot-swapping
- Fits into a TL-FC1420 chassis

## Overview

MC230L is a gigabit fiber converter with 2 SFP slots, supporting the combined use of multiple SFP modules.

# Specifications

## Hardware Features & Performance

Product Picture		
Model	MC230L	
Standards	IEEE 802.3z	
Interface	2×Gigabit SFP Slots	
Transmission Distance	Depends on the inserted SFP module	
Transmission Media	Depends on the inserted SFP module	
Wave Length	Depends on the inserted SFP module	
Dimensions (W x D x H)	3.7 x 2.9 x 1.1 in (94.5 x 73.0 x 27.0 mm)	
Max Power Consumption	1.54 W	
Power Supply	5 V/0.6 A	
Certifications	CE, FCC	
Physical & Environment	Operating Temperature	0 °C to 50 °C (32 °F to 122 °F)
	Storage Temperature	-40 °C to 70 °C (-40 °F to 158 °F)
	Operating Humidity	10% to 90% RH non-condensing
	Storage Humidity	5% to 90% RH non-condensing