

Lenovo V14 G5 IRL

Featuring Intel® Core™ i7 processor, this laptop delivers powerful performance for demanding business applications, multitasking, and processing large datasets. Equipped with up to 32GB DDR5-5200 memory, users can seamlessly run multiple applications simultaneously without encountering slowdowns or performance bottlenecks. Additionally, up to 1TB SSD storage ensures rapid read and write speeds, enabling quick boot times, faster application loading, and smooth file access.



Redefining possibilities with powerful performance and groundbreaking on-device AI

Combining security and productivity features with a simple design, powerful technology, and all-day battery life, Lenovo V Series laptops are perfect for small business professionals who demand long-term performance and reliability.


The 1.5W dual stereo speakers deliver superior sound quality, beneficial for business professionals during video conferences, presentations, and multimedia playback. The HD 720p camera with a privacy shutter, ensures clear video quality for seamless communication and collaboration with remote teams or partners.

The discrete TPM 2.0 chipset ensures data remains safe and encrypted. For added security and convenience, an optional touch-style fingerprint reader integrated into the power button allows professionals to access sensitive data and systems swiftly and securely while on the go.

The 1.5W dual stereo speakers and dual-array microphones enable a wider soundstage, enhancing professionals' ability to discern audio from various directions.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo 300 Wireless Compact Mouse

- Smooth ergonomics for all-day comfort
- Wireless for enhanced work productivity
- Accurate and precise navigation



PN: WW : GX30K79401, NA : GX30K79402, WW (without battery) : GX30K85315

Lenovo Go 130W Multi-Port Charger

- Get the maximum power out of your charger
- On-the-go port expansion & charging
- Power multiple devices through easy interface connection



PN: GOA6130WUS, GOA6130WEU, GOA6130WUK

Lenovo V14 G5 IRL

Performance

Processor

Intel Core 3/5/7 Processor (Series 1)

Operating System

Windows 11 Pro
Windows 11 Home
Windows 11 Home Single Language

Graphics

Intel Graphics (integrated)

Memory ¹

Up to 32GB DDR5-5200 offering, 2x SO-DIMM

¹The max memory is based on the test results with current Lenovo memory offerings.

Storage ²

Up to 1x 1TB M.2 2242 PCIe NVMe SSD

²The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio

High Definition (HD) Audio
Stereo speakers, 1.5W x2
Dual-microphone array

Camera ^{*}

HD 720p, with privacy shutter

Battery ³

47Wh battery (up to 9.3 hr), Rapid Charge

³Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter ^{*}

65W round tip adapter
65W USB-C adapter, PD 3.0

Design

Display ⁴

14" FHD (1920x1080) TN 16:9 Anti-glare
- 250nit, 45% NTSC, 60Hz

14" FHD (1920x1080) IPS 16:9 Anti-glare
- 300nits, 45% NTSC, 60Hz

⁴IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Keyboard

6-row, spill-resistant

Touchpad

Mylar surface touchpad
62 x 104 mm (2.44 x 4.09 inches)

Dimensions ⁵

324.2 x 215.2 x 17.9 mm (12.76 x 8.47 x 0.70 inches)

⁵The system dimensions may vary depending on configurations.

Weight ⁶

Starting at 1.37 kg (3.02 lbs)

⁶The system weight is approximate and may vary depending on configurations

Color

Business black
Luna grey

Case material

PC-ABS (top)
PC-ABS (bottom)

Special Features

Modern Standby

Connectivity

Ethernet

Gigabit onboard Ethernet

WLAN + Bluetooth ^{*7}

802.11ax (Wi-Fi 6), Bluetooth 5.2
Up to Intel Wi-Fi 6 AX203, Bluetooth 5.2

⁷Bluetooth may operate at a lower version than hardware design depending on the factors such as operating system, driver, etc.

Ports

2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
1x USB-C (USB 5Gbps / USB 3.2 Gen 1), with USB PD (20W only) & DP 1.2
1x HDMI 1.4b
1x Ethernet (RJ-45)
1x Headphone / microphone combo jack (3.5mm)
1x Power connector

Docking

Docking support via USB-C

Security & Privacy

Security

Discrete TPM 2.0
Firmware TPM 2.0
Kensington Nano Security Slot
Touch style MOC fingerprint reader on power button*
Camera privacy shutter

Certifications

Green Certifications ^{8 9 10}

ENERGY STAR 8.0
ErP Lot 6
EPEAT Gold Registered
TCO Certified 9.0
RoHS compliant

⁸The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁹EPEAT registration and ENERGY STAR certification are dependent on system OS.

¹⁰EPEAT registration and TCO certification are only available for MT 83HD. EPEAT is registered where applicable, please see epeat.net for registration status by country.

Other Certifications

TÜV Rheinland Low Blue Light (Software Solution)
MIL-STD-810H