

**OVERVIEW**



1. Volume button	3. Card slot
2. Power button	4. USB-C 2.0

Notes:

- Card slot is for microSD card (WLAN model) or nano-SIM + microSD card (WWAN model)
- Headphone / microphone combo jack (3.5mm) (not shown on the sample product above)

## PERFORMANCE

### Processor

#### Processor Family

MediaTek Processor

#### Processor

Processor Name	Cores	Max Frequency	Processor Graphics
MediaTek Helio P22T	ARM Cortex A53 Octa-core	A53@2.3GHz / A53@1.8GHz	IMG PowerVR GE8320 GPU

### Operating System

#### Operating System<sup>[1]</sup>

Android™ 11 or later

Notes:

[1] For latest operating system and security patches deliver plan, please visit <https://support.lenovo.com/solutions/ht501098>.

### Graphics

#### Graphics

Graphics	Type	Memory
IMG PowerVR GE8320 GPU	Integrated	Shared

### Chipset

#### Chipset

MediaTek SoC (System on Chip) platform

### Memory

#### Max Memory

- 3GB soldered memory, not upgradable
- 4GB soldered memory, not upgradable

#### Memory Type

LPDDR4x

### Storage

#### Storage Support

- 32GB eMCP4x on systemboard
- 64GB eMCP4x on systemboard
- 128GB eMCP4x on systemboard
- microSD card, supports FAT32 up to 128GB, exFAT up to 2TB

#### Storage Type

Disk Type	Interface	Offering
Flash Memory	eMMC 5.1	32GB / 64GB / 128GB

### Removable Storage

#### Card Reader\*\*

- Nano-SIM + microSD card slot (WWAN models)
- microSD card slot (WLAN models)

### Multi-Media

#### Speakers

Dual speaker, Dolby® Audio™

#### Microphone

Dual-microphone array

## Camera

Front 5.0MP, fixed focus, face unlock, rear 8.0MP, autofocus, single LED flashlight

### VoiceCall

- Voice call<sup>[1]</sup>
- No support

Notes:

[1] Use of Voice call requires cellular data plan. Voice call functionality details may vary based on local operator network, data and messaging services. Please contact your carriers for details.

## Sensor

### Vibration Motor

Eccentric Rotating Mass (ERM)

### Sensors

- Accelerometer (G) sensor
- Ambient light sensor (ALS)
- Gyroscope sensor
- Hall sensor
- Proximity (P) sensor
- e-Compass

## Battery

### Battery

- Integrated Li-Polymer 7500mAh (minimum) / 7700mAh (typical) battery
- No battery

### Max Battery Life<sup>[1]</sup>

Models with battery:

Standby: 2 wks

Online video playback: 12 hr

Web browsing: 15 hr

Music playback: 22 hr

### Charging Time<sup>[2]</sup>

Models with battery: over 5.5 hr to fully charged

Notes:

[1] All battery life claims are approximate and based on internal testing under optimal laboratory and network conditions. Actual battery performance will vary depending on numerous factors including product configuration and usage, software, operating conditions, wireless functionality, power management settings, screen brightness and other factors. The maximum capacity of the battery will naturally decrease with time and usage.

[2] Charging data claim is approximate and based on internal testing under optimal laboratory. Actual result may vary owing to differences in product configuration, usage, software, operating conditions and other factors.

## Power Adapter

### Power Adapter

- Models (w/ battery, w/ power adapter): 5V/2A (10W) AC adapter, 100-240V, 50-60Hz
- Models (w/o battery, w/o power adapter): support USB-C® power adapter with PD 2.0 or PD 3.0 PPS protocol, power at 12V/3A

## DESIGN

## Display

### Display\*\*<sup>[1]</sup>

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Color Gamut	Key Features
10.3"	FHD (1920x1200)	Multi-touch	IPS	330nits	Anti-fingerprint	16:10	100% sRGB	TÜV Low Blue Light
10.3"	FHD (1920x1200)	Multi-touch	IPS	400nits	Anti-fingerprint	16:10	100% sRGB	TÜV Low Blue Light

### Touchscreen

Capacitive-type multi-touch, supports 10-point touch

Notes:

[1] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

## Input Device

### Pen

No pen (purchase separately)<sup>[1]</sup>

Notes:

[1] For details upon pen compatibility, please check the file "Lenovo® Android Tablet - Option Compatibility Matrix" from <https://support.lenovo.com/solutions/accs-guide>.

## Mechanical

### Dimensions (WxDxH)<sup>[1]</sup>

244.8 x 153.9 x 8.15 mm (9.63 x 6.05 x 0.32 inches)

### Weight\*\*<sup>[2]</sup>

Models	Weight
Models without battery	Starting at 360 g (0.79 lbs)
Models with battery	Starting at 460 g (1.01 lbs)

### Case Color

Abyss blue

### Case Material

Plastic + metal

### Buttons

- Power button
- Volume button

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

## CONNECTIVITY

### Network

#### WLAN + Bluetooth®

802.11a/b/g/n/ac dual band 1x1 Wi-Fi® + Bluetooth 5.0

#### WWAN

- 4G LTE
- No support

#### Cellular Bands

- NA models:  
 GSM: B2/B3/B5/B8  
 WCDMA: B2/B4/B5/B8  
 LTE: B2/B4/B5/B12/B13/B14/B17/B25/B29/B30/B66/B71
- Other models:  
 GSM: B2/B3/B5/B8  
 WCDMA: B1/B2/B4/B5(B6/B19)/B8  
 CDMA/EVDO: BCO  
 TD-SCDMA: B34/B39  
 LTE: B1/B2/B3/B4/B5(B19)/B7/B8/B20/B26/B28(a+b)/B34/B38/B39/B40/B41 (Full bandwidth)

#### Wi-Fi Direct

Support

**Wi-Fi Display**

Support

**FM Radio**

FM Radio

**Location Services\*\***

Models	Location
WLAN models	GPS + GLONASS
WWAN models	GPS + GLONASS + A-GPS

**Ports<sup>[1]</sup>****Standard Ports**

- 1x USB-C 2.0 (support data transfer and charging)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Card slot

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

**SERVICE****Warranty****Base Warranty\*\*<sup>[1]</sup>**

- 1-year carry-in service
- 1-year mail-in service
- 1-year courier service
- 2-year courier or carry-in service
- 2-year (2-yr battery) carry-in service
- 2-year (2-yr battery) courier or carry-in service

Notes:

[1] For warranty upgrade service, please go to <https://smartfind.lenovo.com/services>. To learn more details of warranty policy, please access <https://pcsupport.lenovo.com/warranty>.

**ENVIRONMENTAL****Operating Environment****Temperature**

Operating: 0°C (32°F) to 40°C (104°F)

**ACCESSORIES****Bundled Accessories****Bundled Accessories\*\*<sup>[1]</sup>**

- Film
- Folio case
- None

## Notes:

[1] For more compatible accessories, please check the file "Lenovo Android Tablet - Option Compatibility Matrix" from <https://support.lenovo.com/solutions/accs-guide>.

## SOFTWARE

### Preinstalled Software

#### Preinstalled Software

Google

## CERTIFICATIONS

### Green Certifications<sup>[1]</sup>

#### Green Certifications

- ENERGY STAR® 8.0
- RoHS compliant

## Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

### Other Certifications

#### Dust and Water Resistant<sup>[1]</sup>

IP52

#### Other Certifications\*\*

- TÜV Rheinland® Low Blue Light (Hardware Solution)
- TÜV Rheinland Low Blue Light (Software Solution)

## Notes:

[1] Testing result of Proofing.

- Feature with \*\* means that only one offering listed under the feature is configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

