






THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2



SPECIFICATION:

1. STANDARD:

UNIT TYPE:	MONITORED INPUT
ORIENTATION:	VERTICAL, 0U FULL
OUTLET QTY&TYPE:	(24)C13, (12)C19
INPUT VOLTAGE:	200-240VAC
INPUT CURRENT:	60A (48A DERATED)
BREAKER QTY&TYPE:	(6) 20AMP, DOUBLE-POLE
INPUT PHASE:	THREE-PHASE DELTA
RATED POWER:	17.3 KVA
INPUT PLUG:	IEC 60309 3P+E 9H 60A (IP44)
INPUT POWER CORD:	SEE SHEET 2 PART NUMBER TABLE
REGULATORY STANDARD:	RoHS COMPLIANT

2. ADDITIONAL:

THE G6 CONTROLLER IS NOT BACKWARDS COMPATIBLE WITH ANY LEGACY CONTROLLERS

3. ACCESSORIES:

- DOCUMENTATION KIT
- PRODUCT SAFETY WARNING SHEET

NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION


FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: **P36D31G-XX Y Z**

<p>XX: FINISHED GOOD COLOR</p> <p>BL =BLACK YL =YELLOW RD =RED BU =BLUE WH =WHITE GN =GREEN</p>	<p>Y: INPUT FEED TYPE</p> <p>1 =TOP-END FED 2 =BOTTOM-END FED</p>	<p>Z: INPUT CORD LENGTH</p> <p>A =1 METER B =2 METER C =3 METER</p>
---	---	---


PLUG/RECEPTACLE BLOCK



PLUG
IEC 60309, 3P 4W, 9H
IP44 (SPASHPROOF)
60A, 250V, 3-PHASE MAX RATED INPUT
48A DERATED



RECEPTACLES
C13/C15 COMBO
10A, 250V MAX RATED OUTPUT



RECEPTACLES
C13/C15/C19 COMBO
16A, 250V MAX RATED OUTPUT

<p>WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY</p>		<p>SIGN _____</p> <p>DATE _____</p> <p>PRINT _____</p>				
<p>TITLE</p> <p>INTELLIGENT SERIES PDU P36D31G-XXYZ CUSTOMER DRAWING</p>						
<p>ITEM REVISION NAME:</p> <p>DATASHEET FILE NAME:</p>						
<p>UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]</p> <p>Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0</p>		<p>MATERIAL/COLOR:</p> <p>N/A</p> <p>DRAWING NUMBER:</p> <p>P36D31G-XXYZ_DC</p>				
<p>00A</p>	<p>12/01/2023</p>	<p>NW</p>	<p>CSH</p>	<p>MJD</p>	<p>INITIAL RELEASE</p>	<p>P36D31G-XXYZ</p>
<p>REV</p>	<p>DATE</p>	<p>BY</p>	<p>CHK</p>	<p>APR</p>	<p>DESCRIPTION</p>	<p>ECN</p>
						<p>1</p>



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P36D31G	G6 MI PDU, 60AMP, (24) C13 (12) C19, IEC 60309 3P 4W 9H IP44-3M, TOP FED, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10'[+10"/-5"]	10.2kg



B

B

A

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	12/01/2023	NW	CSH	MJD	INITIAL RELEASE	P36D31G-XXYZ

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY	SIGN	
	DATE	
	PRINT	
TITLE: INTELLIGENT SERIES PDU P36D31G-XXYZ CONTROL DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:
 THIRD ANGLE PROJECTION		N/A
Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		DRAWING NUMBER: P36D31G-XXYZ_DC
DRAWN BY	DATE	SCALE
NW	12/01/2023	NONE
CHK	SCALE	
CSH	NONE	
SHT 2 OF 2		SCALE B

