

## OVERVIEW

Upgradeable Unit Level EC Monitored rPDUs provide reliable power distribution to critical IT equipment while delivering a comprehensive view of input level power usage via remote network access. Includes environmental monitoring capabilities to obtain real-time environmental metrics. Upgrade the hot-swappable monitoring device on select units to leverage new technologies and accommodate changing business needs.

### Benefits

- Reliable power distribution with local and remote power monitoring options offer quick access to critical power usage information to evaluate energy usage trends and maximize uptime.
- Environmental monitoring capabilities with the addition of optional environmental sensors ensure users have critical infrastructure data at their fingertips to prevent climate-related equipment failure and system downtime.
- Fault-Tolerant Daisy Chaining with RSTP simplifies intelligent rPDU connectivity and ensures data is reported even when a break in the network chain occurs. Supports up to 40 rPDUs.
- Every unit is 100% tested for reliability and functionality.
- Daisy-chain up to 50 devices on a single IP address and reduce deployment time with self-configuration of downstream devices.



## Part #: VP4N62A1

**Model Number:** MN05MDR1-15P3B8-6PS15D0H10-S

**Category:** Monitored

**Sub Category:** Unit Level

**Power Configuration:** 60A, 208V DELTA, 17.2kW

**Physical Configuration:** 19in / 483mm, Horizontal

**Product Summary:** rPDU, Monitored Unit Level EC, 60A, 208V DELTA, 17.2kW, Horizontal, (3) Locking IEC C13, (12) Locking IEC C19, 10ft power cord with 3P+E (IP67), Black Powder Coat.

**Monitoring:** Input and per Phase power monitoring with Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility display.

**Plug Form:**

3P+E (IP67)

**Receptacle:**Locking IEC C13  
(Quantity: 3)Locking IEC C19  
(Quantity: 12)**Chassis Color Options:**

To discuss color options, contact your local sales representative.

**Product Specification and Options****System Features**

<b>Monitoring</b>	Input and per Phase power monitoring with Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility display.
<b>Monitoring Level 1</b>	Aggregate - Total Unit Monitoring (kWh, W, VA, PF)  Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
<b>Monitoring Level 2</b>	Phase (AB, BC, CA) Monitoring (kWh, W, VA, PF, V, A) Line (A,B,C) Monitoring (A)  Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
<b>Monitoring Level 3</b>	Circuit / Breaker Monitoring (A)  Circuit/Breaker Current Measurements Independently Tested and Verified at 2% Accuracy
<b>Quantity Of Inputs</b>	1
<b>Voltage</b>	200-240V Delta
<b>Current</b>	60A x 3 Phase DELTA
<b>VA per Input (Load Capacity)</b>	17.2kW (208V)
<b>Frequency</b>	50/60Hz
<b>Over Current Protection</b>	(6) 20A Double Pole Magnetic Breakers
<b>Switch</b>	Breaker/Switch Combination
<b>LCD Touchscreen Display / Auto Oriented</b>	Yes
<b>Power Cable Wire Gauge</b>	6/4
<b>Power Cable Length</b>	10ft / 3m
<b>Power Entry Location</b>	Left Rear
<b>Plug Type</b>	IEC60309 3P + E, 60A, Watertight IP67
<b>Combined Total Receptacle/Socket Quantity</b>	15
<b>Receptacle/Socket Type #1</b>	U-Lock IEC C13
<b>- Quantity on Rear</b>	3
<b>- Quantity per Breaker</b>	1 - Breaker 1; 1 - Breaker 2; 1 - Breaker 3

- Quantity per Phase Combination	1
- U-Lock Color ID	6 Circuit = Orange, Green, Blue
- Style	Individual
- Voltage per Receptacle/Socket	208V
Receptacle/Socket Type #2	U-Lock IEC C19
- Quantity on Rear	12
- Quantity per Breaker Pair	2
- Quantity per Phase Combination	4
- U-Lock Color ID	6 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue
- Style	Individual
- Voltage per Receptacle/Socket	208V
Internal RMS Voltage Sensor	Yes
Internal RMS Current Sensor	Yes
Network Connection	Dual 10/100/1000Mbps Ethernet
Protocols Supported	DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RADIUS, RSTP, SSH, SMTP, SNMP (v1/v2c/v3), Syslog, TACACS+, Modbus TCP
Data Access Formats	CSV datalog, JSON API, JSON datalog
USB Support	Yes
IP Reset Button	Yes
Hard Reboot Button	Yes
Serial Connection	RS232 via RJ45
Remote Sensor RJ Connection Jacks	1 (Supports up to 16 Sensors)
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	19in / 483mm Horizontal Rackmount
19in Recess Mount	Yes
Country of Origin	USA, TAA Compliant and Buy American Act COTS Compliant
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	UL & c-UL Listed 62368-1
Chassis Dimensions (HxWxD)	3.4in x 17in x 12in
Shipped Weight	29lbs (13.15kg)