

# ThinkPad P16s Gen 2 (AMD)

Crafted to tackle even the most challenging tasks, this laptop is redesigned for modern professionals who require an advanced computing device. AMD Radeon 780M graphics and color accuracy of the 16" expansive display offers true-to-life working experience, allowing video producers and editors to deliver visually stunning content. Equipped with up to AMD Ryzen 7 PRO processors, it allows analytical data scientists to run resource-intensive algorithms and conduct sophisticated statistical analysis with speed and precision.



## Professional machines for advanced users

Designed for business users who tackle compute-intensive workflows. With professional-grade graphics and powerful, multi-core processors, Lenovo sets the standard for mobile workstations and ensures best-in-class reliability even when you're away from the office.

It is an ultimate productivity partner, combining up to 64GB LPDDR5 memory and up to 2 TB SSD storage options. Seamlessly switch between multiple applications, run virtual machines, and handle large-scale projects without a hiccup.

Data scientists, statisticians, and analysts dealing with extensive datasets can rely on the onboard up to 64GB LPDDR5 memory and up to 2TB SSD storage for handling resource-demanding software with reduced loading times.

Trust the integrated AMD Radeon 780M graphic feature for faster rendering times for video effects, transitions, transformations and 3D elements.

## Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



### Premier Support

- Talk directly with advanced technical support agents
- Support for software & hardware
- Next business day onsite repairs

## Accessories

### Lenovo Powered USB-C Travel Hub

- Connects to a PC through a single USB-C cable which also recharges the device
- Connect to an external display with HDMI or VGA, and other peripherals with 2x USB ports
- Compact 183x100mm (7.2x4") design with integrated cable management



PN: 4X90S92381

### Lenovo Essential Wireless Keyboard & Mouse Combo

- Simple design that is comfortable for all day use and tough enough to handle spills
- Convenient and easy to use wireless connection
- Quality typing experience with quiet key strokes and a full-size number pad



PN: 4X30M39458 - US English

# ThinkPad P16s Gen 2 (AMD)

## Performance

<b>Processor</b> AMD Ryzen 5/7 PRO 7040U Series Processor
<b>Operating System</b> Windows 11 Pro Windows 11 Home Windows 11 Home Single Language Windows 11 DG Windows 10 Pro 64 Fedora Linux Ubuntu Linux LTS
<b>Graphics</b> AMD Radeon 740M Graphics (integrated) AMD Radeon 780M Graphics (integrated)
<b>Memory</b> 16GB LPDDR5, soldered 32GB LPDDR5x, soldered 64GB LPDDR, soldered
<b>Storage <sup>1</sup></b> Up to 1x 2TB M.2 2280 PCIe NVMe SSD
<sup>1</sup> The storage capacity supported is based on the test results with current Lenovo storage offerings.
<b>Audio</b> High Definition (HD) Audio Stereo speakers, 2W x2, Dolby Atmos Dual-microphone array, 360° far-field, Dolby Voice
<b>Camera <sup>*</sup></b> HD 720p, with privacy shutter FHD 1080p + IR hybrid, with privacy shutter and Ultrasonic Human Presence Detection 5.0MP + IR discrete, with privacy shutter and Ultrasonic Human Presence Detection
<b>Battery</b> 52.5Wh or 86Wh battery, 52.5Wh battery supports Rapid Charge
<b>Power Adapter <sup>*</sup></b> 65W USB-C adapter, PD 3.0 65W USB-C slim adapter, PD 3.0 100W USB-C slim adapter, PD 3.0

## Design

<b>Display <sup>2</sup></b> 16" WUXGA (1920x1200) IPS Anti-glare 16:10 - 300nits, 45% NTSC - 300nits, 45% NTSC, touch - 400nits, 100% sRGB, low power, Eyesafe  16" WQUXGA (3840x2400) OLED ARAS 16:10 - 400nits, 100% DCI-P3, Eyesafe  <sup>2</sup> IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.
<b>Keyboard</b> 6-row, spill-resistant, numeric keypad, optional backlight
<b>Touchpad</b> TrackPoint and glass-like Mylar surface touchpad 67 x 115 mm (2.64 x 4.53 inches)
<b>Dimensions <sup>3</sup></b> Integrated graphics models: 361.98 x 255.5 x 20.5 mm (14.25 x 10.06 x 0.81 inches) NVIDIA graphics models: 361.9 x 255.5 x 21.1 mm (14.25 x 10.06 x 0.83 inches)  <sup>3</sup> The system dimensions may vary depending on configurations.
<b>Weight <sup>4</sup></b> Starting at 1.71 kg (3.77 lbs)  <sup>4</sup> The system weight is approximate and may vary depending on configurations
<b>Color</b> Storm grey Villi black
<b>Case material</b> Aluminium or PC 50% GF + PC 20% CF (top), PPS (bottom)

## Connectivity

<b>Ethernet</b> Gigabit onboard Ethernet
<b>WLAN + Bluetooth <sup>*</sup> <sup>5</sup> <sup>6</sup></b> AMD Wi-Fi 6E RZ616, 802.11ax, Bluetooth 5.3 Qualcomm NFA-725A Wi-Fi 6E, 802.11ax, Bluetooth 5.3  <sup>5</sup> Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.  <sup>6</sup> Bluetooth 5.3 operation requires Windows 11.
<b>WWAN <sup>*</sup></b> Up to 4G LTE CAT16 <sup>*</sup>
<b>NFC</b> Near Field Communication <sup>*</sup>
<b>Ports</b> 2x USB 3.2 Gen 1 (one Always On) 1x USB-C 3.2 Gen 2 (data, PD 3.0, DP 1.4) 1x USB4 40Gbps (data, PD 3.0, DP 1.4) 1x HDMI 2.1, up to 4K/60Hz 1x Ethernet (RJ-45) 1x Headphone / microphone combo jack (3.5mm) 1x Security keyhole 1x Smart card reader <sup>*</sup> 1x Nano-SIM card slot (WWAN support models) <sup>*</sup>
<b>Docking</b> Docking support via Thunderbolt or USB-C
<b>Security</b> Discrete TPM 2.0 Kensington Nano Security Slot Smart card reader, supports ISO 7816 and EMV <sup>*</sup> Touch style MOC fingerprint reader <sup>*</sup> Camera privacy shutter <sup>*</sup> IR camera for Windows Hello (facial recognition) <sup>*</sup> Glance by Mirametrix Ultrasonic Human Presence Detection <sup>*</sup>

## Manageability

<b>System Management <sup>*</sup></b> AMD PRO Manageability 2.0
<b>Certifications</b>  <b>Green Certifications <sup>7</sup> <sup>8</sup> <sup>9</sup></b> EPEAT Gold Registered ENERGY STAR 8.0 TCO Certified 9.0 RoHS compliant  <sup>7</sup> The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.  <sup>8</sup> EPEAT registration and ENERGY STAR certification are dependent on system OS.  <sup>9</sup> EPEAT is registered where applicable, please see epeat.net for registration status by country.
<b>Other Certifications</b> Eyesafe Certified 2.0 <sup>*</sup> TÜV Rheinland Low Blue Light <sup>*</sup> MIL-STD-810H

Items with \* are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2024 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.