

HPE NVMe High Performance Read Intensive EDSFF E3.S Solid State Drives

HPE 7.68TB NVMe Gen5 High Performance Read Intensive E3S EC1 PS1010 SSD (P70395-K21)



What's new

- Offer 3.84 TB, 7.68 TB, and 15.36 TB storage capacities for our next gen EDSFF E3.S SSDs
- Offer better protection with support for Security Protocol and Data Model (SPDM).
- Offer Self-Encrypting Drive (SED) Federal Information Processing Standards (FIPS 140-3) specific E3.S SSDs.

Overview

Do you need to accelerate the performance of your read intensive applications?

HPE NVMe High Performance Read Intensive (RI) Enterprise and Datacenter Standard Form Factor (EDSFF) E3.S Solid State Drives (SSDs) are best suited for applications requiring a strong blend of high read IOPS, low latency, and high endurance at a strong price point. NVMe SSDs communicate directly to applications via the PCIe Gen 5 bus to boost I/O bandwidth and reduce latency.

HPE NVMe High Performance RI EDSFF E3.S SSDs replace the traditional 2.5 inch small form factor SSD while supporting greater density of NVMe drives. It provides high-performance data transfers at rates faster than SAS or SATA SSDs. Designed to utilize the high bandwidth of PCIe Gen 5 on servers with workloads high in reads such as read caching, web servers, and boot/swap.

Features

High Performance and Exceptional Reliability for Faster Business Results

HPE NVMe High Performance Read Intensive Enterprise and Datacenter Standard Form Factor (EDSFF) E3.S Solid State Drives (SSDs) are ideal for databases, artificial intelligence, machine learning, and high performance servers application.

Achieve higher IOPS and lower latency to enhance the performance of your enterprise servers while maintaining data accuracy with full data-path error detection.

Improved thermals, power, and scalability provide better system efficiency for high I/O applications.

Faster PCIe Gen 5 technology only available with EDSFF E3.S SSDs.

Improved Design and Efficiency for increased performance on Gen 11 Servers

Dramatically increase density with a 1U server that can fit 20 E3.S or 10 E3.S 2T drives, or a 2U server that can fit 36 E3.S or 18 E3.S 2T drives.

Improved power management and density while utilizing less power.

Technical specifications

HPE 7.68TB NVMe Gen5 High Performance Read Intensive E3S EC1 PS1010 SSD

Product Number	P70395-K21
Lifetime writes	18,922
Endurance DWPD (Drive Writes Per Day)	1.35
Read IOPS	Random Read IOPS (4KiB, Q=16)=267,567 Max Random Read IOPS (4KiB)=1,187,283@Q256
Write IOPS	Random Write IOPS (4KiB, Q=16)=413,609 Max Random Write IOPS (4KiB)=413,886@Q256
Power (Watts)	21.56
Plug type	Hot pluggable
Height	7.5 mm
Platform supported	HPE Storage Platforms, see QuickSpecs for more information
Product dimensions	20 x 25.4 x 11.6 cm
Weight	0.54 kg
Warranty	HPE Solid State Drives and Add-In Cards have a standard 3/0/0 warranty Customer Self Repair (CSR) subject to maximum usage limitations. Maximum usage limit is the maximum amount of data that can be written to the drive. Drives that have reached this limit will not be eligible for warranty coverage.



For additional technical information, available models and options, please reference the QuickSpecs

Make the right purchase decision.
Contact our presales specialists.

[Call for availability](#)



Chat now (sales)



Share now



Get updates

HPE Services

No matter where you are in your transformation journey, you can count on HPE Services to deliver the expertise you need when, where and how you need it. From strategy and planning to deployment, ongoing operations and beyond, our experts can help you realize your digital ambitions.

Advisory & Professional services

Experts can help you map out your path to hybrid cloud and optimize your operations.

Managed services

HPE runs your IT operations, giving you unified control, so can focus on innovation.

Support services

Optimize your entire IT environment and drive innovation. Manage day-to-day IT operational tasks while freeing up valuable time and resources.

- **HPE Complete Care Service:** a modular service designed to help optimize your entire IT environment and achieve agreed upon IT outcomes and business goals. All delivered by an assigned team of HPE experts.
- **HPE Tech Care Service:** the operational service experience for HPE products. The service provides access to product specific experts, an AI driven digital experience, and general technical guidance to help reduce risk and search for ways to do things better.
- **HPE Multivendor Services:** Single point of accountability for managing on-site hardware and software support for multivendor products. HPE experts help manage your IT across technologies and platforms for HPE and non-HPE technologies, acting as the single point of contact for your IT operational needs.

Lifecycle Services

Address your specific IT deployment project needs with tailored project management and deployment services.

HPE Education Services

Training and certification designed for IT and business professionals across all industries. Create learning paths to expand proficiency in a specific subject. Schedule training in a way that works best for your business with flexible continuous learning options

Defective Media Retention is optional and allows you to retain Disk or eligible SSD/Flash Drives replaced by HPE due to malfunction.

HPE GreenLake

HPE GreenLake edge-to-cloud platform is HPE's market-leading as-a-Service offering that brings the cloud experience to apps and data everywhere – data centers, multi-clouds, and edges – with one unified operating model, on premises, fully managed in a pay per use model.

If you are looking for more services, like **IT financing solutions**, please [explore them here](#).

Visit **HPE.com**

