

ThinkVision T65

PERFORMANCE

Display Size

65"

View Area

1428.5x803.5 mm

Panel

In-Plane Switching

Backlight

DLED

Aspect Ratio

16:9

Resolution

3840x2160

Pixel Pitch

0.3720x0.3720 mm

Dot / Pixel Per Inch

67 dpi

View Angle (H / V)

178° / 178°

Response Time

8ms

Color Support

1.07 Billion

Refresh Rate

60Hz

Brightness

400 cd/m²

Contrast Ratio

1200:1

Color Gamut

85% NTSC, 99% sRGB

Screen Surface Treatment

Anti-glare

Curvature

None

Camera

Detachable 4K Camera

Microphone

8x, Array

Speakers

15Wx2

Power Consumption (Typical / Maximum)

199W / 251W

Power Adapter

Integrated

Touchscreen

20-point IR Touch

Smart System

Android™ 9.0 / 4x A73 Cores / 4 GB / 64 GB / Remote Control with Battery

DESIGN

Stand

None

Case Color

Raven Black

Side Bezel Width

28.84 mm

Mounting

Supports VESA mount 600 x 400 mm

ThinkCentre® M Series Support

None

Dimensions (WxDxH)

1527.5 x 87.8 x 952.0 mm (60.14 x 3.42 x 37.48 inches)

Packaging Dimensions (WxDxH)

1660 x 220 x 1045 mm (64.74 x 8.58 x 40.76 inches)

Weight

40.5 kg (89.29 lbs)

Packaging Weight

52.5 kg (115.74 lbs)

CONNECTIVITY

USB Port

3x USB 3.0, 2x USB-C® 3.0, 1x USB 2.0, 1x USB-B (Touch), 1x USB-B (Touch Out)

Video Connector

4x HDMI® 2.0, 1x HDMI® 2.0 out, 1x DP 1.2, 1x VGA, 1x AV, 2x USB-C® 3.0

Network Connectivity

1x RJ45 In, 1x RJ45 Out, Bluetooth® 5.0+802.11ac (2.4 and 5 GHz bands)

SERVICE

Base Warranty

3-year

CERTIFICATIONS

Environmental Certification

RoHS Compliant

Ergonomic Certification

TÜV Rheinland® Low Blue Light, TÜV Rheinland® Flicker Free

Sync Technology

None

PSREF

Product Specifications
Reference

Special Features

- HDR10 Compliance
- 1x Human Detection Sensor
- 1x Ambient Light Sensor

SOFTWARE

Operating System

Android™ 9 (Pie)

ACCESSORIES

Video Cables

HDMI® Cable, USB Type-A to Type-B Cable

MODEL

Announce : 2024-02-06

Date

EAN /

UPC / : 0197531552785 / 197531552785 / None

JAN



Product image is a sample, it may not match the real color of this model

Premium Care - Advanced Support from Real People. Real Fast.

REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.

HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.

PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.



Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.



Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade



Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

PSREF
Product Specifications
Reference