




HP 32GB DDR5 5600 SODIMM Memory (ALOM7AA)

Overview

Expand Your Productivity

Upgrade your capacity for uninterrupted, undeterred, unbelievably fast speed. Upgrading to 32 GB DDR5 5600MHz SODIMM to open up your workspace to its full potential. Make way for all the things you need to get done, at once, with state-of-the-art processing power.



Maximize Your Capacity

Expand your laptop's memory for speed, space, and seamless productivity. With the new 32 GB DDR5 5600MHz SODIMM, you'll have plenty of room to work and play and multitask with ease^[1]. Open your workspace for more and start thinking about computer memory less.

Tested. Trusted. Warrantied

Invest in genuine HP-branded memory that's tested^[2], certified, and built for HP laptops. Robust and reliable, this product even comes with an extensive 3-year warranty, just in case.

More Power, Less Drain

Upgrading to 32 GB DDR5 5600MHz SODIMM doesn't just expand your RAM, it increases the overall computing power of your HP laptop—opening the floodgates of speed and giving every part more room to think. It's also extremely efficient, so all that power doesn't drain your battery faster or heat everything up.

Build for a better tomorrow

Innovating with purpose and intention to drive impactful, positive, lasting change.

Features

Power Through the Day

This speedy 32GB 5600MHz DDR5 RAM lets you multitask, toggle, and shift between all your applications quickly. Upgrade now and leave waiting behind.

Easy Installation

Follow the extremely easy visual steps to install your brand new memory in minutes. You don't need to contact IT or take in your laptop, just follow the instructions and get ready to power up a new level of speed.

HP Quality

Engineered to ensure quality and reliability that comes with decades of innovation. Get the memory you can trust.

HP-Tested with a 3-Year Warranty

If you trust your memory, you can stay focused on what matters. Invest in genuine HP-branded memory that's tested and certified for HP laptops, with a handy 3-year warranty, just in case. ^[2]

[1] Due to the non-industry standard nature of some third-party memory modules, we recommend HP branded memory to ensure compatibility. If you mix memory speeds, the system will perform at the lower memory speed.

[2] HP Total Test Process testing is not a guarantee of future performance under these test conditions.

Specifications

| | |
|-----------------------------------|------------------------------------|
| Minimum dimensions (W x D x H) | 70 x 30 x 3 mm |
| Minimum dimensions (W x D x H) | 2.76 x 1.18 x 0.12 in |
| Weight | 10 g |
| Weight | 0.02 lb |
| Package dimensions (W x D x H) | 232 x 148 x 10 mm |
| Package weight | 56 g |
| Sustainable impact specifications | 30% post-consumer recycled plastic |
| UPC number | 198701274216 |
| Manufacturer Warranty | HP Three-year limited warranty |
| What's in the box | Memory; Document; Tube; |

Additional specifications

| | |
|--------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Cartons per layer | 20 |
| Cartons per pallet | 100 |
| Compatibility | HP EliteBook 630 13.3 inch G11 Notebook PC; HP EliteBook 640 14 inch G11 Notebook PC; HP EliteBook 660 16 inch G11 Notebook PC; HP EliteBook 645 14 inch G11 Notebook PC; HP EliteBook 665 16 inch G11 Notebook PC; HP EliteBook 840 14 inch G11 Notebook PC; HP EliteBook 860 16 inch G11 Notebook PC; HP EliteBook 845 14 inch G11 Notebook PC; HP EliteBook 865 16 inch G11 Notebook PC; HP ZBook Power 16 inch G11 Mobile Workstation PC; HP ZBook Power 16 inch G11 A Mobile Workstation PC; HP ZBook Fury G11 Mobile Workstation PC; HP ZBook Firefly 14 inch G11 Mobile Workstation PC; HP ZBook Firefly 16 inch G11 Mobile Workstation PC; HP ZBook Firefly 14 inch G11 A Mobile Workstation PC |
| Compatible Operating Systems | Windows 10; Windows 11 |
| Datasheet photo 1 | AHID/4e1f24c67f7572e2f44a500a62e0d5d94e6a9c0d |
| Memory capacity maximum | 32 GB ^[2] |
| Memory type | DDR5 |
| Number of pins | 262 |
| Operating voltage | 1.1 V |
| Package dimensions (W x D x H) | 9.13 x 5.83 x 0.39 in |
| Package weight | 0.12 lb |
| Pallet (layers) | 5 |
| Pallet weight | 261.03 lb |
| Pallet weight | 118.4 kg |
| Products per pallet | 1800 |
| Products per pallet layer | 360 |
| Transfer rate | 5600 Mbps ^[1] |
| UNSPSC code | 32101602 |

[1] Data transfer rate may be lower depending on the platforms.

[2] Graphics chipset uses part of the total system memory (RAM) for graphics performance. System memory dedicated to graphics performance is not available for other use by other programs.

Disclaimer — Copyright

Actual product may vary from image shown.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Oct 24, 2024 8:05 AM UTC+0000