

ProductSheet

HP 218X High Yield Magenta Original LaserJet Toner Cartridge (W2183X)



Exceptional performance

HP TerraJet Toner Cartridges are designed for efficient toner use for less waste and outstanding quality printing with built-in security.[13,14]



Less energy consumption[8] and easy recycling[10]

Use an average of 7% less energy.[8] Use less energy when printing than previous generation cartridges.[8]

Truer-to-life colors. Higher efficiency toner[1,2]

Highly efficient toner particle design with protective shell and low-melt formula.

To protect your printer and your data[13]


With tamper-resistant proprietary firmware and secure chips, be confident they're genuine HP cartridges.[13]

Featuring

Precision output, page after page^[1,2]

Designed with the planet in mind^[3]

Meets eco-label emission criteria^[4]



Specifications

| | |
|---------------------------------------|--|
| Color(s) of printing supplies | Magenta |
| Print Technology | Laser |
| Supply type | Cartridges |
| Operating temperature range | 10 to 32.5°C |
| Storage temperature range | -20 to 40°C |
| Operating humidity range | 10 to 80% RH |
| Non-Operating Humidity Range | 10 to 95% RH |
| Compatibility | HP LaserJet Pro 3201 Printers; HP LaserJet MFP 3301 Printers |
| Product count per unit | 1 |
| Quantity per pallet | 300 |
| Quantity per European pallet | 216 |
| Cartons per pallet | 300 |
| UPC number | 195161016257 |
| Minimum dimensions (W x D x H) | 363 x 96 x 111 mm |
| Minimum dimensions (W x D x H) | 14.29 x 3.78 x 4.37 in |
| Package dimensions (W x D x H) | 363 x 96 x 111 mm |
| Package dimensions (W x D x H) | 14.29 x 3.78 x 4.37 in |
| Pallet dimensions (W x D x H) | 1100 x 986 x 1254 mm |
| Pallet dimensions | 43.3 x 38.8 x 49.4 in |
| Package weight | 0.74 kg |
| Package weight | 1.63 lb |
| Pallet weight | 243 kg |
| Pallet weight | 533 lb |
| What's in the box | HP Toner Cartridge |
| Manufacturer Warranty | HP's Premium Protection Warranty. This HP product is warranted to be free from defects in materials and workmanship. |

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

- [1] Standard print mode for HP Color LaserJet Pro and Enterprise series with HP TerraJet Toner Cartridges compared to predecessors. See hp.com/TerraJet/colors.
- [2] Premium mode offers more colors compared to Standard Mode; varies between cartridge series. See www.hp.com/TerraJet/colors.
- [3] Calculations of more pages printed per cartridge size in Original HP TerraJet Toner Cartridges compared to predecessors. See www.hp.com/TerraJet/tonersaving.
- [4] Size of HP TerraJet Toner Cartridges compared to predecessors. See www.hp.com/TerraJet/smaller.
- [8] HP calculations based on normalized Energy Star® TEC data of HP LaserJet Pro and Enterprise series with HP TerraJet Cartridges compared to predecessors. See www.hp.com/TerraJet/energysaving.
- [10] Program availability varies. See www.hp.com/hprecycle.
- [13] HP office-class printing systems are select Enterprise and Managed devices with FutureSmart firmware [4.5] and up, Pro devices, LaserJet models 200 and up, with respective Original HP Toner, PageWide and Ink Cartridges. Does not include HP integrated printhead cartridges. Digital supply-chain tracking, hardware, chips and packaging security features vary locally by SKU. See www.hp.com/cartridgesecurity.
- [14] See ISO/IEC 20243:2018 Open Trusted Technology Provider™ Standard Certification Register. See certification.opengroup.org/register/ottps-certification

Technical Specifications Footnotes

No Technical Specifications Footnotes

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

