

Plenum Signature Core™ Trunk Cable Assemblies

specifications

Signature Core™ Trunk Cable Assemblies shall allow for rapid deployment of high-density permanent links in a single assembly for data center applications requiring quick infrastructure deployment, such as main, horizontal, and zone distribution areas. These trunk cable assemblies shall optimize cable routing requirements to ensure efficient use of pathway space and significantly reduce installation time and cost. QuickNet™ Trunk Cable Assemblies are built with modular MPO connectivity and provide compatibility, flexibility and system performance in all permanent link applications. All trunk cable assemblies are factory terminated and tested to deliver verified optical performance and reliability for improved network integrity at speeds of 10/25/40/50/100G and beyond. Signature Core™ Trunk Cables support channel lengths 15 – 30% longer than traditional OM4/OM5 depending on the application (SR4, BiDi, SWDM4).



applications

Allows system designers to tailor configuration, reach and breakout construction to application requirements; to minimize waste, optimize cable management, speed deployment, improve flexibility and manageability for lower installation costs. Small diameter trunk cable assemblies use 30 – 40% less space which is ideal for high cable density applications.

construction

Cable type:	Indoor Small Diameter Trunk	
Cable jacket rating:	Optical Fiber Non-conductive Plenum (OFNP)	
Fiber types:	Multimode:	OM4+ 50/125µm
Connector types end 'A':	12-fiber – MPO Female or Male, 12-fiber – PanMPO™ Female or Male	
Connector types end 'B':	12-fiber – MPO Female or Male, 12-fiber – PanMPO™ Female or Male, Pigtail	
Fiber count:	12, 24, 48	
Jacket color:	OM4+	Aqua

optical properties

Maximum cable attenuation:	Multimode:	2.8dB/km at 850nm 1.0dB/km at 1300nm
Maximum connector insertion loss:	Ultra Multimode MPO:	0.25dB
Maximum connector return loss:	Multimode:	MPO 30dB

physical properties

Cable outside diameter (OD):	12-fiber: 4.5mm 24-fiber: 5.4mm 48-fiber: 6.2mm	
Cable Construction:	250µm Distribution Cable	
Minimum bend radius:	Under load: Static:	20 x Cable OD 10 x Cable OD
Cable tensile strength:	440N (100 lbs.)	
Cable compressive load:	100 N/mm	
Connector durability:	500 mating cycles*	
Breakout outside diameter:	2.0mm	
Breakout length:	1m	

*With proper cleaning and inspecting.

environmental properties

Operating temperature:	-20°C to + 70°C (-4°F to 158°F)
Storage and shipping temperature:	-40°C to +70°C (-40°F to 158°F)
Installation temperature:	-10°C to + 60°C (14°F to 140°F)

standards

Meets or exceeds:	ISO/IEC 1180, TIA/EIA-568-C.3, TIA-604-5 (FOCIS-5), TIC/EIA-568-C.1, GR-409-CORE, ICEA S-83-596 RoHS Compliant
--------------------------	---

Plenum Signature Core™ Trunk Cable Assemblies

part number configurator

Example: FYXTP77Y001F030 = OM4+ 12-Fiber HD Flex™ Indoor Small Diameter Trunk, Plenum, 1x12F PanMPO Female with 1m breakout to 1x12F PanMPO Female with 1m breakout, Polarity A, Ultra IL, Pulling Eye End A, 30 feet.

CHARACTER	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
EXAMPLE	F	Y	S	T	P	7	7	L	0	0	1	F	0	3	0

1 – Fiber
F = Fiber

2 – Cable Type
Y = Indoor small diameter trunk cable

3 – Fiber Type
S = OM4+ 50/125µm

4 – Fiber Count
T = 12 fibers
U = 24 fibers
W = 48 fibers

5 – Jacket Type
P = Plenum

6 – Connector Type (End A)
5 = 12-fiber MPO Female
6 = 12-fiber MPO Male
7 = 12-fiber PanMPO Female
8 = 12-fiber PanMPO Male

7 – Connector Type (End B)
5 = 12-fiber MPO Female
6 = 12-fiber MPO Male
7 = 12-fiber PanMPO Female
8 = 12-fiber PanMPO Male
U = Pigtail

8 – Construction/Performance
K = Method A, Ultra IL
L = Method B, Ultra IL


9 – 11 – Serial

12 – Unit of Measure
F = Feet
M = Meters

13, 14, 15 – Cable Assembly Length
015 - 999 Feet
005 = 300 Meters

Serial	Transition	Pulling Eye
001	HD Flex™	Yes
002	HD Flex™	No
003	HD Flex™ to pigtail	Yes
005	Standard	Yes
006	Standard	No
007	Standard to pigtail	Yes

small diameter trunk cable assembly detail



Please contact Panduit customer service for information on additional part number options.

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

PANDUIT®

For more information
Visit us at www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

© 2021 Panduit Corp.
ALL RIGHTS RESERVED.
Printed in the U.S.A.
FBSP170--WW-ENG
7/2021