

2N



2N Indoor View

Indoor station with a 7" touch display

The 2N Indoor View unit looks at home in even the most luxurious of penthouse apartments! It's advanced too - it offers widescreen HD video calls, can integrate with smart home systems, and supports video surveillance. Install it inside the wall, on the wall, or on a stand.

7" HD TOUCHSCREEN

Your customer will appreciate how easy it is to operate the unit on the large display. The home screen even provides the current weather forecast.

STYLISH DESIGN

A luxury penthouse deserves a great looking unit. Offer the 2N Indoor View to ensure you win your project.

VIDEO SURVEILLANCE

The resident can see what is going on in places where no intercom has been installed, and there is only an IP camera (e.g., a hallway, yard or garage).

FULL SCREEN VIDEO CALLS

We've enlarged the video call preview. This means residents can even read a courier's name tag with ease. Wide screen calls will be compatible only with some 2N intercoms.

FIRST CONFIGURATION FROM YOUR OFFICE

Save time and money. You can set up all the units in a project remotely without the need to travel to the installation site.

RESIDENTS' PRIVACY IN SAFE HANDS

The 2N Indoor View runs on our very own operating system. We've made sure that no one can listen in or record residents' conversations.

SMART HOME INTEGRATION

The resident can turn on the air-conditioning, lighting or call the lift directly from the display on their unit. The unit can send up to 3 different HTTP commands.

GREAT FOR RETROFIT PROJECTS

In addition to the classic Ethernet version, we also offer a Wi-Fi variant which is great for adding all these advanced features to places without network cabling.

Variants



2N Indoor View
Black
02087-001



2N Indoor View
White
02088-001



2N Indoor View Wi-Fi
Black
03134-001



2N Indoor View Wi-Fi
White
03135-001

Technical Parameters

Power Supply

| | |
|-----------------------------|-------------------------------|
| Type | 12V DC adapter or PoE 802.3af |
| Recommended power supply | 12V/1A |
| Reverse polarity protection | yes |

User Interface

| | |
|--------------|------------------------|
| Controls | capacitive touch panel |
| Display size | 7" |
| Resolution | 1024x600px |

Audio

| | |
|-----------------------|------------------------------------|
| Microphone | integrated |
| Speaker | integrated, 2W |
| Induction loop output | 600mV RMS |
| Codecs | G.711a/u, G.722, G.729, L16/16 kHz |

Video

| | |
|--------|-------|
| Codecs | H.264 |
|--------|-------|

Interface

| | |
|---------------------|--------------------|
| LAN | 10/100BaseT, RJ-45 |
| Recommended cabling | Cat5e or higher |

Wi-Fi (optional)

| | |
|-----------|--|
| Frequency | 2.4GHz and 5GHz |
| Standard | 802.11n and 802.11ac |
| Antenna | in-built |
| Important | Wi-Fi and ethernet cannot be used simultaneously |

Doorbell Input

| | |
|--------------------|----------------------------------|
| Input type | switching contact (button/relay) |
| Contact type | normally open (NO) |
| Contact parameters | up to 50V/5mA, DC |

Mechanical Parameters

| | |
|-----------------------------|----------------------------|
| Dimensions (W x H x D) | 7.6 x 6.18 x 1.97inch |
| Weight | 1.23lb |
| Operating temperature | 32°F to 122°F |
| Relative operating humidity | 10 to 90% (non-condensing) |
| Storage temperature | -4°F to 158°F |
| Recommended altitude | 0 to 6,500 ft |

Warranty

5-years warranty see
https://www.2n.com/en_GB/support/warranty-and-repairs

Member of the AXIS group



Axis Communications provides 2N sales and support for the Americas and APAC (excluding Japan).

2N.com