


# 5520 Series

## Highlights

- Fixed 24 and 48-port switches with gigabit and multi-gigabit support
- Choice of operating system (OS) with universal dual-persona hardware
- Intuitive and centralized cloud-based network management with ExtremeCloud™ IQ and ExtremeCloud IQ Site Engine
- Fabric-enabled operations with Extreme Fabric Connect for simplified and secure network provisioning and automation
- Front to back cooling and AC power supply input on all models
- Back to front cooling and DC power supply input option on specific models
- AC and DC Power Supply Unit (PSU) capable SKUs

## Key Hardware Features

- Choice of 10Gb and 25Gb modular uplink ports
- 30W, 60W and 90W PoE support for powering connected devices
- 200Gb per unit stacking of up to eight switches
- Hot-swappable, redundant power supplies and fans
- MACsec on access and modular uplink ports for secure link encryption
- Extended Edge Switching controlling bridge in support of V300/V400 edge devices
- Non-blocking, wire-speed design



## Universal Edge/Aggregation Switch Platform

The 5520 Series is a family of high-performance, feature-rich edge and aggregation switches designed for the next-generation digital enterprise. Available in 24 and 48-port 1 Gigabit models, 1/2.5/5 Gigabit multi-rate models, as well as, a 24-port 10 Gigabit model, the 5520 Series provides end-to-end secure network segmentation and advanced policy capabilities that can be deployed across a range of edge, aggregation, and wiring closet environments. As a universal hardware platform, the 5520 offers a user-selectable choice of Extreme's flagship switch operating systems for a uniquely flexible platform.

The 5520 supports 10Gb and 25Gb modular uplinks for flexible linkage to other switches or devices over a range of media. Extended Edge Switching controlling bridge is also available in support of V300/V400 edge devices, and select models offer a choice between Front to Back or Back to Front cooling. The 5520 Series offers 30W, 60W, and 90W PoE, making it an ideal wired backend for wireless APs or in support of next-gen powered Ethernet devices, such as digital signage, pan-tilt-zoom cameras, smart lighting, or point-of-sale terminals.

## Universal Hardware Platform

The 5520 comes with a dual-persona capability, allowing you to choose your OS. Either the Switch Engine (EXOS)<sup>1</sup> or Fabric Engine (VOSS)<sup>2</sup> OS can be selected at switch start-up or changed at a later stage. When selected, the switch assumes the features and capabilities of that OS.

5520 OS selection can also be automated with ExtremeCloud IQ so that the desired OS can be automatically loaded at switch start-up, facilitating remote OS enablement.

<sup>1</sup> Switch Engine is the new name for ExtremeXOS (EXOS) on all universal switch platforms, starting with Version 31.6.

<sup>2</sup> Fabric Engine is the new name for the VSP Operating System Software (VOSS) on all universal switch platforms, starting with Version 8.6.

---

## Cloud-Based Network Management

The 5520 can be managed by ExtremeCloud IQ and ExtremeCloud IQ Site Engine for centralized switch management, giving you a consolidated view of users, devices, and applications across wired and wireless networks for efficient inventory and network topology management. ExtremeCloud IQ enables zero touch provisioning, allowing you to quickly bring new 5520 switches online as well as select the OS persona.

Alternatively, 5520 on-box management can be done manually via a web-based GUI or generic command-line interface (CLI).

---

## Ethernet Fabric Services

The 5520 supports a variety of Ethernet Fabric services, including Extreme's Fabric Connect when running Fabric Engine and Extreme's IP Fabric when running Switch Engine. It also supports Fabric Attach for automated connection to either Layer 2 or Layer 3 Fabric services.

Extreme's Fabric Connect and IP Fabric enable the creation of virtualized networks that automate network operations, simplify network provisioning, and enhance security, all while reducing the strain on network and IT personnel.

## Power over Ethernet (PoE)

All 5520 models support 30W, 60W, and 90W PoE that conforms with IEEE 802.3bt. This enables the 5520 to address the needs of powered edge devices, while eliminating the need for additional electrical cabling and circuits. In addition, 5520 PoE models support perpetual and fast PoE for even more efficient and reliable powered edge device operation

---

## VIM Options for Flexible Uplinks

The 5520 supports Versatile Interface Modules (VIMs), providing flexible uplink capabilities with a single VIM slot. VIM options include four-port 10Gb or 25Gb modules that include LRM and 256-bit MACsec support.

---

## High-Performance Stacking

The 5520 Series supports high-speed 200Gb\* stacking when running Switch Engine via its two built-in QSFP28 stacking ports. Up to eight systems can be stacked using qualified QSFP+ direct attach cables and optical transceivers.

\*200Gb stacking available with Switch Engine 31.6

---

## Audio Video Bridging

The 5520 series supports IEEE 802.1 Audio Video Bridging (AVB) when running Switch Engine OS. This allows 5520 models to deliver reliable, real-time audio/video transmission over Ethernet, meeting the quality of service required for today's high-definition, time-sensitive multimedia streams.

## External Interfaces

Switch Model	Interfaces
5520-24T	<ul style="list-style-type: none"> <li>• 24 x 10/100/1000BASE-T ports               <ul style="list-style-type: none"> <li>◦ Full / Half-Duplex (autosensing)</li> <li>◦ MACsec-capable</li> </ul> </li> <li>• 2 x Stacking/QSFP28 ports* (unpopulated)</li> <li>• 1 x Serial console port (RJ-45)</li> <li>• 1 x 10/100/1000BASE-T out-of-band management port</li> <li>• 2 x USB A ports for management or external USB flash</li> <li>• 1 x USB Micro-B console port</li> <li>• 1 x VIM slot</li> </ul>
5520-24W	<ul style="list-style-type: none"> <li>• 24 x 10/100/1000BASE-T 802.3bt (90W) ports               <ul style="list-style-type: none"> <li>◦ Full / Half-Duplex (autosensing)</li> <li>◦ MACsec-capable</li> </ul> </li> <li>• 2 x Stacking/QSFP28 ports* (unpopulated)</li> <li>• 1 x Serial console port (RJ-45)</li> <li>• 1 x 10/100/1000BASE-T out-of-band management port</li> <li>• 2 x USB A ports for management or external USB flash</li> <li>• 1 x USB Micro-B console port</li> <li>• 1 x VIM slot</li> </ul>
5520-48T	<ul style="list-style-type: none"> <li>• 48 x 10/100/1000BASE-T ports               <ul style="list-style-type: none"> <li>◦ Full / Half-Duplex (autosensing)</li> <li>◦ MACsec-capable</li> </ul> </li> <li>• 2 x Stacking/QSFP28 ports* (unpopulated)</li> <li>• 1 x Serial console port (RJ-45)</li> <li>• 1 x 10/100/1000BASE-T out-of-band management port</li> <li>• 2 x USB A ports for management or external USB flash</li> <li>• 1 x USB Micro-B console port</li> <li>• 1 x VIM slot</li> </ul>
5520-48W	<ul style="list-style-type: none"> <li>• 48 x 10/100/1000BASE-T 802.3bt (90W) ports               <ul style="list-style-type: none"> <li>◦ Full / Half-Duplex (autosensing)</li> <li>◦ MACsec-capable</li> </ul> </li> <li>• 2 x Stacking/QSFP28 ports* (unpopulated)</li> <li>• 1 x Serial console port (RJ-45)</li> <li>• 1 x 10/100/1000BASE-T out-of-band management port</li> <li>• 2 x USB A ports for management or external USB flash</li> <li>• 1 x USB Micro-B console port</li> <li>• 1 x VIM slot</li> </ul>
5520-12MW-36W	<ul style="list-style-type: none"> <li>• 12 x 100M/1/2.5/5GBASE-T 802.3bt (90W) PoE ports</li> <li>• 36 x 10/100/1000BASE-T 802.3bt (90W) PoE ports               <ul style="list-style-type: none"> <li>◦ Full-Duplex</li> <li>◦ MACsec-capable</li> </ul> </li> <li>• 2 x Stacking/QSFP28 ports* (unpopulated)</li> <li>• 1 x Serial console port (RJ-45)</li> <li>• 1 x 10/100/1000BASE-T out-of-band management port</li> <li>• 2 x USB A ports for management or external USB flash</li> <li>• 1 x USB Micro-B console port</li> <li>• 1 x VIM slot</li> </ul>

Switch Model	Interfaces
5520-48SE	<ul style="list-style-type: none"> <li>• 48 x 100/1000BASE-X (SFP) ports (unpopulated) <ul style="list-style-type: none"> <li>◦ MACsec-capable</li> </ul> </li> <li>• 2 x Stacking/QSFP28 ports* (unpopulated)</li> <li>• 1 x Serial console port (RJ-45)</li> <li>• 1 x 10/100/1000BASE-T out-of-band management port</li> <li>• 2 x USB A ports for management or external USB flash</li> <li>• 1 x USB Micro-B console port</li> <li>• 1 x VIM slot</li> </ul>
5520-24X	<ul style="list-style-type: none"> <li>• 24 x 100M/1G/10GBASE-X (SFP+) ports** (unpopulated)</li> <li>• 2 x Stacking/QSFP28 ports* (unpopulated)</li> <li>• 1 x Serial console port (RJ-45)</li> <li>• 1 x 10/100/1000BASE-T out-of-band management port</li> <li>• 2 x USB A ports for management or external USB flash</li> <li>• 1 x USB Micro-B console port</li> <li>• 1 x VIM slot</li> </ul>
5520-24T-ACDC	<ul style="list-style-type: none"> <li>• 24 x 10/100/1000BASE-T FDX/HDX MACsec capable ports</li> <li>• 2 stacking/QSFP28 ports</li> <li>• 1 unpopulated VIM slot</li> <li>• 3 unpopulated modular fan slots</li> <li>• 2 unpopulated modular PSU slots</li> <li>• AC or DC PSU capable</li> </ul>
5520-48T-ACDC	<ul style="list-style-type: none"> <li>• 48 x 10/100/1000BASE-T FDX/HDX MACsec capable ports</li> <li>• 2 stacking/QSFP28 ports</li> <li>• 1 unpopulated VIM slot</li> <li>• 3 unpopulated modular fan slots</li> <li>• 2 unpopulated modular PSU slots</li> <li>• AC or DC PSU capable</li> </ul>
5520-24X-ACDC	<ul style="list-style-type: none"> <li>• 24 x 1Gb/10Gb SFP+ ports</li> <li>• 2 stacking/QSFP28 ports</li> <li>• 1 unpopulated VIM slot</li> <li>• 3 unpopulated modular fan slots</li> <li>• 2 unpopulated modular PSU slots</li> <li>• AC or DC PSU capable</li> </ul>
5520-48SE-ACDC	<ul style="list-style-type: none"> <li>• 48 x 1000BASE-X SFP MACsec capable ports</li> <li>• 2 stacking/QSFP28 ports</li> <li>• 1 unpopulated VIM slot</li> <li>• 3 unpopulated modular fan slots</li> <li>• 2 unpopulated modular PSU slots</li> <li>• AC or DC PSU capable</li> </ul>
5520-VIM-4X	<ul style="list-style-type: none"> <li>• 4 x 1/10GBASE-X SFP+ ports (unpopulated)</li> </ul>
5520-VIM-4XE	<ul style="list-style-type: none"> <li>• 4 x 1/10GBASE-X SFP+ ports (unpopulated) <ul style="list-style-type: none"> <li>◦ LRM-capable</li> <li>◦ MACsec-capable</li> </ul> </li> </ul>
5520-VIM-4YE	<ul style="list-style-type: none"> <li>• 4 x 10/25GBASE-X SFP28 ports (unpopulated) <ul style="list-style-type: none"> <li>◦ MACsec-capable</li> </ul> </li> </ul>

\* Notes on use of the 2 x Stacking/QSFP28 ports

1. With Switch Engine, the 2 x QSFP28 ports can be used for stacking or as Ethernet uplink ports (when not stacking); stacking data rate is 40Gb or 50Gb per port.
2. With Fabric Engine, the 2 x QSFP28 ports can be used as Ethernet uplink ports if in non-Fabric mode or if no VIM is present as of the VOSS 8.4.2 release.
3. Ethernet uplink QSFP28 data rate options per port, with channelization: 4 x 10Gb SFP+, 4 x 25Gb SFP28, 1 x 40Gb QSFP+ (supported with Switch Engine and Fabric Engine); 2 x 50Gb (Switch Engine only)

\*\* 100M on 5520-24 x access ports supported with Switch Engine and with Fabric Engine (minimum Release 8.6).

## Performance and Scale

Switch Model	Max Active 10Mb/100Mb/1000Mb ports	Max Active 100Mb/1Gb/2.5Gb/5Gb ports	Max Active 100Mb/1Gb SFP ports	Max Active 1Gb/10Gb SFP+ ports*	Max Active 25Gb SFP28 ports*	Max Active 40Gb QSFP+ ports**	Max Active 50Gb ports**	Max Active 40Gb/50Gb Stacking ports***	Aggregated Switch Bandwidth	Frame Forwarding Rate
5520-24T	24	0	0	12	12	2	4	2	648 Gbps	482.1 Mpps
5520-24W	24	0	0	12	12	2	4	2	648 Gbps	482.1 Mpps
5520-48T	48	0	0	12	12	2	4	2	696 Gbps	517.8 Mpps
5520-48W	48	0	0	12	12	2	4	2	696 Gbps	517.8 Mpps
5520-12MW-36W	36	12	0	12	12	2	4	2	792 Gbps	589.3 Mpps
5520-48SE	0	0	48	12	12	2	4	2	696 Gbps	517.8 Mpps
5520-24X	0	0	24	36	12	2	4	2	1080 Gbps	803.5 Mpps
5520-24T-ACDC	24	0	0	12	12	2	4	2	648 Gbps	482.1 Mpps
5520-48T-ACDC	48	0	0	12	12	2	4	2	696 Gbps	517.8 Mpps
5520-24X-ACDC	0	0	24	36	12	2	4	2	1080 Gbps	803.5 Mpps
5520-48SE-ACDC	0	0	48	12	12	2	4	2	696 Gbps	517.8 Mpps

\* Includes 8 ports available through channelization of the 2 x QSFP28 ports when not used for stacking with Switch Engine, or with VOSS 8.4.2 or later

\*\* Available through channelization of the 2 x QSFP28 ports when these ports are not used for stacking in Switch Engine, or with VOSS 8.4.2 or later

\*\*\* 50Gb stacking with Switch Engine mode only 31.6 or later

## Software Scaling Values

### 5520 with Switch Engine

- MAC Table: 114,688/65,536
- IPv4 ARP Table: 60,000/41,000\*
- IPv4 Route Table: 81,000/16,000\*
- IP Multicast Entries (S,G,V): 43,000/24,000\*
- IPv6 ND Table: 18,000
- IPv6 Route Table: 40,000/8,000\*
- ACL (Ingress/Egress): 9,216/1,024
- QoS Egress Queues/Port: 8
- VLANs: 4,094
- Routed VLANs: 2,048

\* First value is the maximum; second is the default. Scaling limits are configurable. See the Switch Engine Release Notes for additional details

### OnePolicy Scaling

- Policy Profiles: 63
- Unique permit/deny rules per switch: 8,120
- Authenticated policy users/switch: 9,216

### 5520 with Fabric Engine

- MAC Table: 40,960 (81,920 non-Fabric)
- IPv4 ARP/IP Host Table: 16,000/48,000
- IPv4 Route Table: 15,500
- IP Multicast Routes: 4,000
- IPv6 ND Table: 16,000
- IPv6 Route Table: 7,500
- IPv4 ACL (Ingress/Egress): 1,024/336
- QoS Egress Queues/Port: 8
- VLANs: 4,059

- Routed VLANs: 500

### Fabric Connect Scaling

- Fabric Adjacencies per switch: 128
- Fabric nodes per area (BEB + BCB): 800
- BEB Nodes per VSN: 500
- L2 VSN: 3500
- L3 VSN: 256

## Weights and Dimensions

### Switches

Switch Model	Weight*	Physical Dimensions	
		Chassis Only	With PSU
5520-24T	5.54 kg (12.21 lb.)	Height: 44 mm (1.73 in.) Width: 441 mm (17.36 in.) Depth: 442 mm (17.42 in.)	Height: 44 mm (1.73 in.) Width: 441 mm (17.36 in.) Depth: 449 mm (17.68 in.)
5520-24W	6.25 kg (13.78 lb.)		
5520-48T	5.76 kg (12.70 lb.)		
5520-48W	6.06 kg (13.36 lb.)		
5520-12MW-36W	6.33 kg (13.96 lb.)		
5520-48SE	5.70 kg (12.57 lb.)		
5520-24X	6.25 kg (13.78 lb.)		
5520-24T-ACDC	5.15 kg (11.35 lb.)	Height: 43 mm (1.71 in.) Width: 431 mm (16.98 in.) Depth: 442 mm (17.42 in.)	Not applicable
5520-48T-ACDC	5.95 kg (13.12 lb.)		
5520-24X-ACDC	5.68 kg (12.52 lb.)		
5520-48SE-ACDC	5.91 kg (13.03 lb.)		

\* Switch weights include fans but no PSUs

## VIM Modules

Model	Weight	Physical Dimensions
5520-VIM-4X	0.17 kg (0.37 lb.)	Height: 40.8 mm (1.61 in.) Width: 48.8 mm (1.92 in.) Depth: 146.3 mm (5.76 in.)
5520-VIM-4XE	0.20 kg (0.44 lb.)	
5520-VIM-4YE	0.21 kg (0.46 lb.)	

## Power Supplies

Model	Weight*	Physical Dimensions
10953 (350W AC)	1.08 kg (2.38 lb.)	Height: 82.5 mm (3.25 in.) Width: 40 mm (1.57 in.) Depth: 287 mm (11.30 in.)
10951 (715W AC)	1.16 kg (2.56 lb.)	
10941 (1100W AC)	1.16 kg (2.56 lb.)	
XN-ACPWR-2000W-F (2000W AC)	1.16 kg (2.56 lb.)	Height: 75 mm (2.95 in.) Width: 40 mm (1.57 in.) Depth: 292 mm (11.50 in.)
XN-ACPWR-550W-FB	0.81 kg (1.79 lb.)	Height: 40 mm (1.58 in.) Width: 73.7 mm (2.90 in.) Depth: 185.2 mm (7.29 in.)
XN-ACPWR-550W-BF	0.81 kg (1.79 lb.)	
XN-DCPWR-550W-FB	0.81 kg (1.79 lb.)	
XN-DCPWR-550W-BF	0.81 kg (1.79 lb.)	

## Power Supply Unit Specifications

	10953	10951	10941	XN-ACPWR-2000-F*
Voltage Input Range (Nominal)	100VAC-127VAC/ 200VAC-240VAC	100VAC-127VAC/ 200VAC-240VAC	100VAC-127VAC/ 200VAC-240VAC	100VAC-127VAC/ 200VAC-240VAC
Line Frequency Range	50Hz to 60Hz	50Hz to 60Hz	50Hz to 60Hz	50Hz to 60Hz
Power Supply Input Socket	IEC/EN 60320 C14	IEC/EN 60320 C16	IEC/EN 60320 C16	IEC/EN 60320 C16
Power Cord Input Plug	IEC/EN 60320 C15	IEC/EN 60320 C15	IEC/EN 60320 C15	IEC/EN 60320 C15
Operating Temperature	0°C to 55°C (32°F to 131°F) Normal Operation	0°C to 50°C (32°F to 122°F) Normal Operation	0°C to 50°C (32°F to 122°F) Normal Operation	0°C to 55°C (32°F to 131°F) Normal Operation

\* 200VAC-240VAC is required to achieve full 2000W output. If run at 100VAC-120VAC, output is limited to 1100W.

## Power Supply Unit Specifications (cont.)

	XN-ACPWR-350W-FB	XN-ACPWR-350W-BF	XN-ACPWR-715W-FB	XN-ACPWR-1100W-FB	XN-ACPWR-2000W-FB*
Voltage Input Range (Nominal)	100VAC-240VAC	100VAC-240VAC	100VAC-240VAC	100VAC-240VAC	100VAC-240VAC
Line Frequency Range	50Hz to 60Hz	50Hz to 60Hz	50Hz to 60Hz	50Hz to 60Hz	50Hz to 60Hz

	XN-ACPWR-350W-FB	XN-ACPWR-350W-BF	XN-ACPWR-715W-FB	XN-ACPWR-1100W-FB	XN-ACPWR-2000W-FB*
Power Supply Input Socket	IEC/EN 60320 C14	IEC/EN 60320 C14	IEC/EN 60320 C16	IEC/EN 60320 C16	IEC/EN 60320 C16
Power Cord Input Plug	IEC/EN 60320 C15	IEC/EN 60320 C15	IEC/EN 60320 C15	IEC/EN 60320 C15	IEC/EN 60320 C15
Operating Temperature	0°C to 55°C (32°F to 131°F) Normal Operation	0°C to 55°C (32°F to 131°F) Normal Operation	0°C to 50°C (32°F to 122°F) Normal Operation	0°C to 50°C (32°F to 122°F) Normal Operation	0°C to 50°C (32°F to 122°F) Normal Operation

\* 200VAC-240VAC is required to achieve full 2000W output. If run at 100VAC-120VAC, output is limited to 1100W.

## Power Supply Unit Specifications (cont.)

	XN-ACPWR-550W-FB	XN-ACPWR-550W-BF	XN-DCPWR-550W-FB	XN-DCPWR-550W-BF
Voltage Input Range (Nominal)	100VAC-240VAC	100VAC-240VAC	-48VDC (-36VDC to -72VDC)	-48VDC (-36VDC to -72VDC)
Line Frequency Range	50Hz to 60Hz	50Hz to 60Hz	N/A	N/A
Power Supply Input Socket	IEC 320 - C14	IEC 320 - C14	POSITRONIC PN# PLAH03M400A1/AA-E1A	POSITRONIC PN# PLAH03M400A1/AA-E1A
Power Cord Input Plug	IEC 320 - C13	IEC 320 - C13	POSITRONIC PN# PLAH03M400A1/AA-E1A	POSITRONIC PN# PLAH03M400A1/AA-E1A
Operating Temperature	0°C to 50°C (32°F to 122°F) Normal Operation	0°C to 50°C (32°F to 122°F) Normal Operation	0°C to 50°C (32°F to 122°F) Normal Operation	0°C to 50°C (32°F to 122°F) Normal Operation

## PoE Power Budget

Switch Model	1 x 715W	2x 715W	1 x 1100W	2 x 1100W	1 x 2000W @ 100-120VAC	1 x 2000W @ 200-240VAC	2 x 2000W @ 100-120VAC	2 x 2000W @ 200-240VAC
5520-24W	494W	1079W	879W	1781W	879W	1779W	1869W	2160W
5520-48W	483W	1068W	868W	1770W	868W	1768W	1858W	3568W
5520-12MW-36W	464W	1049W	849W	1751W	849W	1749W	1839W	3549W

Note: It is recommended that primary and secondary power supply units (PSUs) be of the same type to support optimal PoE operation.

## Minimum/Maximum Power Consumption and Heat Dissipation

Switch Model	Minimum Power Consumption (W)	Minimum Heat Dissipation (BTU/hr)	Maximum Power Consumption (W)*	Maximum Heat Dissipation (BTU/hr)**
5520-24T	52	176	142	483
5520-24W	54	182	2480	1092



Switch Model	Minimum Power Consumption (W)	Minimum Heat Dissipation (BTU/hr)	Maximum Power Consumption (W)*	Maximum Heat Dissipation (BTU/hr)**
5520-48T	60	205	171	584
5520-48W	59	203	4100	1817
5520-12MW-36W	66	224	4095	1862
5520-48SE	61	209	255	872
5520-24X	48	165	171	585
5520-24T-ACDC	41	140	135	459
5520-48T-ACDC	46	156	141	481
5520-24X-ACDC	39	132	169	575
5520-48SE-ACDC	45	154	223	760

\* Includes maximum PoE load (W) through the switch

\*\* Does not include PoE load heat dissipated through external electronic load

## Fan and Acoustic Noise

Switch Model	Acoustic Information	
5520-24T	Typical: Single 350W AC PSU, no VIM Maximum: Dual 350W AC PSU, 5520-VIM-4YE	
	Bystander Sound Pressure 39.6 dB(A), 0 °C to 35 °C (32 °F to 95 °F) (Typical) 77.5 dB(A), 50 °C (122 °F) (Maximum)	Sound Power 5.1 B, 0 °C to 35 °C (32 °F to 95 °F) (Typical) 8.46 B, 50 °C (122 °F) (Maximum)
5520-24W	Typical: Single 715W AC PSU, no VIM Maximum: Dual 1100W AC PSU, 5520-VIM-4YE	
	Bystander Sound Pressure 50.4 dB(A), 0 °C to 35 °C (32 °F to 95 °F) (Typical) 67.1 dB(A), 25 °C (77 °F) (Maximum) 78.9 dB(A), 50 °C (122 °F) (Maximum)	Sound Power 6 B, 0 °C to 35 °C (32 °F to 95 °F) (Typical) 7.61 B, 25 °C (77 °F) (Maximum) 8.6 B, 50 °C (122 °F) (Maximum)
5520-48T	Typical: Single 350W AC PSU, no VIM Maximum: Dual 350W AC PSU, 5520-VIM-4YE	
	Bystander Sound Pressure 39.0 dB(A), 0 °C to 35 °C (32 °F to 95 °F) (Typical) 79.0 dB(A), 50 °C (122 °F) (Maximum)	Sound Power 4.9 B, 0 °C to 35 °C (32 °F to 95 °F) (Typical) 8.52 B, 50 °C (122 °F) (Maximum)
5520-48W	Typical: Single 1100W AC PSU, no VIM Maximum: Dual 2000W AC PSU (240VAC), 5520-VIM-4YE	

Switch Model	Acoustic Information	
	<p>Bystander Sound Pressure</p> <p>64.3 dB(A), 0 °C to 35 °C (32 °F to 95 °F) (Typical)</p> <p>69.1 dB(A), 25 °C (77 °F) (Maximum)</p> <p>79.4 dB(A), 50 °C (122 °F) (Maximum)</p>	<p>Sound Power</p> <p>7.24 B, 0 °C to 35 °C (32 °F to 95 °F) (Typical)</p> <p>7.65 B, 25 °C (77 °F) (Maximum)</p> <p>8.6 B, 50 °C (122 °F) (Maximum)</p>
5520-12MW-36W	<p>Typical: Single 1100W AC PSU, no VIM</p> <p>Maximum: Dual 2000W AC PSU (240VAC), 5520-VIM-4YE</p>	
	<p>Bystander Sound Pressure</p> <p>62.7 dB(A), 0 °C to 35 °C (32 °F to 95 °F) (Typical)</p> <p>69.2 dB(A), 25 °C (77 °F) (Maximum)</p> <p>78.8 dB(A), 50 °C (122 °F) (Maximum)</p>	<p>Sound Power</p> <p>7.25 B, 0 °C to 35 °C (32 °F to 95 °F) (Typical)</p> <p>7.64 B, 25 °C (77 °F) (Maximum)</p> <p>8.6 B, 50 °C (122 °F) (Maximum)</p>
5520-48SE	<p>Typical: Single 350W AC PSU, no VIM</p> <p>Maximum: Dual 350W AC PSU, 5520-VIM-4YE</p>	
	<p>Bystander Sound Pressure</p> <p>41.4 dB(A), 0 °C to 35 °C (32 °F to 95 °F) (Typical)</p> <p>77.9 dB(A), 50 °C (122 °F) (Maximum)</p>	<p>Sound Power</p> <p>5.14 B, 0 °C to 35 °C (32 °F to 95 °F) (Typical)</p> <p>8.53 B, 50 °C (122 °F) (Maximum)</p>
5520-24X	<p>Typical: Single 350W AC PSU, no VIM</p> <p>Maximum: Dual 350W AC PSU, 5520-VIM-4YE</p>	
	<p>Bystander Sound Pressure</p> <p>40.6 dB(A), 0 °C to 35 °C (32 °F to 95 °F) (Typical)</p> <p>76.9 dB(A), 50 °C (122 °F) (Maximum)</p>	<p>Sound Power</p> <p>5.05 B, 0 °C to 35 °C (32 °F to 95 °F) (Typical)</p> <p>8.52 B, 50 °C (122 °F) (Maximum)</p>
5520-24T-ACDC	<p>Typical: F2B Airflow; Single 550W AC PSU, no VIM</p> <p>Maximum: F2B Airflow; Dual 550W AC PSU, with 5520-VIM-4YE</p>	
	<p>Bystander Sound Pressure</p> <p>38.6 dB(A), 0 °C to 40 °C (Typical)</p> <p>76.5 dB(A), 50 °C (Maximum)</p>	<p>Sound Power</p> <p>4.94 B, 0 °C to 40 °C (Typical)</p> <p>8.60 B, 50 °C (Maximum)</p>
	<p>Typical: F2B Airflow; Single 550W DC PSU, no VIM</p> <p>Maximum: F2B Airflow; Dual 550W DC PSU, with 5520-VIM-4YE</p>	
	<p>Bystander Sound Pressure</p> <p>38.2 dB(A), 0 °C to 40 °C (Typical)</p> <p>77.0 dB(A), 50 °C (Maximum)</p>	<p>Sound Power</p> <p>4.89 B, 0 °C to 40 °C (Typical)</p> <p>8.56 B, 50 °C (Maximum)</p>
	<p>Typical: B2F Airflow; Single 550W AC PSU, no VIM</p> <p>Maximum: B2F Airflow; Dual 550W AC PSU, with 5520-VIM-4YE</p>	
	<p>Bystander Sound Pressure</p> <p>38.46dB(A), 0 °C to 40 °C (Typical)</p> <p>76.6 dB(A), 50 °C (Maximum)</p>	<p>Sound Power</p> <p>4.99 B, 0 °C to 40 °C (Typical)</p> <p>8.61 B, 50 °C (Maximum)</p>
	<p>Typical: B2F Airflow; Single 550W DC PSU, no VIM</p> <p>Maximum: B2F Airflow; Dual 550W DC PSU, with 5520-VIM-4YE</p>	
	<p>Bystander Sound Pressure</p> <p>39.8 dB(A), 0 °C to 40 °C (Typical)</p> <p>79.0 dB(A), 50 °C (Maximum)</p>	<p>Sound Power</p> <p>5.03 B, 0 °C to 40 °C (Typical)</p> <p>8.69 B, 50 °C (Maximum)</p>

Switch Model	Acoustic Information	
5520-48T-ACDC	Typical: F2B Airflow; Single 550W AC PSU, no VIM Maximum: F2B Airflow; Dual 550W AC PSU, with 5520-VIM-4YE	
	Bystander Sound Pressure 38.2 dB(A), 0°C to 40°C (Typical) 76.4 dB(A), 50°C (Maximum)	Sound Power 4.91 B, 0°C to 40°C (Typical) 8.58 B, 50°C (Maximum)
	Typical: F2B Airflow; Single 550W DC PSU, no VIM Maximum: F2B Airflow; Dual 550W DC PSU, with 5520-VIM-4YE	
	Bystander Sound Pressure 38.1 dB(A), 0°C to 40°C (Typical) 77.1 dB(A), 50°C (Maximum)	Sound Power 4.88 B, 0°C to 40°C (Typical) 8.55 B, 50°C (Maximum)
	Typical: B2F Airflow; Single 550W AC PSU, no VIM Maximum: B2F Airflow; Dual 550W AC PSU, with 5520-VIM-4YE	
	Bystander Sound Pressure 38.5 dB(A), 0°C to 40°C (Typical) 76.7 dB(A), 50°C (Maximum)	Sound Power 4.94 B, 0°C to 40°C (Typical) 8.54 B, 50°C (Maximum)
	Typical: B2F Airflow; Single 550W DC PSU, no VIM Maximum: B2F Airflow; Dual 550W DC PSU, with 5520-VIM-4YE	
	Bystander Sound Pressure 39.6 dB(A), 0°C to 40°C (Typical) 79.0 dB(A), 50°C (Maximum)	Sound Power 5.00 B, 0°C to 40°C (Typical) 8.70 B, 50°C (Maximum)
5520-48SE-ACDC	Typical: F2B Airflow; Single 550W AC PSU, no VIM Maximum: F2B Airflow; Dual 550W AC PSU, with 5520-VIM-4YE	
	Bystander Sound Pressure 39.0 dB(A), 0°C to 40°C (Typical) 76.6 dB(A), 50°C (Maximum)	Sound Power 4.98 B, 0°C to 40°C (Typical) 8.65 B, 50°C (Maximum)
	Typical: F2B Airflow; Single 550W DC PSU, no VIM Maximum: F2B Airflow; Dual 550W DC PSU, with 5520-VIM-4YE	
	Bystander Sound Pressure 38.7 dB(A), 0°C to 40°C (Typical) 77.2 dB(A), 50°C (Maximum)	Sound Power 4.96 B, 0°C to 40°C (Typical) 8.64 B, 50°C (Maximum)
	Typical: B2F Airflow; Single 550W AC PSU, no VIM Maximum: B2F Airflow; Dual 550W AC PSU, with 5520-VIM-4YE	
	Bystander Sound Pressure 38.9 dB(A), 0°C to 40°C (Typical) 77.4 dB(A), 50°C (Maximum)	Sound Power 4.95 B, 0°C to 40°C (Typical) 8.65 B, 50°C (Maximum)
	Typical: B2F Airflow; Single 550W DC PSU, no VIM Maximum: B2F Airflow; Dual 550W DC PSU, with 5520-VIM-4YE	
	Bystander Sound Pressure 40.2 dB(A), 0°C to 40°C (Typical) 79.5 dB(A), 50°C (Maximum)	Sound Power 5.04 B, 0°C to 40°C (Typical) 8.75 B, 50°C (Maximum)

Switch Model	Acoustic Information	
5520-24X-ACDC	Typical: F2B Airflow; Single 550W AC PSU, no VIM Maximum: F2B Airflow; Dual 550W AC PSU, with 5520-VIM-4YE	
	Bystander Sound Pressure 38.1 dB(A), 0 °C to 40 °C (Typical) 75.8 dB(A), 50 °C (Maximum)	Sound Power 4.90 B, 0 °C to 40 °C (Typical) 8.59 B, 50 °C (Maximum)
	Typical: F2B Airflow; Single 550W DC PSU, no VIM Maximum: F2B Airflow; Dual 550W DC PSU, with 5520-VIM-4YE	
	Bystander Sound Pressure 38.0 dB(A), 0 °C to 40 °C (Typical) 76.6 dB(A), 50 °C (Maximum)	Sound Power 4.88 B, 0 °C to 40 °C (Typical) 8.53 B, 50 °C (Maximum)
	Typical: B2F Airflow; Single 550W AC PSU, no VIM Maximum: B2F Airflow; Dual 550W AC PSU, with 5520-VIM-4YE	
	Bystander Sound Pressure 38.3 dB(A), 0 °C to 40 °C (Typical) 77.3 dB(A), 50 °C (Maximum)	Sound Power 4.94 B, 0 °C to 40 °C (Typical) 8.64 B, 50 °C (Maximum)
	Typical: B2F Airflow; Single 550W DC PSU, no VIM Maximum: B2F Airflow; Dual 550W DC PSU, with 5520-VIM-4YE	
	Bystander Sound Pressure 40.1 dB(A), 0 °C to 40 °C (Typical) 79.3 dB(A), 50 °C (Maximum)	Sound Power 4.94 B, 0 °C to 40 °C (Typical) 8.73 B, 50 °C (Maximum)

## Environmental

### Environmental Specifications

EN/ETSI 300 019-2-1 v2.1.2 - Class 1.2 Storage  
 EN/ETSI 300 019-2-2 v2.1.2 - Class 2.3 Transportation  
 EN/ETSI 300 019-2-3 v2.1.2 - Class 3.1e Operational  
 EN/ETSI 300 753 (1997-10) - Acoustic Noise  
 ASTM D3580 Random Vibration Unpackaged 1.5 G

### Environmental Compliance

EU RoHS - 2011/65/EU  
 EU WEEE - 2012/19/EU  
 EU REACH - Regulation (EC) No 1907/2006 - Reporting  
 China RoHS - SJ/T 11363-2006  
 Taiwan RoHS - CNS 15663 (2013.7)

### Environmental Operating Conditions

Temp: 0°C to 50°C (32°F to 122°F) for Front-Back cooling  
 Temp: 0°C to 45°C (32°F to 113°F) for Back-Front cooling (5520-24T, 5520-24X, 5520-48T, 5520-48SE)  
 Humidity: 10% to 95% relative humidity, non-condensing  
 Altitude: 0 to 3,000 meters (9,850 feet)  
 Shock (half sine): 30m/s<sup>2</sup> (3G), 11ms, 60 shocks  
 Random vibration: 3Hz to 500Hz at 1.5 G rms

### Packaging and Storage Specifications

Temp: -40°C to 70°C (-40°F to 158°F)  
 Humidity: 10% to 95% relative humidity, non-condensing  
 Packaged Shock (half sine): 180 m/s<sup>2</sup> (18 G), 6 ms, 600 shocks  
 Packaged Vibration: 5Hz to 62Hz at velocity 5 mm/s, 62Hz to 500Hz at 0.2 G  
 Packaged Random Vibration: 5Hz to 20Hz at 1.0 ASD w/-3 dB/oct. from 20Hz to 200Hz  
 Packaged Drop Height: 14 drops minimum on sides and corners at 42 inches (<15 kg box)

## Regulatory and Safety

### North American ITE

UL 60950-1  
 UL/CuL 62368-1 Listed  
 Complies with FCC 21CFR 1040.10 (U.S. Laser Safety)  
 CDRH Letter of Approval (US FDA Approval)  
 CAN/CSA 22.2 No. 60950-1

### European ITE

EN 60950-1, EN 62368-1  
 EN 60825-1 Class 1 (Lasers Safety)  
 2014/35/EU Low Voltage Directive

## International ITE

CB Report and Certificate per IEC 60950-1  
IEC 62368-1

## EMI/EMC Standards

### North American EMC for ITE

FCC CFR 47 Part 15 Class A (USA)  
CB Report and Certificate IEC 62368-1  
RoHS Directive 2011/65/EU  
AS/NZS 60950-1 (Australia /New Zealand)

### European EMC Standards

EN 55035  
EN 55032 Class A  
EN 55024  
EN 55011  
EN 61000-3-2,2014 (Harmonics)  
EN 61000-3-3 2013 (Flicker)  
EN 300 386 (EMC Telecommunications)  
2014/30/EU EMC Directive

### International EMC Certifications

CISPR 32, Class A (International Emissions)  
AS/NZS CISPR32  
CISPR 24 Class A (International Immunity)  
IEC 61000-4-2/EN 61000-4-2 Electrostatic Discharge, 8kV Contact, 15 kV Air, Criteria B  
IEC 61000-4-3 /EN 61000-4-3 Radiated Immunity 10V/m, Criteria A  
IEC 61000-4-4/EN 61000-4-4 Transient Burst, 1 kV, Criteria AB  
IEC 61000-4-5 /EN 61000-4-5 Surge, 2 kV L-L, 2 kV L-G, Level 3, Criteria B  
IEC 61000-4-6 Conducted Immunity, 0.15-80 MHz, 10V/m unmod. RMS, Criteria A  
IEC/EN 61000-4-11 Power Dips & Interruptions, >30%, 25 periods, Criteria C

### Country Specific

VCCI Class A (Japan Emissions)  
ACMA RCM (Australia Emissions)  
CCC Mark (China)  
KCC Mark, EMC Approval (Korea)  
EAC Mark (Custom Union)  
NRCS Mark (South Africa)  
BSMI Mark (Taiwan)  
Anatel (Brazil)  
NoM (Mexico)

## IEEE 802.3 Media Access Standards

IEEE 802.3ab 1000BASE-T

IEEE 802.3bz 2.5G/5GBASE-T  
IEEE 802.3bt Type4 PoE  
IEEE 802.3ae 10GBASE-X  
IEEE 802.3aq 10GBASE-LRM  
IEEE 802.3by 25GBASE-X  
IEEE 802.3ba/802.3bm 40GBASE-X and 100GBASE-X  
IEEE 802.3az Energy Efficient Ethernet

## Ordering Notes

Customers ordering a 5520 Series switch receive the base switch along with Base software license, fan modules and rack-mount kit. At least one Power Supply Unit (PSU) is required for 5520 operation, and a second PSU is required for redundancy and/or additional power.

Versatile Interface Modules (VIMs), power supplies, transceiver/optics, power cords, as well as Premier and MACsec licenses must be ordered separately.

## Base Software and Optional Premier License

The Base software included with each 5520 unit supports most available switch features. Certain features, however, require a Premier license to operate.

For Switch Engine, a Premier License is required for:

- 5 or more OSPF interfaces
- PIM DM / PM SSM
- Anycast RP (Rendezvous Point)
- Multi-Source Discovery Protocol (MSDP)
- IS-IS/BGP4/MBGP\*
- GRE Tunneling
- EthernetVPN (EVPN)
- Multi-Protocol Label Switching (MPLS)\*\*\*

For Fabric Engine, a Premier License is required for:

- 5 or more OSPF or RIP interfaces
- 3 or more BGP peers
- 25 or more VRFs\*\*
- Layer 3 Virtual Service Networks (L3 VSNs)
- Distributed Virtual Routing (DvR) Controller

\* Up to 2 BGP interfaces included in Base software with the EXOS 31.4 Release

\*\* VRFs included in Base software with the VOSS 8.4 Release

\*\*\* MPLS available with Switch Engine 31.6 release

## Ordering Information

### 5520 Systems - Fans Included

Part Number	Product Name	Product Description
5520-24T	5520 24-port Switch	5520 Universal Switch with 24 x 10/100/1000BASE-T Full / Half-Duplex MACsec-capable ports, includes 2 x Stacking/QSFP28 ports, 2 fan modules, 1 VIM slot, 2 unpopulated modular PSU slots, Base software license.
5520-24W	5520 24-port 90w PoE Switch	5520 Universal Switch with 24 x 10/100/1000BASE-T Full / Half-Duplex 802.3bt 90W PoE MACsec-capable ports, includes 2 x Stacking/QSFP28 ports, 3 fan modules, 1 VIM slot, 2 unpopulated modular PSU slots, Base software license.
5520-48T	5520 48-port Switch	5520 Universal Switch with 48 x 10/100/1000BASE-T Full / Half-Duplex MACsec-capable ports, includes 2 x Stacking/QSFP28 ports, 3 fan modules, 1 VIM slot, 2 unpopulated modular PSU slots, Base software license.
5520-48W	5520 48-port 90w PoE Switch	5520 Universal Switch with 48 x 10/100/1000BASE-T Full / Half-Duplex 802.3bt 90W PoE MACsec-capable ports, includes 2 x Stacking/QSFP28 ports, 3 fan modules, 1 VIM slot, 2 unpopulated modular PSU slots, Base software license.
5520-12MW-36W	5520 48-port 90w PoE with 12 ports multi-rate Switch	5520 Universal Switch with 12 x 100Mb/1Gb/2.5Gb/5Gb 802.3bt 90W PoE MACsec-capable ports plus 36 x 10/100/1000BASE-T 802.3bt 90W PoE Full / Half-Duplex MACsec-capable ports, includes 2 x Stacking/QSFP28 ports, 3 fan modules, 1 VIM slot, 2 unpopulated modular PSU slots, Base software license.
5520-24X	5520 24-port SFP+ Switch	5520 Universal Switch with 24 x 100Mb/1Gb/10Gb SFP+ ports, includes 2 Stacking/QSFP28 ports, 2 fan modules, 1 VIM slot, 2 unpopulated modular PSU slots, Base software license.

### 5520 Systems – Without Fans and PSUs (ordered separately)

Part Number	Product Name	Product Description
5520-24T-BASE	5520 24-port Switch	5520 Universal Switch with 24 x 10/100/1000BASE-T Full / Half-Duplex MACsec-capable ports, includes 2 x Stacking/QSFP28 ports, 2 unpopulated fan slots, 1 VIM slot, 2 unpopulated modular PSU slots, Base software license.
5520-48T-BASE	5520 48-port Switch	5520 Universal Switch with 48 x 10/100/1000BASE-T Full / Half-Duplex MACsec-capable ports, includes 2 x Stacking/QSFP28 ports, 3 unpopulated fan slots, 1 VIM slot, 2 unpopulated modular PSU slots, Base software license.
5520-48SE	5520 48-port 90w PoE Switch	5520 Universal Switch with 48 x 100M/1Gb SFP MACsec-capable ports, includes 2 x Stacking/ QSFP28 ports, 3 unpopulated fan slots, 1 VIM slot, 2 unpopulated modular PSU slots, Base software license.
5520-48SE-BASE	5520 48-port SFP Switch	5520 Universal Switch with 48 x 100M/1Gb SFP MACsec-capable ports, includes 2 x Stacking/ QSFP28 ports, 3 unpopulated fan slots, 1 VIM slot, 2 unpopulated modular PSU slots, Base software license.
5520-24X-BASE	5520 24-port SFP+ Switch	5520 Universal Switch with 24 x 100Mb/1Gb/10Gb SFP+ ports, includes 2 Stacking/QSFP28 ports, 2 unpopulated fan slots, 1 VIM slot, 2 unpopulated modular PSU slots, Base software license.

## 5520 Systems - AC/DC Switches without Fans and PSUs (ordered separately)

Part Number	Product Name	Product Description
5520-24T-ACDC-BASE	5520 24-port Switch	5520 Universal Switch with 24 x 10/100/1000BASE-T FDX/HDX MACsec-capable ports, 2 x Stacking/QSFP28 ports, 1 unpopulated VIM slot, 3 unpopulated modular fan slots, 2 unpopulated modular PSU slots, AC or DC PSU capable.
5520-48T-ACDC-BASE	5520 48-port Switch	5520 Universal Switch with 48 x 10/100/1000BASE-T FDX/HDX MACsec-capable ports, 2 x Stacking/QSFP28 ports, 1 unpopulated VIM slot, 3 unpopulated modular fan slots, 2 unpopulated modular PSU slots, AC or DC PSU capable.
5520-24X-ACDC-BASE	5520 24-port SFP+ Switch	5520 Universal Switch with 24 x 1Gb/10Gb SFP+ ports, 2 Stacking/QSFP28 ports, 1 unpopulated VIM slot, 3 unpopulated modular fan slots, 2 unpopulated modular PSU slots, AC or DC PSU capable.
5520-48SE-ACDC-BASE	5520 48-port SFP Switch	5520 Universal Switch with 48 x 1000BASE-X SFP MACsec capable ports, 2 x Stacking/QSFP28 ports, 1 unpopulated VIM slot, 3 unpopulated modular fan slots, 2 unpopulated modular PSU slots, AC or DC PSU capable.

## Versatile Interface Modules

Part Number	Product Name	Product Description
5520-VIM-4X	4-port SFP+ module	5520 Versatile Interface Module with 4 x 1/10Gb SFP+ ports
5520-VIM-4XE	4-port SFP+ module LRM/ MACsec capable	5520 Versatile Interface Module with 4 x 1/10Gb SFP+ LRM and MACsec-capable ports
5520-VIM-4YE	4-port SFP28 module MACsec capable	5520 Versatile Interface Module with 4 x 10/25Gb SFP28 MACsec-capable ports

## Power Supplies for use with 5520 AC only

Part Number	Product Name	Product Description
10953	350W AC PSU FB	350W AC PSU supported on 5520
10951	715W AC PSU FB	715W AC PSU supported on 5520
10941	1100W AC PSU FB	1100W AC PSU supported on 5520
XN-ACPWR-2000W-F	2000W AC PSU FB	2000W AC PSU supported on 5520
XN-ACPWR-350W-FB*	350W AC PSU FB	350W AC Power Supply Module - Front to Back airflow, also used on X465 and VSP 4900
XN-ACPWR-715W-FB*	715W AC PSU FB	715W AC PoE Power Supply Module - Front to Back airflow, also used on 5720, X465, and VSP 4900
XN-ACPWR-1100W-FB*	1100W AC PSU FB	1100W AC PoE Power Supply Module - Front to Back airflow, also used on 5720, X465, and VSP 4900
XN-ACPWR-2000W-FB*	2000W AC PSU FB	2000W AC PoE Power Supply Module - Front to Back airflow, also used on 5720, X465, and VSP 4900
XN-ACPWR-350W-BF	350W AC PSU BF	350W Back to Front cooling AC PSU supported on 5520 Non-PoE switches

\* XN-ACPWR-xxx-FB power supply units cannot be used with the 10941, 10951, 10953, or XN-ACPWR-2000W-F PSUs on the same switch. Not available for Mexico, Russia, Brazil, China, Korea, South Africa, India at present, pending certification.

## Power Supplies for use with 5520-ACDC Switches

Part Number	Product Name	Product Description
XN-ACPWR-550W-FB	550W AC PSU FB	550W AC Power Supply Module - Front to Back airflow
XN-ACPWR-550W-BF	550W AC PSU BF	550W AC Power Supply Module - Back to Front airflow
XN-DCPWR-550W-FB	550W DC PSU FB	550W DC Power Supply Module - Front to Back airflow
XN-DCPWR-550W-BF	550W DC PSU BF	550W DC Power Supply Module - Back to Front airflow

## Fan Modules and Rack Mount Kits

Part Number	Product Name	Product Description
17115	Spare Fan Module FB	Fan module for 5520, Front to Back airflow
17116	Spare Fan Module BF	Fan module for 5520, Back to Front airflow
XN-4P-RMKIT-005	4-Post Rack Mount Kit	Spare 4-Post Rack Mount Kit for 5520
XN-2P-RMKIT-005**	2-Post Rack Mount Kit	Optional 2-Post Rack Mount Kit for 5520

\*\* The optional 2-post rack mount kit can be used with 5520 chassis HW rev AD or higher.

## Software Licenses

Part Number	Product Name	Product Description
5000-PRMR-LIC-P	Premier License for 5000 Series	Perpetual Premier License for 5000 Series switches
5000-MACSEC-LIC-P	MACsec License for the 5000 Series	Perpetual MACsec license for the 5000 Series switches



## Warranty

All 5520 Series models are covered under Extreme's Universal LLW policy. For warranty details, please visit our [Policies and Warranties page](#).

## Power Cords

Power cords are not included with the 5520 in support of our green initiatives but can be ordered separately.

## Optics / Transceivers

For a list of the optics and transceivers supported on the 5520 Series hardware, refer to our [Extreme Optics Compatibility Tool](#).

## Maintenance Services

Extreme's maintenance and support services are provided by 100% in-house engineering experts. We have a rate of over 90% first-person resolution, ensuring efficient operation of your business- essential network.

With 24x7x365 phone support, advanced parts replacement, and on-site support, we augment your staff with expert resources to help you mitigate critical network issues fast. Visit [ExtremeWorks Maintenance Services](#) for more information.

## Certifications

For information on Industry, Security, and Government certifications for 5520 Series models, contact your Sales Representative.



©2023 Extreme Networks, Inc. All rights reserved. Extreme Networks and the Extreme Networks logo are trademarks or registered trademarks of Extreme Networks, Inc. in the United States and/or other countries. All other names are the property of their respective owners. For additional information on Extreme Networks Trademarks please see <http://www.extremenetworks.com/company/legal/trademarks>. Specifications and product availability are subject to change without notice. 2nov23