

HPE 100GbE 16QSFP28 Power to Connector Airflow Half Width Switch SN2100M with NVIDIA Cumulus (S2T76A)

What's new

- The NVIDIA® Cumulus Linux® Network Operating System is now bundled with the HPE Storage Switch M-series SN2100M using SKU S2T76A

Overview

How can you provide fast, reliable, and cost-effective connectivity in the data center with predictable performance and investment protection? HPE Storage Switch M-series SN2100M is ideal for modern server and storage networks. Supporting port speeds of 1, 10, 25, 40, 50, and 100GbE, delivering predictable performance and zero packet loss at line-rate across each port and packet size. Enhanced for storage combined with efficient design, it provides enterprise-level performance with attractive economics and outstanding ROI. Networks built on HPE Storage SN2100M are fast, reliable, and scalable while also being affordable and easy to manage. It supports primary and secondary storage, providing consistently fair, fast, and low-latency connectivity even under heavy workloads or a mix of different port speeds. This makes them ideal for storage, hyperconverged infrastructure, financial services, and media and entertainment deployments.

Features

Lossless Low-latency Connectivity at 100GbE in a Half-width Form Factor

HPE Storage Switch M-series SN2100M provides predictability within a storage network and consistent throughput regardless of the packet size being transferred, the mixture of ports which are sending data, and even within mixed speed environments.

Provides wire-rate performance with zero packet loss across frame sizes, avoiding any negative impact on applications that could occur with frame loss as unexpected packet loss is unacceptable in modern data centers, especially within a storage network.

Capable of forwarding complete capacity wire-rate performance with zero packet loss across ports concurrently at 100GbE speeds while transferring data across both Layer 2 and Layer 3 networks.

Can be deployed to support 1/10GbE ports and is designed to be able to evolve over time to support 25, 50, and 100GbE speeds. This helps future-proof your network architecture and allows for implementing significant speed changes to the architecture over time.

Enhanced for Storage and Hyperconverged Environments

HPE Storage Switch M-series SN2100M provides high-port density in a single rack unit, allowing for higher capacity and efficiency, simplifying scale-out environments and saving on total cost of ownership (TCO). Unique breakout cables fan out individual switch ports to multiple device ports.

With unique form factors and port counts, these Ethernet switches allow two HPE SN2100M units to be deployed side-by-side allowing for increased density, making it the ideal top-of-rack (ToR) switch.

Designed to use less electric power than competing switches, with less than 95W, HPE Storage Switch M-series SN2100M provides one of the industry's lowest power draws, producing less heat than competing products and allowing reduced OpEx cost.

Unleashes Flash Storage Performance

HPE Storage Switch M-series SN2100M provides ultra-low latency of under 300ns port-to-port. This is advantageous for flash storage, which moved latency from storage access to the network, as well as for the burst nature of today's software-defined and cloud data centers traffic.

Provides enough internal bandwidth that there is sufficient capacity to carry ports at 100 Gbps bandwidth concurrently. This allows the switches to avoid head-of-line blocking which can reduce overall performance and throughput.

Introduces dynamic shared buffers and wire speed performance with no packet loss for predictable data delivery.



Technical specifications**HPE 100GbE 16QSFP28 Power to Connector
Airflow Half Width Switch SN2100M with NVIDIA
Cumulus**

Product Number	S2T76A
Port speed	Supports speeds of 1/10/25/40/50/100GbE
Aggregate switch bandwidth	3.2 Tbps
Encryption capability	No
Protocol supported	Ethernet
Availability features	Integrated redundant power supply
Form factor	1U half-width
Model availability	16 ports active switch bundled with NVIDIA Cumulus Linux Network Operating System
Upgradability	Flash for convenient OS upgrades
Media types	QSFP28
Software (required)	NVIDIA® Cumulus Linux®
Ports	16 ports
Software (optional)	HPE SN2100M 100GbE 8p Upgrade E-LTU (Q2M94AAE)
Product dimensions	4.39 x 20 x 50.8 cm
Weight	4.53 kg



[For additional technical information, available models and options, please reference the QuickSpecs](#)

HPE Services

No matter where you are in your transformation journey, you can count on HPE Services to deliver the expertise you need when, where and how you need it. From strategy and planning to deployment, ongoing operations and beyond, our experts can help you realize your digital ambitions.

Consulting services

Experts can help you map out your path to hybrid cloud and optimize your operations.

Managed services

HPE runs your IT operations, giving you unified control, so can focus on innovation.

Operational services

Optimize your entire IT environment and drive innovation. Manage day-to-day IT operational tasks while freeing up valuable time and resources.

- HPE Complete Care Service: a modular service designed to help optimize your entire IT environment and achieve agreed upon IT outcomes and business goals. All delivered by an assigned team of HPE experts.
- HPE Tech Care Service: the operational service experience for HPE products. The service provides access to product specific experts, an AI driven digital experience, and general technical guidance to help reduce risk and search for ways to do things better.

Lifecycle Services

Address your specific IT deployment project needs with tailored project management and deployment services.

HPE Education Services

Training and certification designed for IT and business professionals across all industries. Create learning paths to expand proficiency in a specific subject. Schedule training in a way that works best for your business with flexible continuous learning options.

[The Defective Media Retention \(DMR\)](#) service feature option applies only to Disk or eligible SSD/Flash Drives replaced by Hewlett Packard Enterprise due to malfunction. [Comprehensive Defective Material Retention \(CDMR\)](#) allows you to keep all data retentive components.


HPE GreenLake

[HPE GreenLake edge-to-cloud platform](#) is HPE's market-leading as-a-Service offering that brings the cloud experience to apps and data everywhere – data centers, multi-clouds, and edges – with one unified operating model, on premises, fully managed in a pay per use model.

If you are looking for more services, like **IT financing solutions**, please explore them [here](#).

**Make the right purchase decision.
Contact our presales specialists.**

[Find a partner](#)



Explore **HPE GreenLake**



Share now



Get updates

**Hewlett Packard
Enterprise**

© Copyright 2024 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Linux is the registered trademark of Linus Torvalds in the U.S. and other countries. NVIDIA is a trademark and/or registered trademark of NVIDIA Corporation in the U.S. and other countries. All third-party marks are property of their respective owners.

Image may differ from the actual product
[PSN1014808068WWEN](#), July, 2024.