



MW3050 Wireless Optical USB Mouse

USB-A Nano Receiver, Three Buttons with Scroll Wheel, 1200 dpi, Ambidextrous, White

Part No.: [190329](#)

EAN-13: 0766623190329 | UPC: 766623190329

Durable 3-Button Computer Mouse for Laptop and PC at Home or Office

The Manhattan MW3050 Wireless Optical USB Mouse offers reliable performance in a durable, comfortable design. Its precise 1200 dpi optical sensor offers smooth, lag-free control on almost any surface for a wide range of computing tasks.

Just the right size

With a full-size shape of 10 cm (4 in.) length, this mouse offers a more comfortable grip than a mini mouse but is still compact enough for small laptop-bag pockets. The nano receiver hardly sticks out of your notebook's USB-A port and provides an effective range up to 10 m (33 ft.) for true wireless convenience.

Plug & play and all you need

Plug-and-play capability with Windows[®], Mac[®], Linux[®], and Chrome OS™ compatibility makes installation quick and easy. An ambidextrous shape that comfortably fits the palms of right- and left-handed people and its familiar configuration (three buttons with scroll wheel) make this Wireless Optical Mouse ideal for nearly anyone's daily computing needs.

Features:

- Wireless 2.4 GHz RF nano receiver with USB-A plug for an effective range up to 10 m (33 ft.)
- Ambidextrous design for left- and right-handed users
- Classic left, right and middle mouse buttons with smooth scroll wheel featuring great tactile response
- Compatible with Windows®, macOS®, Linux®, and Chrome OS™
- High-precision optical sensor with 1200 dpi for lag-free control on almost any surface
- On-board storage compartment to protect USB receiver from loss and damage
- Low-friction base that smoothly glides over work surfaces
- Requires one AA battery (included)
- Three-year warranty

Specifications:

Standards and Certifications

- CE
- FCC
- RoHS
- REACH
- UKCA

General

- Range: 2.4 GHz wireless: up to 10 m (33 ft.)
- Optical sensor: 1200 dpi resolution
- Key life: ~ 5 million clicks
- Key cap force: 50 ± 10 g
- Controls: right and left mouse with scroll wheel (auto-scroll)
- Form factor: ambidextrous
- On/off switch
- Battery details:
 - Type: alkaline
 - Battery size: AA
 - Number of batteries required to power product: 1 (included)
 - Battery voltage: 1.5 V DC
 - Working current: ≤25 mA
 - Sleeping current 0.2 - 0.3 mA
 - Battery capacity: 1200 mAh
 - Number of battery cells: 1

Physical

- Dimensions mouse (L x W x H): 104 x 61 x 31 (4.09 x 2.4 x 1.22 in.)
- Net weight: 43 g (0.09 lbs.)

- Gross weight: 66 g (1.46 lbs.)
- Nano receiver/dongle: USB-A, dimensions (L x W x H): 19 x 13 x 6 mm (0.75 x 0.51 x 0.24 in.), weight: 1.6 g (0.06 oz.)
- Material: ABS plastic

Operating Environment

- Operation temperature: 0 - 40°C (32 - 104°F)
- Storage temperature: -15 - 60°C (5 - 140°F)
- Operation and storage humidity (non-condensing): <85% RH

System Requirements

- Windows XP/Vista/7/8.1/10/11, Linux, Chrome OS or macOS

Package Contents

- MW3050 Wireless Optical USB Mouse
- AA battery
- Instructions



