



MWK7350 Wireless USB Keyboard and Mouse Combo Set

One Single USB-A Nano Receiver for Both Devices, Full-Size Wireless Keyboard with 12 Multimedia/Function Keys, Ambidextrous Optical Mouse with Three Buttons and Scroll Wheel, 1200 dpi, Black

Part No.: [180771](#)

EAN-13: 0766623180771 | UPC: 766623180771

Full-Size Wireless Keyboard and Mouse Set to maximize your productivity

The Manhattan MWK7350 Wireless USB Keyboard and Mouse Combo Set combines excellent value with comfort and durability. Use the keyboard anywhere that falls within 10 m (33 ft.) of your USB-A device. When used in tandem with the included Wireless Optical Mouse with its 1200 dpi, standard buttons for left and right clicks, and an easy-access scroll wheel, you are sure to notice an increase in how much you can get done. One single nano receiver connects both devices to your computer and is so small that it hardly sticks out of your laptop's USB-A port.

The benefits of wireless freedom

Cut the cord from your wired USB keyboard to declutter your desk and raise your typing comfort over the touchscreen on your tablet. It requires just two AAA batteries and is equipped with an intelligent power management system that conserves battery life. When the keyboard is not in use, it will automatically power down. Once you start typing again, it turns back on.

Comfortable typing plus quick multimedia access

The membrane key switches give you a comfortable, highly precise typing experience. Twelve function keys offer quick access to frequently used multimedia commands like email, browser or music control. A full-size layout with numeric keypad and navigation keys ensures most convenient data entry.

Just the right mouse size

With a full-size shape of 11 cm (4 in.) length, the mouse offers a more comfortable grip than a mini mouse but is still compact enough for small laptop-bag pockets. An ambidextrous shape that comfortably fits the palms of right- and left-handed people and its familiar configuration (three buttons with scroll wheel) make this Wireless Optical Mouse ideal for nearly anyone's daily computing needs.

Plug & play

Plug-and-play capability with Windows[®], Mac[®], Linux[®], and Chrome OS™ compatibility makes installation quick and easy.

Features:

- Set of 1200 dpi optical mouse, keyboard, and wireless receiver with auto power management
- 104 membrane switches to reduce typing noise and offer precise keystroke response
- 12 function keys offering quick and easy access to frequent multimedia functions
- Full-size layout with numeric keypad and navigation keys for most convenient data entry
- Wireless 2.4 GHz RF nano receiver with USB-A plug for an effective range up to 10 m (33 ft.)
- Adjustable tilt mechanism offers comfortable typing positions
- Rubber feet to prevent slipping and to protect your desk from scratches
- On-board storage compartment to protect USB receiver from loss and damage
- Classic left, right and middle mouse buttons with smooth scroll wheel featuring great tactile response
- Ambidextrous design for left- and right-handed users
- High-precision optical sensor with 1200 dpi for lag-free control on almost any surface
- Mouse requires one AA battery, keyboard requires two AAA batteries (all three included)
- Auto-power management to help maintain proper battery levels
- Plug-and-play installation; no configuration or drivers required
- Compatible with Windows[®], Linux[®], and Chrome OS™
- Three-year warranty

Specifications:

Standards and Certifications

- CE
- FCC

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- RoHS
- REACH
- UKCA

General - Mouse

- Range: 2.4 GHz wireless: up to 10 m (33 ft.)
- Optical sensor: 1200 dpi resolution
- Key life: ~ 3 million clicks
- Key cap force: 60 ± 15 g
- Controls: right and left mouse with scroll wheel (auto-scroll)
- Form factor: ambidextrous
- Automatic power save/power off mode
- On/off switch
- Battery details:
 - Type: alkaline
 - Battery size: AA
 - Number of batteries required to power product: 1 (included)
 - Battery voltage: 1.5 V DC
 - Working current: ≤25 mA
 - Sleeping current ≤0.06 mA
 - Battery capacity: 1550 mAh
 - Number of battery cells: 1

Physical

- Dimensions (L x W x H): 106 x 63 x 38 mm (4.17 x 2.48 x 1.5 in.)
- Net weight: 62 g (0.12 lbs.)

General - Keyboard

- Key life: ~ 3 million keystrokes
- Key style: 104 membrane key switches
- Key cap force: 55 ± 10 g

Electrical

- Working voltage: 3.0 V DC
- Working current ≤1.0 mA
- Sleeping current ≤0.03 mA
- Included battery details:
 - Type: alkaline
 - Battery size: AAA
 - Number of batteries required to power product: 2 (included)
 - Battery voltage: 1.5 V
 - Battery capacity: 600 mAh

Physical

- Dimensions (L x W x H): 440 x 156 x 28 mm (17.32 x 6.14 x 1.1 in.)
- Net weight: 526 g (1.16 lbs.)
- Nano receiver/dongle: USB-A, dimensions (L x W x H): 19 x 13 x 6 mm (11.22

x 5.24 x 0.87 in.), weight: 1.6 g (0.06 oz.)

- Housing materials: ABS plastic

Operating Environment

- Operation temperature: 0 - 40°C (32 - 104°F)
- Storage temperature: -15 - 60°C (5 - 140°F)
- Operation and storage humidity (non-condensing): <85% RH

System Requirements

- Windows 7/8.1/10/11, Linux or Chrome OS

Package Contents

- Wireless USB Keyboard
- Three-Button Wireless Optical USB Mouse
- 2 x AAA battery
- 1 x AA battery
- Instructions



*Shown: US layout. Regional layouts vary.



*Shown: US layout. Regional layouts vary.



*Shown: US layout. Regional layouts vary.



*Shown: US layout. Regional layouts vary.



*Shown: US layout. Regional layouts vary.



*Shown: US layout. Regional layouts vary.

