



HP Color LaserJet Pro 3201dw Printer

Designed for business work teams that need professional performance with fast, high-quality two-sided color printing, laser productivity, and award-winning reliability in a space-saving design.¹¹



Dynamic security enabled printer. Contains technology that may prevent cartridges with non-HP chips or circuitry from working now or in the future. More at: Learn more at: <http://www.hp.com/learn/ds>

Print Speed: Letter: Up to 26 ppm black; Up to 26 ppm color; First Page Out: As fast as 10.8 sec black; As fast as 10.9 sec color

Print Resolution: Black (best): Up to 600 x 600 dpi; Color (best): Up to 600 x 600 dpi

Standard Connectivity: 1 Gigabit Ethernet 10/100/1000 Base-TX network; 1 Hi-Speed USB 2.0 (device); 1 Wi-Fi 802.11ac (dual band); Auto-crossover Ethernet

Mobile Printing Capability: HP Smart App; Apple AirPrint™; Mobile Apps; Mopria™ Certified; Wi-Fi® DirectPrinting

Duty cycle: Monthly (letter): Up to 40,000 pages

Display: 2" diagonal DFSTN-backlit (200 x 114)

Paper Handling: 250-sheets input tray; 100-sheet output bin

Professional color and speed

- Experience high-speed, automatic, two-sided color printing up to 26 pages per minute (Letter) / 25 pages per minute (A4).¹
- Bring our business to life with next-generation TerraJet toner designed for more true-to-life, vibrant colors.⁸
- Streamline your workspace and help boost your team's efficiency with this compact laser printer.

Peace-of-mind with award-winning reliability¹¹

- Performance you can count on page after page with award-winning reliability.¹¹
- Keep your business connected with reliable Wi-Fi® that automatically reconnects to stay online.²
- Rely on low maintenance printing to avoid downtime and stay focused on your business.

Pro level security to help protect your business

- Safeguard your business with proactive, embedded security ready out of the box and tamper-resistant toner.¹²
- Professional level printer security with preconfigured settings mean it's ready for business.
- Strengthen and simplify compliance. HP Security Manager upgrade applies policies across your printer network.¹⁰

Compact and energy efficient design

- Designed in a compact size with energy saving auto-on/auto-off technology to optimize printer energy use.¹⁹
- Specially formulated HP TerraJet Toner engineered for low energy use when printing.⁷
- Trim your paper use. Default duplex setting prints on both sides of each page.
- Easily recycle your used Original HP Toner Cartridges for free through the HP Planet Partners program.⁹



HP Smart App



Easy access USB



¹ Measured using ISO/IEC 24734 and excludes first set of test documents. For more information, see <https://www.hp.com/go/printerclaims>. Exact speed varies depending on the system configuration, software application, driver, and document complexity. ² Internet access required and must be purchased separately. Wireless operations are compatible with 2.4 GHz and 5.0 GHz operations only. Supports both 5.0 GHz and 2.4 GHz using up to 12 non-overlapping channels vs. only 3 non-overlapping channels for 2.4 GHz only. Supports 5.0 GHz band (up to 150 mbps) v. 2.4 GHz band (up to 72.2 mbps). Learn more at: <https://www.hp.com/go/learn/ds> ³ HP Web Jetadmin is available for download at no additional charge at <https://www.hp.com/go/webjetadmin> ⁴ HP calculations based on normalized Energy Star® TEC data of HP LaserJet Pro and Enterprise series with HP TerraJet Cartridges compared to predecessors. See <https://www.hp.com/TerraJet/energysaving> ⁵ Standard print mode for HP Color LaserJet Pro series with HP TerraJet Toner Cartridges compared to predecessors. See <https://www.hp.com/TerraJet/colors> ⁶ Recycling: Program availability varies. Original HP cartridge return and recycling is currently available in more than 60 countries, territories and regions in Asia, Africa, Europe, and North and South America through the HP Planet Partners program. For details, see <https://www.hp.com/recycle> ⁷ HP Security Manager must be purchased separately. For details, see <https://www.hp.com/go/securitymanager> ⁸ Buyers Lab (BLI) 2022-2024 Most Reliable A4 Brand Award based on devices tested by Keypoint Intelligence from 2017 to 2021. See <https://www.keypointintelligence.com/view-award?region=&id=135871174680> ⁹ HP office-class printing systems are select Managed and Enterprise devices with FutureSmart firmware 4.5 and up, Pro devices, LaserJet models 200 and up, with respective Original HP Toner, PageWide and Ink Cartridges. Does not include HP integrated printhead cartridges. Digital supply-chain tracking, hardware, chips and packaging security features vary locally by SKU. See <https://www.hp.com/cartridgesecurity> ¹⁰ Based on 2023 Q2 shipments in the IDC Worldwide Quarterly Hardcopy Peripherals Tracker®, 2023 Q2 Release. Includes shipments of all printing devices (inkjet printers, laser printers, copiers and multifunction devices, including production units). ¹¹ HP account required for full functionality. ¹² HP Auto-On/Auto-Off Technology capabilities subject to printer and settings; may require a firmware upgrade.

Technical specifications

Functions	Print
Print speed ^{6,7}	First page out Letter: As fast as 10.8 sec Black; As fast as 10.9 sec Color; First page out A4: As fast as 10.9 sec Black; As fast as 11.0 sec Color; Letter: Up to 26 ppm Black; Up to 26 ppm Color; A4: Up to 25 ppm Black; Up to 25 ppm Color; Print speed (Landscape, A5): Up to 43 ppm Black
Print resolution	Black (best): Up to 600 x 600 dpi; Black (normal): 600 x 600 dpi; Color (best): Up to 600 x 600 dpi; Color (normal): 600 x 600 dpi;
Print technology	Laser
Print cartridges number	4 (1 each black, cyan, magenta, yellow)
Standard print languages	HP PCL6, PostScript, HP PCL5, PDF, URF, PWG-Raster, JPEG
Connectivity	
Standard connectivity	1 Hi-Speed USB 2.0 (device); 1 Wi-Fi 802.11ac (dual band); Auto-crossover Ethernet; 1 Gigabit Ethernet 10/100TX network
Network capabilities	Built-in 10/100 Base-TX Ethernet, Gigabit; Auto-crossover Ethernet; Authentication via 802.1X
Wireless capability	Built-in dual-band Wi-Fi; Authentication via WEP, WPA/WPA2, WPA Enterprise; Encryption via AES or TKIP; WPS; Wi-Fi Direct
Memory	Standard: 256 MB; Maximum: 256 MB
Processor speed	1.2 GHz /
Duty cycle (monthly)	Letter: Up to 40,000 pages; A4: Up to 40,000 pages; Recommended monthly page volume ⁸ : 150 to 2,500
Recommended monthly page volume ⁹	150 to 2,500
Paper handling	Input Capacities: Up to 250 sheets (25mm stack height) in Tray 2 Standard; Up to 10 envelopes; ; Output Capacities: Up to 100 sheets @ 75gsm (or Up to 15mm stack) Standard; Up to 10 mm stack; ; Duplex Options: Automatic; Envelope feeder: No; Standard paper trays: 2

Media types supported	Paper (bond, brochure, colored, glossy, heavy, letterhead, light, plain, preprinted, prepunched, recycled, rough), transparencies, labels, envelopes, cardstock
Media weight supported	16 to 43 lb Paper (Bond); Up to 47 lb (Bond) with postcards; Up to 52 lb (Bond) Glossy Papers
Media sizes supported	A4; A5; A6; B5 (JIS); B6 (JIS); 10 x 15 cm; Oficio 216 x 340 mm; 16K 195 x 270 mm; 16K 184 x 260 mm; 16K 197 x 273 mm; Postcard (JIS); Envelope B5; Envelope C5; Envelope DL; A5-R
Media Sizes Custom	3 x 5 in to 8.5 x 14 in
What's in the box	499Q9FR HP Color LaserJet Pro 3201dw Printer; Power cord; Toner cartridge; User Guide, Flyers
Product dimensions	W x d x h: 15.35 x 16.5 x 10.01 in ; Maximum: 15.35 x 18.58 x 10.47 in
Product weight ¹³	30.42 lb
Warranty features	One-year limited warranty. For more info please visit us at https://www.support.hp.com ¹²
Control panel	2" MGD display; 4 buttons (Back, Home, Cancel and OK); 1 directional pad (Up, Down, Left and Right)
Display description	2" diagonal DFSTN-backlit (200 x 114)
Software included	HP Printer Software downloadable from https://www.hp.com/download
Compatible operating systems ¹¹	Windows 11; Windows 10; Android; iOS; macOS 12 Monterey; macOS 13 Ventura; macOS 14 Sonoma; macOS 15 Sequoia; Linux
Compatible network operating systems	Windows 11; Windows 10; macOS 12 Monterey; macOS 13 Ventura; macOS 14 Sonoma; macOS 15 Sequoia; Linux
Minimum system requirements	PC: Microsoft® Windows® 11, 10: 32-bit or 64-bit, 2 GB available hard disk space, Internet connection; Mac: Apple® macOS 12.0 Monterey; macOS 13.0 Ventura; macOS v14 Sonoma; 2GB HD; Internet required
Power ¹	Power supply type: Internal (Built-in) power supply; Power requirements: 220-volt input voltage: 220–240V (±10%) @ 50Hz ± 3 Hz, 60Hz ± 3 Hz; 110-volt input voltage: 110–127V (±10%) @ 50Hz ± 3 Hz, 60Hz ± 3 Hz (Not dual voltage, product varies by part number with # Option code identifier); Power consumption: 415 watts (Printing), 6.1 watts (Ready), 0.63 watts (Sleep), 0.05 watts (Auto-Off), 0.05 watts (Manual-Off)
Acoustics	Acoustic power emissions: 6.2 B(A) ; Acoustic Pressure Emissions (active, printing): 51 dB(A)
Operating environment	Operating temperature range: 15 to 30°C; Recommended operating temperature: 15 to 27°C; Storage temperature range: -20 to 60°C; Non-operating humidity range: ; Operating humidity range: 10 to 80% RH; Recommended humidity operating range: 30 to 70% RH

Learn more at

¹ Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Power consumption values typically based on measurement of 115V device. ² For yield information on the cartridge(s) included with your printer, see <https://www.hp.com/go/toneryield>. Yield values measured in accordance with ISO/IEC 19798 and continuous printing. Actual yields vary considerably based on images printed and other factors. ³ Declared yields based on ISO/IEC 19798 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see <https://www.hp.com/go/toneryield> ⁴ End to End Dimensions when printer is set up and on standby ⁵ Configuration tested: base model, simplex printing, A4 paper at an average of 25 ppm ⁶ Measured using ISO/IEC 24734, excludes first set of test documents. For more information see <https://www.hp.com/go/printerclaims>. Exact speed varies depending on the system configuration, software application, driver, and document complexity. ⁷ Measured using ISO/IEC 24734 Feature Performance Test, excludes first set of test documents. For more information see <https://www.hp.com/go/printerclaims>. Exact speed varies depending on the system configuration, software application, driver, and document complexity. ⁸ Measured using ISO/IEC 17629. For more information see <https://www.hp.com/go/printerclaims>. Exact speed varies depending on the system configuration, software application, driver, and document complexity. ⁹ HP recommends that the number of printed pages per month be within the stated range for optimum device performance, based on factors including supplies replacement intervals and device life over an extended warranty period. ¹⁰ Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Energy Star value typically based on measurement of 115V device. ¹¹ Windows Server 2016, Windows Server 2019, Windows Server 2022, Linux (For more information see <https://www.developers.hp.com/hp-linux-imaging-and-printing>) ¹² Warranty and support options vary by product, country, and local legal requirements ¹³ Product Weight Inclusive of Starter Supplies

