



High Mileage® ProX

Floor Finish

High Mileage® ProX Floor Finish delivers excellent gloss build and outstanding durability for your floors, even in the heaviest of traffic.

Features & Benefits

- Specifically designed higher solids formula builds durability over time, allowing for extended recoat and stripping cycles yielding labor savings and overall improved productivity
- Extremely tough in high traffic areas and resists dirt, black heel marks and scratches exceptionally well
- Unsurpassed buff response with all types of UHS equipment - propane, battery or cord electric
- Solids Content 25%
- Meets ASTM D-2047 requirement for slip resistance
- Product does not contain intentionally added PFAS

Applications

- For use on resilient and most hard surface flooring
- A sealer may be required for highly polished stone surfaces, glazed ceramic tile, luxury vinyl tile, and some rubber floors
- Not intended for use on cork, wood, or bamboo flooring





High Mileage® ProX

Floor Finish

Use Instructions

- Blockade areas to be stripped or finished. Floors will be very slippery until dry.
- Strip floors, using a Diversey stripper per the instructions on the stripper label.

Coating

- Apply 3 or more medium coats using a clean finish mop or the Diversey ProSpeed™/MC or TrailBlazer™/MC Floor Finish Applicator System. Apply additional coats until desired gloss is obtained.
- Allow 30–45 minutes drying time between coats. Temperature, humidity and ventilation may affect drying time. Allow finish to cure for 24 hours before burnishing.

Maintenance

- Dust mop or sweep. Clean the floor with a mop or an automatic scrubber using the recommended Diversey brand cleaner according to label directions.
- If desired, dry buff using medium to aggressive pad and 1000– 500 rpm equipment. Ultra-high speed burnish using a medium aggressiveness pad and 2000+ rpm equipment.

Recoating

- Dust mop or sweep.
- Clean the floor with a mop or an automatic scrubber using the recommended Diversey brand cleaner according to label directions.
- Blockade area and apply 1-2 uniform coats of finish using a clean finish mop or the Diversey ProSpeed™/MC or TrailBlazer™/MC Floor Finish Applicator System. Allow finish to cure for 24 hours before burnishing.



Removal

- Remove using recommended Diversey brand stripper following label directions.

Precautions

- Do not dilute. Do not use on surfaces colder than 50°F (10°C) @ 15% RH. To avoid contamination, do not return unused finish to original container. Do not freeze.

| Technical data | High Mileage® ProX Floor Finish |
|----------------|---------------------------------|
| Color/Form | Clear White, liquid |
| pH | 8.2 |
| Scent | Solvent |
| Shelf Life | 2 Years |

| Product | Pack size | Dilution | Product code | |
|---------------------------------|---------------------------------------|--------------|--------------|---------------------------------------------------------------------------------------|
| High Mileage® ProX Floor Finish | 1 x 5 gal. / 18.9 L Envirobox™/MC | Ready-to-use | 101110008 |  |
| High Mileage® ProX Floor Finish | 6 x 2.64 Qt. / 2.5 L ProSpeed™/MC BIB | Ready-to-use | 101110007 |  |

Safe handling

Please make sure your employees read and understand the product label and Safety Data Sheet before using this product. The label contains directions for use; and both the label and SDS contain hazard warnings, precautionary statements and first aid procedures. SDS are available online at www.diversey.com or by calling 888.352.2249. Improper use or dilution may result in damage to surfaces and may result in health and physical hazards that match those of the concentrate.