



## QSW-2104-2T-R2

Management Type	Unmanaged
Number of Ports	6
10GbE BASE-T (RJ45)	2 10G/5G/2.5G/1G/100M
2.5GbE (RJ45)	4
Power Supply Description	Adapter
Max. Power Consumption	18W
Input Power Type	DC
Input Voltage Range	12V/1.5A
MAC Address Table	4K
Total Non-Blocking Throughput	30Gbps
Switching Capacity	60Gbps
Energy Efficient Ethernet (IEEE 802.3az complaint)	Yes
Fanless	Yes
Supported Standards	IEEE 802.3 Ethernet IEEE 802.3u 100BASE-T IEEE 802.3ab 1000BASE-T IEEE 802.3bz 2.5G/5GBase-T IEEE 802.3an 10GBASE-T IEEE 802.3az EEE IEEE 802.3x Full-Duplex Flow Control
Form Factor	Desktop
LED Indicators	Per Port: Speed/Link/Activity Loop LED: Loop Per System: Power/Status
Dimensions (HxWxD)	26 x 160 x110 mm

Weight (Net)	0.99 lbs
Weight (Gross)	1.15 lbs
Operating Temperature	0°C to 40°C (32°F to 104°F)
Relative Humidity	10~95% Non-condensing
Certifications	CE, UKCA, FCC, IC, VCCI, RCM, BSMI, LVD, KC
Electromagnetic Compliance	CLASS B
Jumbo Frames	12K
Warranty	2 Years

Note: QNAP reserves the right to replace partial parts or accessories if the original is no longer available from its manufacturer/supplier. Any replacement would be fully tested and verified to meet strict compatibility and stability guidelines and will deliver identical performance to the original.

Product images are for illustrative purposes only and may differ from the actual product. Due to differences in monitors, colors of products may also appear different to those shown on the site.

Designs and specifications are subject to change without notice.