


2-Port Dual-Monitor DisplayPort KVM with Video Matrix - 4K 60Hz

Product ID

P2ADD121D-KVM-SWITCH



|    |                              |  |
|----|------------------------------|--|
| 8  | Grounding Screw              | • Connect a <b>Grounding Wire</b>  |
| 9  | Reset Button                 | • Power cycles the <b>KVM Switch</b>   |
| 10 | DC Power Input Port          | • Connect the supplied <b>Universal Power Adapter</b> to power the <b>KVM Switch</b> |
| 11 | PC 1 - 2 DisplayPort Inputs  | • Connect to a <b>DisplayPort Output Port</b> on <b>PC 1 - 2</b>                     |
| 12 | PC 1 - 2 USB Host Connection | • Connect to a <b>Computer</b> with a <b>USB Port</b>                                |

Product Information

For the latest manuals, product information, technical specifications, and declarations of conformance, please visit: [www.StarTech.com/P2ADD121D-KVM-SWITCH](http://www.StarTech.com/P2ADD121D-KVM-SWITCH)

Package Contents

- KVM Switch x 1
- Remote Selector Cable x 1
- Universal Power Adapter (NA/EU/UK/ANZ) x 1
- Quick-Start Guide x 1

Requirements

Source PCs

- DisplayPort-Enabled Computer x 2
- DisplayPort Cable x 4
- USB Type-B Cable x 2

Console

- DisplayPort Display x 2
- DisplayPort Cable x 2
- USB Mouse x 1
- USB Keyboard x 1
- (Optional) Audio Devices (e.g. Headphones and Microphone) x 2
- (Optional) USB 2.0 Devices x 2

| Component |                             | Function   |
|-----------|-----------------------------|--|
| 1         | LED Indicators              | • Refer to <b>LED Chart</b>  |
| 2         | Push Button Selector        | • Press the <b>Button</b> to switch to between <b>PC Ports 1 - 2</b><br>• <b>Audible Beep</b> when pressed                                     |
| 3         | Remote Port                 | • Connect the included <b>Remote Selector Cable</b><br>• Press the <b>Remote Selector Cable Button</b> to switch between <b>PC Ports 1 - 2</b> |
| 4         | Console Audio Ports         | • <b>Green:</b> Connect an <b>Audio Device</b> (e.g. Speakers or Headphones)<br>• <b>Pink:</b> Connect a <b>Microphone</b>                     |
| 5         | Console DisplayPort Outputs | • Connect to <b>DisplayPort Monitors</b>   |
| 6         | Keyboard/Mouse USB Ports    | • Connect a <b>USB Keyboard</b> and <b>Mouse</b>   |
| 7         | USB Hub Ports               | • Connect <b>USB 2.0 Peripheral Devices</b>  |

# Installation

## Connect the Console

**Note:** Power off all Computers, Displays, and Peripherals before completing the following steps.

1. Connect the **DisplayPort Displays** to the **Console DisplayPort Ports**, located on the front of the **KVM Switch**, using **DisplayPort Cables** (sold separately).
2. Connect a **USB Mouse** and a **USB Keyboard** to the **Console Keyboard and Mouse Ports**, located on the front of the **KVM Switch**.
3. (Optional) Connect the included **Remote Selector Cable** and place it in the desired location on the **Work Surface**.
4. (Optional) Connect up to two additional **USB Devices** to the **USB Hub Ports**, located on the front of the **KVM Switch**.
5. (Optional) Connect an **Audio Device** and a **Microphone** to the **Console Audio Ports**, located on the front of the **KVM Switch**.

## Connect the PCs

1. Connect **DisplayPort Cables** (sold separately) from the **DisplayPort Output Ports** on the **Computer** to the **PC 1 DisplayPort Input Ports**, located on the rear of the **KVM Switch**.
2. Connect a **USB Type-B Cable** (sold separately) from a **USB Port** on the **Computer** to the **PC 1 USB Host Connection**, located on the rear of the **KVM Switch**.
3. Repeat **Steps 1 and 2** for the remaining **PC**.
4. Connect the included **Power Adapter** from an available **Wall Outlet** to the **DC Power Input Port**, located on the rear of the **KVM Switch**.
5. Power on all connected **Peripheral Devices**.

# Regulatory Compliance

## FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to Part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment to an outlet on a different circuit than the receiver.
- Consult the dealer or an experienced radio/TV technician for help.

Any changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the device. If shielded interface cables are included with the product, or if additional components or accessories are designated for use with the installation, they must be used to ensure compliance with FCC regulations.

## ISED Statement / Déclaration d'ISDE

CAN ICES-003(B) / NMB-003(B)  
This Class B digital apparatus complies with Canadian ICES-003.  
This device complies with ISED Canada licence-exempt RSS standard(s). Operation is subject to the following two conditions: (1) this device may not cause interference, and (2) this device must accept any interference, including interference that may cause undesired operation of the device.  
Cet appareil numérique de la classe B est conforme à la norme NMB-003 du Canada.  
Le présent appareil est conforme aux CNR d'ISDE Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes : (1) l'appareil ne doit pas produire de brouillage, et (2) l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.

## Warranty Information

This product is backed by a two-year warranty.  
For further information on product warranty terms and conditions, please refer to [www.startech.com/warranty](http://www.startech.com/warranty).

# Operation

## LED Chart

| LED Indicator | Function  |
|---------------|---|
| Power         | • <b>Solid Red:</b> Indicates the <b>KVM Switch</b> is receiving power                          |
| PC 1          | • <b>Flashing Green:</b> <b>PC 1 Port</b> is selected but no <b>USB Connection</b> is detected  |
|               | • <b>Solid Green:</b> <b>PC 1 Port</b> is selected and a <b>USB Connection</b> is detected      |
| PC 2          | • <b>Flashing Orange:</b> <b>PC 1 Port</b> is selected but no <b>USB Connection</b> is detected |
|               | • <b>Solid Orange:</b> <b>PC 1 Port</b> is selected and a <b>USB Connection</b> is detected     |

## Hotkey Commands

For a list of available **Hotkey Commands**, please visit:  
[www.StarTech.com/P2ADD121D-KVM-SWITCH](http://www.StarTech.com/P2ADD121D-KVM-SWITCH)

## Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

## Safety Measures

If product has an exposed circuit board, do not touch the product under power.

### Mesures de sécurité

Si l'un des circuits imprimés du produit est visible, ne pas touchez le produit lorsqu'il est sous tension.

### 安全対策


製品に露出した状態の回路基盤が含まれる場合、電源が入っている状態で製品に触らないでください。

### Misure di sicurezza

Se il prodotto ha un circuito stampato visibile, non toccare il prodotto quando è acceso.

### Säkerhetsåtgärder

Rör aldrig vid enheter med oskyddade kretskort när strömmen är påslagen.



**StarTech.com Ltd.**  
45 Artisans Cres  
London, Ontario  
N5V 5E9  
Canada

**StarTech.com LLP**  
4490 South Hamilton  
Road  
Groveport, Ohio  
43125  
U.S.A.

**StarTech.com Ltd.**  
Unit B, Pinnacle 15  
Gowerton Rd,  
Brackmills  
Northampton  
NN4 7BW  
United Kingdom

**StarTech.com Ltd.**  
Siriusdreef 17-27  
2132 WT Hoofddorp  
The Netherlands

FR: [startech.com/fr](http://startech.com/fr)  
DE: [startech.com/de](http://startech.com/de)  
ES: [startech.com/es](http://startech.com/es)  
NL: [startech.com/nl](http://startech.com/nl)  
IT: [startech.com/it](http://startech.com/it)  
JP: [startech.com/jp](http://startech.com/jp)