



## User Manual

### Type-C to HDMI/USB-Ax2/RJ45/SD/Micro SD/Type-C PD Charging with DP1.4 Alt mode

Y10A310-S1

#### Congratulations

Thank you for purchasing this premium Rocstor product. For optimum performance and safety, please read these instructions carefully before connecting, operating or using this product. Please keep this manual for future reference.

#### Introduction

Rocstor introduces the Type-C 7-in-1 hub, equipped with HDMI, 2 USB-A ports, RJ45, SD/TF card slots, and a Type-C female port, offering an ideal solution for extending the port options of Type-C or Thunderbolt 3 hosts (PC/Laptop/Mobile phone, etc.), particularly beneficial for those with a single Type-C port. This hub incorporates the latest DP1.4 Alt mode supported IC, enabling HDMI video output at a maximum resolution of 4k/60Hz while simultaneously transferring USB 3.1 data at a maximum speed of 5Gbps. With 2 USB-A ports, you can connect 2 USB devices simultaneously, and the SD/Micro SD card slots support the insertion of 2 cards simultaneously for data transmission or accessing information on the host. The RJ45 port provides the host with access to Gigabit Ethernet. Additionally, the Type-C female port supports PD 3.0 with a maximum power delivery of 100W for PD Charging. Compatible with all DP Alt mode supported Type-C hosts, this hub ensures seamless compatibility and enhanced functionality.

#### Package Contents

Before attempting to use this unit, please check the packaging and make sure the following items are contained in it:

- Main Unit x1
- User Manual

#### Upstream:

##### USB Type-C Male (Connect to host computer)

- Support DP1.4 Alt mode, downward compatible with DP1.2 Alt mode
- Note:** To get max bandwidth, the host should support DP1.4 Alt mode with DSC format.

#### Downstream:

##### HDMI

- Supports HDMI max 4K/60Hz, 4:4:4, 8bit with 18Gbps Bandwidth
- Supports 6/8/10/12 bit color depth output
- Supports output pixel format RGB4:4:4/YCbCr4:4:4/YCbCr4:2:2
- Supports HDCP 2.2&HDCP1.4
- Supports HDR

**Note:** When connecting a DP1.4 Alt mode supported host, the max resolution of HDMI is 4k/60Hz; When connecting a DP1.2 Alt mode supported host, the max resolution of HDMI is 4k/30Hz due to bandwidth limitation

##### USB-A 3.0 X2

- 1 USB-A port supports max 7.5W(5V@1.5A) downstream charging, 2 USB-A share max 8W (5V/1.6A) downstream charging.
- Max 5Gbps bandwidth per USB-A port

##### SD/Micro SD 3.0

- Supports Secure Digital v3.0 UHS-I (Ultra High Speed): SDR12 (12.5Mbyte/s)/SDR25(25Mbyte/s)/SDR50(50Mbyte/s)/DDR50(50Mbyte/s)/SDR104(104Mbyte/s)

##### RJ45 (Gigabit Ethernet)

- Supports 10/100/1000Mbps bandwidth

##### Type-C Female (for PD Charging)

- Support PD Charging 100W (20V/5A)
- Support Fast Role Swap of PD 3.0, the connected device will not get disconnected while plugging in and out PD Adapter
- 8W is dedicated to the functioning of this product, the rest power (max 92W) will be passed to charge for the host

#### Specification

##### Input / Output Connector

Input	Type-C Male x1
Output	HDMI Female x1
	USB-A Female x2
	SD/Micro SD x1
	RJ45 x1
	Micro SD Card Slot x1
	Type-C Female x1 (only PD)

##### Warranty

Limited Warranty	3 Years
------------------	---------

##### Environmental

Operating Temperature	0°C to 45°C
Operating Humidity	10% to 90 % RH (no condensation)
Storage Temperature	-10°C to 70°C
Storage Humidity	10% to 90 % RH (no condensation)

##### Electronic Parameter

Input Voltage	5V
Power Consumption	Max 2W

##### Power Supply

USB-C PD Charging Port	100W(20V/5A)
------------------------	--------------

##### Regulatory Approvals

Certifications	FCC, CE
----------------	---------

##### Accessory Adapter

User Manual	English Version
-------------	-----------------



**Support**

Technical support is available to all the registered users of Rocstor products.

**Technical Support / RMA**  
Hours: 9:00 am - 5:00 pm PST  
Monday to Friday (except holidays)

Tell: +1 (818) 727-7000 (National and international)  
Fax: +1 (818) 875-0002  
Email: support@rocstor.com

**⚠ Safety Information:**

**WARNING:**  
Please follow these safety instructions. Failure to do so may result damages or injury. It is normal that the device adapter becomes very warm during use.

**Please note that:**  
Continuous contact with warm surfaces for extended time may cause discomfort or injury. In order to reduce the possibility of overheating or heat-related injuries, always allow needed ventilation around the device and use care when handling it. Avoid instances where your skin is in extended contact with the device when plugged into the host computer. It is not recommended to sleep with the device when plugged into a host computer. Avoid placing the device under a pillow, blanket, or your body when connected to a host computer. If you have a medical condition that affects your ability to detect heat against the body, extra care should be used. Never use the device in locations with water, such as a sink, bathtub, or shower stall. Never connect or disconnect the device with wet hands.



**Warranty Information**

**Warranty Information**  
This product is backed by a (3) three-year warranty. Rocstor warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. Rocstor does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

**Limitation of Liability**  
In no event shall the liability of Rocstor, Inc. and Rocstor (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

©2024 Rocstor, Inc. All rights reserved. Rocstor is registered trademark of Rocstor, Inc. Apple®, the Apple logo, Mac®, MacBook®, MacBook Pro®, MacBook Air®, iPad®, iPad Air®, iPad mini®, iPhone®, MacOS® are registered trademarks of Apple, Inc. Google® and Chromebook™ are registered trademarks of Google, LLC. Microsoft® is registered trademarks of Microsoft corporation. All other product names and logos mentioned herein may be trademarks of their respective companies. Thunderbolt is a trademark of Intel Corporation or its subsidiaries. USB Type-C® and USB-C® are registered trademark of USB Implementers Forum. The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI Trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc. Feature and specification are subject to change without notice. All trademarks and registered trademarks are the property of their respective. All rights reserved.

