



## User Manual

### Type-C to HDMI/USB-A 10GX2/Type-C data/RJ45/ PD Charging with DP1.4 Alt mode

Y10A319-S1

#### Congratulations

Thank you for purchasing this premium Rocstor product. For optimum performance and safety, please read these instructions carefully before connecting, operating or using this product. Please keep this manual for future reference.

#### Introduction

Rocstor introduces the Type-C 6-in-1 hub with HDMI, 2 USB-A, Type-C data, RJ45, and Type-C female port, offering a versatile solution for extending the port capabilities of Type-C or Thunderbolt hosts (PC/Laptop/Mobile phone, etc.), especially beneficial for those with a single Type-C port. This hub facilitates HDMI video output at a maximum resolution of 4k/60Hz while concurrently transferring USB 3.1 Gen2 data at a maximum speed of 10Gbps. With 2 USB-A ports and a Type-C data port, you can connect up to 3 USB devices simultaneously. The RJ45 port provides the host with access to Gigabit Ethernet. Additionally, the Type-C female port supports PD 3.0 with a maximum power delivery of 100W PD Charging. Compatible with all DP Alt mode supported Type-C hosts, this hub ensures seamless compatibility and enhanced functionality.

#### Package Contents

Before attempting to use this unit, please check the packaging and make sure the following items are contained in it:

- Main Unit x1
- User Manual

#### Upstream:

##### USB Type-C Male (Connect to a host computer)

- Supports DP1.4 Alt mode, downward compatible with DP1.2 Alt mode
- Supports USB3.0/2.0 data transmission (transfer speed: Max 10Gbps)
- Supports transmission of DP Alt Mode video up to 4K/60Hz Simultaneously

**Note:** To get max bandwidth, the host should support DP1.4 Alt mode & DSC

#### Downstream:

##### HDMI

- Supports HDMI max 4K/60Hz
- Supports 8/10/12 bit color depth output
- Supports output pixel format RGB/YCbCr4:4:4/YCbCr4:2:2/YCbCr4:2:0
- Supports dynamic HDR
- Supports HDCP2.3

**Note:** The actual resolution supported is determined by the host and the Display.

##### RJ45 X1

- Supports Gigabit Ethernet, 10M/100M/1000M
- Supports Wake-On-LAN
- Supports full duplex flow control
- Light indicates the state, no light when no Internet connected, orange light turns on when network connection is established, white light flashes when transmitting data

##### Type-C Data 10G X1 (Close to HDMI)

- Max 10Gbps data transmission
- Supports max 7.5W(5V/1.5A) downstream charging
- Supports short-circuit, over-current, over-voltage protection

##### USB-A X2

- Max 10Gbps data transmission per port
- Supports max 7.5W(5V/1.5A) downstream charging the port close to Type-C male port, another port supports max 900mA downstream charging.
- 2 USB-A port share max 12 W(5V/2.4A), the 2 USB-A port and the Type-C data port share max 13W(5V/2.6A)
- Supports short-circuit, over-current, over-voltage protection

##### Type-C Female X1 (for PD Charging & Data)

- Supports max 100W PD charging
- Supports PD3.0 Fast Role Swap, the connected device will not get disconnected while plugging out PD Adapter
- 15W is dedicated to the functioning of this product, the rest power (max 85W) will be passed to charge for the host

#### Specification

##### Input / Output Connector

Input	Type-C Male x1
Output	HDMI Female x1 Type-C data 10G x1 USB-A 10G x2 RJ45 x1 Type-C Female x 1 (for PD Charging)

##### Mechanical

Weight	3.7lbs (105g)
Size	4.7x1.9x0.6in (120x50x15.5mm)

##### Warranty

Limited Warranty	3 Years
------------------	---------

##### Environmental

Operating Temperature	0°C to 45°C (32°F to 113°F)
Operating Humidity	10% to 85% RH (no condensation)
Storage Temperature	-10°C to 70°C (14°F to 158°F)
Storage Humidity	5% to 90 % RH (no condensation)

##### Regulatory Approvals

Certifications	FCC, CE
----------------	---------

##### Accessory Adapter

User Manual	English Version
-------------	-----------------

## Connection Diagram



## Support

Technical support is available to all the registered users of Rocstor products.

### Technical Support / RMA

Hours: 9:00 am - 5:00 pm PST

Monday to Friday (except holidays)

Tell: +1 (818) 727-7000 (National and international)

Fax: +1 (818) 875-0002

Email: [support@rocstor.com](mailto:support@rocstor.com)

## ⚠ Safety Information:

### WARNING:

Please follow these safety instructions. Failure to do so may result damages or injury. It is normal that the device adapter becomes very warm during use.

### Please note that:

Continuous contact with warm surfaces for extended time may cause discomfort or injury. In order to reduce the possibility of overheating or heat-related injuries, always allow needed ventilation around the device and use care when handling it. Avoid instances where your skin is in extended contact with the device when plugged into the host computer. It is not recommended to sleep with the device when plugged into a host computer. Avoid placing the device under a pillow, blanket, or your body when connected to a host computer. If you have a medical condition that affects your ability to detect heat against the body, extra care should be used. Never use the device in locations with water, such as a sink, bathtub, or shower stall. Never connect or disconnect the device with wet hands.



## Warranty Information

### Warranty Information

This product is backed by a (3) three-year warranty. Rocstor warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. Rocstor does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

### Limitation of Liability

In no event shall the liability of Rocstor, Inc. and Rocstor (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

©2024 Rocstor, Inc. All rights reserved. Rocstor is registered trademark of Rocstor, Inc. Apple®, the Apple logo, Mac®, MacBook®, MacBook Pro®, MacBook Air®, iPad®, iPad Air®, iPad mini®, iPad Air®, iPhone®, MacOS® are registered trademarks of Apple, Inc. Google® and Chromebook™ are registered trademarks of Google, LLC. Microsoft® is registered trademarks of Microsoft corporation. All other product names and logos mentioned herein may be trademarks of their respective companies. Thunderbolt is a trademark of Intel Corporation or its subsidiaries. USB Type-C® and USB-C® are registered trademark of USB Implementers Forum. The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI Trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc. Feature and specification are subject to change without notice. All trademarks and registered trademarks are the property of their respective. All rights reserved.

