



ORDERING GUIDE

FortiExtender

FortiExtenders are secure 5G/LTE gateways from Fortinet. They offer secure connectivity and enhanced network resiliency for businesses, supporting critical features such as wireless WAN, carrier failover, out of band management (OBM), LAN extensions via VxLAN over IPsec, WAN extensions, active/active connections, VRRP, split tunneling, and more. In this guide, you will find essential information about each FortiExtender model to help you appropriately size and scope your environment.

ORDER INFORMATION

APPLIANCES	ENTRY LEVEL			MIDRANGE
	101F	201F	202F	311F
Number of Modems	Single modem	Single modem	Dual modem	Single modem
Module Category	CAT-6/LTE	CAT-7/LTE	CAT-7/LTE	CAT-16/LTE
SIM Slots	Dual SIM	Dual SIM	Two-Dual SIM	Dual SIM
Connectivity				
Dedicated WAN Ports	1	1	1	1-SFP, 1-WAN
LAN/Switch Ports	4	4	4	4
FortiGate LAN Extension	✓	✓	✓	✓
Hardware Variants				
North America		FEX-201F-AM	FEX-202F-AM	
EMEA/APAC	FEX-101F-EA	FEX-201F-EA	FEX-202F-EA	
Global				FEX-311F
FortiGate-Managed				
FC Premium Support		FC-10-FA21F-247-02-DD	FC-10-FA22F-247-02-DD	
	FC-10-X101A-247-02-DD	FC-10-FE21F-247-02-DD	FC-10-FE22F-247-02-DD	FC-10-X311F-247-02-DD
FortiEdge-Cloud Managed				
FC Support + Management	FC-10-FEXC0-583-02-DD	FC-10-FEXC0-583-02-DD	FC-10-FEXC2-583-02-DD	
	FC-10-FEXC0-583-02-DD	FC-10-FEXC0-583-02-DD	FC-10-FEXC2-583-02-DD	FC-10-FEXC2-583-02-DD

ORDER INFORMATION

Appliances	High End			Vehicle	
	511G	511G-WiFi	511F	211F	212F
Number of Modems	Single Modem	Single Modem	Single modem	Single modem	Dual modem
Module Category	5G	5G	5G	CAT-12/LTE	CAT-12/LTE
SIM Slots	Dual SIM	Dual SIM	Dual SIM	Dual SIM	Two-Dual SIM
Connectivity					
Dedicated WAN Ports	1	1	1-SFP, 1-WAN	1	1
LAN/Switch Ports	1-SFP+RJ45 and 3-LAN	1-SFP+RJ45 and 3-LAN	4	4	4
Wi-Fi (Built-in AP)	No	YES		Ⓢ	Ⓢ
FortiGate LAN Extension	YES	YES	Ⓢ	Ⓢ	Ⓢ
Hardware Variants					
North America				FEV-211F-AM	FEV-212F-AM
Global	FEX-511G	FEX-511G-WiFi-x	FEX-511F	FEV-211F	FEV-212F
FortiGate-Managed					
FC Premium Support	FC-10-FX51G-247-02-DD	FC-10-XW51G-247-02-DD	FC-10-X511F-247-02-DD	FC-10-FV21F-247-02-DD	FC-10-FV22F-247-02-DD
				FC-10-FG21F-247-02-DD	FC-10-FG22F-247-02-DD
FortiEdge-Cloud Managed					
FC Support + Management	FC-10-FEXC2-583-02-DD	FC-10-FEXC2-583-02-DD	FC-10-FEXC2-583-02-DD	FC-10-FEXC2-583-02-DD	FC-10-FEXC2-583-02-DD
				FC-10-FEXC2-583-02-DD	FC-10-FEXC2-583-02-DD
FortiSASE Managed					
FortiSASE Subscription	TBD	TBD		TBD	TBD

FREQUENTLY ASKED QUESTIONS

What is the difference between dual SIM and dual modem?

All FortiExtender models support dual SIM slots to enable redundancy between carriers based on various metrics like signal strength and data plan. Single modem units may only initiate a connection to one carrier at a time. A “2” in the model number (i.e. 202F, 212F) indicates dual modem models, which allow you to have two active wireless connections for faster failover and path selection.

What are FortiGate and FortiSASE LAN extension?

FortiGate LAN extension allows you to seamlessly connect from your FortiExtender locations into a remote FortiGate at an HQ or centralized location. From your connected FortiGate, you can control the ports and connectivity of FortiExtender locations. FortSASE LAN extension works similarly, but with your connection into your FortiSASE Cloud account. FortiExtender 200F supports FortiSASE LAN extension to easily connect your microbranch locations into SASE for cloud-delivered security and connectivity. We will be introducing three new models in 2024 for Thin Edge deployments, called FortiBranchSASE.

Can I use a FortiExtender Vehicle at Fixed Sites?

Yes, FortiExtender Vehicle is a great device for fixed sites with harsh environmental conditions. As an IP64 ruggedized device, FortiExtender Vehicle offers protection against extreme temperatures, shock, vibration, humidity, and are dust and splash tight. In addition, you can leverage LAN extension with your FortiExtender Vehicle, deploying FortiGuard protections, including the OT Security Service, from a centralized FortiGate at the remote FortiExtender Vehicle site.

Visit www.fortinet.com for more details



Copyright © 2025 Fortinet, Inc. All rights reserved. Fortinet®, FortiGate®, FortiCare® and FortiGuard®, and certain other marks are registered trademarks of Fortinet, Inc., and other Fortinet names herein may also be registered and/or common law trademarks of Fortinet. All other product or company names may be trademarks of their respective owners. Performance and other metrics contained herein were attained in internal lab tests under ideal conditions, and actual performance and other results may vary. Network variables, different network environments and other conditions may affect performance results. Nothing herein represents any binding commitment by Fortinet, and Fortinet disclaims all warranties, whether express or implied, except to the extent Fortinet enters a binding written contract, signed by Fortinet's SVP Legal and above, with a purchaser that expressly warrants that the identified product will perform according to certain expressly-identified performance metrics and, in such event, only the specific performance metrics expressly identified in such binding written contract shall be binding on Fortinet. For absolute clarity, any such warranty will be limited to performance in the same ideal conditions as in Fortinet's internal lab tests. Fortinet disclaims in full all covenants, representations, and guarantees pursuant hereto, whether express or implied. Fortinet reserves the right to change, modify, transfer, or otherwise revise this publication without notice, and the most current version of the publication shall be applicable.