

# Lenovo 500e Yoga Chromebook Gen 4



Powered by Intel N-Series processor, this lightweight, 360-degree convertible device is purpose-built with the versatility to help professionals annotate documents and collaborate easily. It comes with up to 12 hours of battery life enabling users to work from anywhere without any hassle. Plus, dual USB 3.2 Gen1, USB-C 3.2 Gen2, HDMI, and a 3.5-mm headphone or microphone combo jack allow users to connect to peripherals or plug-in headphones for listening to meetings on the go.

## Redefining possibilities with powerful performance and groundbreaking on-device AI

Whether you're crunching numbers, analyzing market trends, or collaborating on presentations, these laptops, equipped with the latest-generation processors and ample memory, ensure unparalleled efficiency and reliability.

The 12.2” multi-touch glossy display provides a rich visual experience enabling professionals to scroll through spreadsheets, detailed documents, or presentations with a fingertip. Additionally, with an optional Lenovo Integrated Pen, navigate through data easily.

Configured with up to 128GB SSD storage and up to 8GB LPDDR5 memory, this device lets users multitask and ensures faster retrieval of detailed datasheets.

# Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



### Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

# Accessories

# Lenovo 500e Yoga Chromebook Gen 4

## Performance

**Processor**
Intel N Series

**Operating System**
ChromeOS

**Graphics**
Intel UHD Graphics (integrated)

**Memory**
4GB LPDDR5-4800, soldered
8GB LPDDR5-4800, soldered

**Storage** [1]
32GB eMMC 5.1 on systemboard
64GB eMMC 5.1 on systemboard
128GB eMMC 5.1 on systemboard

[1] *The storage capacity supported is based on the test results with current Lenovo storage offerings.*

**Audio**
High Definition (HD) Audio
Stereo speakers, 2W x2,
optimized with Waves MaxxAudio, Smart AMP
Dual-microphone array or
Dual-microphone array + single microphone

**Camera***
Front HD 720p, with privacy shutter
Front HD 720p, with privacy shutter; rear 5MP
Front FHD 1080p, with privacy shutter
Front FHD 1080p, with privacy shutter; rear 5MP

**Battery** [2]
47Wh battery (up to 12 hr), Rapid Charge

[2] *Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.*

**Power Adapter***
45W USB-C adapter, PD 3.0
65W USB-C adapter, PD 3.0

## Design

**Display** [3]
12.2" WUXGA (1920x1200) IPS Glossy 16:10
- 300nits, Anti-fingerprint, 50% NTSC, 60Hz, Corning Gorilla Glass, TÜV Low Blue Light, touch

[3] *IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.*

**Multimode**
Laptop, tent, stand and tablet modes supported by 360° hinge

**Pen***
Lenovo Integrated Pen*

**Keyboard**
Top-load keyboard, 6-row, spill-resistant,
Anti-pick proof keycaps with full skirt design

**Touchpad**
Mylar surface touchpad
60.5 x 104 mm
(2.38 x 4.09 inches)

**Dimensions** [4]
287 x 208 x 18.9 mm (11.3 x 8.2 x 0.74 inches)

[4] *The system dimensions may vary depending on configurations.*

**Weight** [5]
Starting at 1.32 kg (2.91 lbs)

[5] *The system weight is approximate and may vary depending on configurations*

**Color**
Graphite grey

**Case material**
PC-ABS + 15% Talc + TPU (top), PC-ABS + 15% Talc (bottom)

## Connectivity

**WLAN + Bluetooth*** [6]
Intel Wi-Fi 6 AX211, 802.11ax, Bluetooth 5.1
Mediatek Wi-Fi 6 MT7921, 802.11ax, Bluetooth 5.1

[6] *Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitations.*

**WWAN***
4G LTE CAT6*

**Ports**
1x HDMI 1.4
2x USB 3.2 Gen 1
1x USB-C 3.2 Gen 2 (data, PD, DP)
1x Headphone / microphone combo jack (3.5mm)

## Security & Privacy

**Security**
Google Security Chip H1
Camera privacy shutter
Kensington Nano Security Slot

## Certifications

**Green Certifications** [7] [8] [9]
EPEAT Gold Registered
ENERGY STAR 8.0
ErP Lot 6
ErP Lot 26
TCO Certified 9.0
RoHS compliant

[7] *The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.*

[8] *EPEAT registration and ENERGY STAR certification are dependent on system OS.*

[9] *EPEAT is registered where applicable, please see epeat.net for registration status by country.*

**Other Certifications**
ASTM F963
MIL-STD-810H military test passed
TÜV Rheinland Low Blue Light (Hardware Solution)

Items with * are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2024 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.